

Northbrook, Illinois • (847) 272-8800  
Melville, New York • (631) 271-6200  
Santa Clara, California • (408) 985-2400  
Research Triangle Park,  
North Carolina • (919) 549-1400  
Camas, Washington • (360) 817-5500



VIKING CORP  
MR E JACKSON  
210 N INDUSTRIAL PARK RD  
HASTINGS MI 49058

**RE: Project Number(s) - 01NK25627**

Your most recent Certification is shown below. You may also view this information, or a portion of this information (depending on the product category), on UL's Online Certifications Directory at [www.ul.com/database](http://www.ul.com/database). Please review the text and contact the Conformity Assessment Services staff member who handled your project if revisions are required. For instructions on placing an order for this information in a 3 x 5-inch format, you may refer to the enclosed order form for UL Card Service.

HMER  
Check Valves

July 3, 2002

VIKING CORP  
210 N INDUSTRIAL PARK RD, HASTINGS MI 49058

EX1299

Swing type, iron body, Model D-1, sizes 2-1/2 and 3 in.  
Swing type, iron body, Models D-1, E-1, sizes 2-1/2 in. rated for 250 psig.  
Swing type, iron body, Model D-2, sizes 4 and 6 in.  
Swing type, iron body, Model E-1, sizes 2-1/2, 3, 4, 6 and 8 in.  
Swing type, iron body, Model E-2, sizes 3 and 8 in.  
Swing type, iron body, Model F-1, sizes 3, 4, 6 and 8 in. rated for 250 psig.  
Swing type, iron body, Model G-1, sizes 3, 4, 6 and 8 in. rated for 250 psig.  
Model L-1, Groove/Groove, sizes 1-1/2 and 2 in. rated for 250 psig.  
Model K-1, NPT threaded, sizes 1-1/2 and 2 in. rated for 250 psig.

---

**LOOK FOR LISTING MARK ON PRODUCT**



VIKING CORP  
MR P THOMAS  
210 N INDUSTRIAL PARK RD  
HASTINGS MI 49058

Your most recent listing is shown below. Please review this information and report any inaccuracies to the UL Engineering staff member who handled your Assignment.

HMER  
Check Valves

August 20, 1996

VIKING CORP , HASTINGS MI 49058

EX1299 (N)

Swing type, iron body, Model D-1, sizes 2-1/2 and 3 in.  
Swing type, iron body, Models D-1, E-1, sizes 2-1/2 in. rated for 250 psig.  
Swing type, iron body, Model D-2, sizes 4 and 6 in.  
Swing type, iron body, Model E-1, sizes 2-1/2, 3, 4, 6 and 8 in.  
Swing type, iron body, Model E-2, sizes 3 and 8 in.  
Swing type, iron body, Model F-1, sizes 3, 4, 6 and 8 in. rated for 250 psig.  
Swing type, iron body, Model G-1, sizes 3, 4, 6 and 8 in. rated for 250 psig.

210 N INDUSTRIAL PARK RD

LOOK FOR LISTING MARK ON PRODUCT

Replaces EX1299 dated January 24, 1996.

740276001

Underwriters Laboratories Inc.®

B11/0062284

244

For information on placing an order for UL Listing Cards in a 3 x 5 inch card format, please refer to the enclosed ordering information.

UNDERWRITERS LABORATORIES INC.

A not-for-profit organization dedicated to public safety and committed to quality service

333 Pfingsten Road  
Northbrook, Illinois 60062-2096, USA  
847/272-8800  
Telex: 6502543343  
FAX No. (847) 272-8129

1285 Walt Whitman Road  
Melville, L.I., New York 11747-3081, USA  
516/271-6200  
Telex No. 6852015  
FAX No. (516) 271-8259

1655 Scott Blvd.  
Santa Clara, California 95050-4169, USA  
408/985-2400  
FAX No. (408) 296-3256

12 Laboratory Drive  
P.O. Box 13995  
Research Triangle Park,  
North Carolina 27709-3995, USA  
919/549-1400  
Telex No. 4937928  
FAX No. (919) 547-6000