

Northbrook, Illinois • (847) 272-8800  
 Melville, New York • (631) 271-6200  
 Santa Clara, California • (408) 985-2400  
 Research Triangle Park,  
 North Carolina • (919) 549-1400  
 Camas, Washington • (360) 817-5500



VIKING CORP  
 MR E JACKSON  
 210 N INDUSTRIAL PARK RD  
 HASTINGS MI 49058

**RE: Project Number(s) - 00NK22131**

Your most recent listing is shown below. Please review this information and report any inaccuracies to the UL Engineering staff member who handled your project.

For information on placing an order for UL Listing Cards in a 3 x 5 inch format, please refer to the enclosed ordering information.

**VLMT** September 14, 2000  
**Special System Water Control Valves - Pressure Reducing And Pressure Control Type**

**VIKING CORP**  
**210 N INDUSTRIAL PARK RD, HASTINGS MI 49058**

**EX4529**

Viking Model A-1 pilot operated pressure control valves, ductile iron body consisting of the following sizes, inlet pressure ratings and outlet pressure setting ranges:

Model	Size In.	Max Rated Inlet Pressure psig	Outlet Pressure Setting Range psig
A-2	2, 4, 6	175	25-150
A-2	2	250	80-150
A-2**	4, 6	250	80-150

\*\*For use on deluge (open sprinkler) systems only.  
 For all valves, the manufacturer's design and installation instructions include a description of the performance characteristics for both flow and static conditions.

**LOOK FOR LISTING MARK ON PRODUCT**