


PILOT REGULATING FLOW CONTROL TRIM

2" (DN50) MODEL H

FLOW CONTROL VALVE

The Viking Corporation, 210 N Industrial Park Drive, Hastings MI 49058 Telephone: 269-945-9501 Technical Services 877-384-5464 Fax: 269-818-1680 Email: techsvcs@vikingcorp.com




Valve Size	Galvanized Trim Part No.	Brass Trim Part No.
2" (DN50)	14764-1	14764-2
This trim is for use with the following Release Module Trim Kit		
Release Type	Galvanized	Brass
Electric	10830	10832
Note: Nipple lengths for brass trim may vary from those shown on this Trim Chart.		

Note: When viewing this data page online, blue text represents hyper links and will open the appropriate data page when clicked.

Notes: For use with Trim Charts on Page 543 b

General Notes:

- Valve must be trimmed as shown. Any deviation from trim size or arrangement may affect the proper operation of the valve.
- · Dimensions in parenthesis are millimeters.
- Viking uses ANSI tee designations (large outlet on run, small outlet on run, side outlet) in all trim call-outs.





- Note 1: Release System connection.
- Note 2: Alarm Connections: Connect alarm line piping to 3/4" (20 mm) NPT outlet. When using a Water Motor Alarm, a strainer is required. 1/2" (15 mm) NPT outlet is for electric Alarm Pressure Switch.
- Note 3: Optional non-interruptible connection for Alarm Pressure Switch to activate electric alarm panel. Note: After the Deluge Valve trips, this location cannot be shut off. Alarms may operate until the outlet chamber of the deluge valve is de-pressurized below the set point of the Alarm Pressure Switch.
- Note 4: Viking Drain Check Valve is manufactured with a 0.067^e (1.7 mm) orifice to allow alarm line to drain. Do not substitute. Check label for proper orientation.

for General Notes and

Refer to page 543a

2" Pilot Regulating Flow Control Trim for Model H Flow Control Valve







€ÐÐ



The Viking Corporation, 210 N Industrial Park Drive, Hastings MI 49058 Telephone: 269-945-9501 Technical Services 877-384-5464 Fax: 269-818-1680 Email: techsvcs@vikingcorp.com







THIS PAGE INTENTIONALLY LEFT BLANK