




Strut Channel (Single & Double)

Technical Features

- **Sizes available (mm) :**
Single:
2m Length - 21x41x1,5, 21x41x2,5, 41x41x1,5, 41x41x2,5
3m Length - 21x41x1,5, 21x41x2,5, 21x41x2,5*, 41x41x1,5*, 41x41x2,5*, 62x41x2,5*
6m Length - 21x41x1,5, 21x41x2,5*, 41x41x1,5*, 41x41x2,5*, 62x41x2,5*
Double:
3m Length: 21x41x2,5*, 41x41x2,5*
6m Length: 21x41x2,5*, 41x41x2,5*, 62x41x2,5*, 83x41x2,5*
 - **Material :** Carbon steel
 - **Finish :** Pre-galvanized or hot-dipped galvanized (See note*)
 - **Compatibility :** Compatible with wall brackets, vertical APX and horizontal APY (see separate datasheet).
- * Available in both Pre-Galvanized (PG) and Hot-Dipped Galvanized (HDG)



Strut Channel - Single and Double

Physical Data

Section (mm) AxBxS	Profile Type	Finish	Length (mm) L	Dimensions (mm / inch)			Box Qty.	Weight (x1) (kg / lbs)	Reference
				C	D x E	H			
21 x 41 x 1,50	Single	PG	3000	22,3 / 0.89	11,0 x 27 / 0.43 x 1.06	50,0 / 1.97	10	2,56 / 5.64	317119
21 x 41 x 2,50	Single	PG	2000	22,3 / 0.89	14,0 x 27 / 0.55 x 1.06	50,0 / 1.97	10	3,40 / 7.50	387365
21 x 41 x 2,50	Single	PG	3000	22,3 / 0.89	14,0 x 27 / 0.55 x 1.06	50,0 / 1.97	10	5,10 / 11.24	310241
21 x 41 x 2,50	Single	PG*	6000	22,3 / 0.89	14,0 x 27 / 0.55 x 1.06	50,0 / 1.97	10	10,20 / 22.50	310255
41 x 41 x 1,50	Single	PG	3000	22,3 / 0.89	11,0 x 27 / 0.43 x 1.06	50,0 / 1.97	10	5,58 / 12.30	317099
41 x 41 x 1,50	Single	PG*	6000	22,3 / 0.89	11,0 x 27 / 0.43 x 1.06	50,0 / 1.97	10	11,16 / 24.60	317111
41 x 41 x 2,50	Single	PG*	2000	22,3 / 0.89	14,0 x 27 / 0.55 x 1.06	50,0 / 1.97	10	5,20 / 11.46	385505
41 x 41 x 2,50	Single	PG	3000	22,3 / 0.89	14,0 x 27 / 0.55 x 1.06	50,0 / 1.97	10	7,80 / 17.20	310299
41 x 41 x 2,50	Single	PG	6000	22,3 / 0.89	14,0 x 27 / 0.55 x 1.06	50,0 / 1.97	10	15,60 / 34.40	310311
62 x 41 x 2,50	Single	PG*	6000	22,3 / 0.89	14,0 x 27 / 0.55 x 1.06	50,0 / 1.97	10	22,00 / 48.50	310635
83 x 41 x 2,50	Single	PG	6000	22,3 / 0.89	14,0 x 27 / 0.55 x 1.06	50,0 / 1.97	10	29,40 / 64.80	310605
21 x 41 x 2,50	Single	HDG	3000	22,3 / 0.89	14,0 x 27 / 0.55 x 1.06	50,0 / 1.97	10	5,10 / 11.24	310281
21 x 41 x 2,50	Single	HDG	6000	22,3 / 0.89	14,0 x 27 / 0.55 x 1.06	50,0 / 1.97	10	10,60 / 23.36	310291
41 x 41 x 2,50	Single	HDG	3000	22,3 / 0.89	14,0 x 27 / 0.55 x 1.06	50,0 / 1.97	10	7,90 / 17.41	310339
41 x 41 x 2,50	Single	HDG	6000	22,3 / 0.89	14,0 x 27 / 0.55 x 1.06	50,0 / 1.97	10	15,80 / 34.83	310358
41 x 41 x 2,50	Double	PG	3000	22,3 / 0.89	14,0 x 27 / 0.55 x 1.06	50,0 / 1.97	5	15,60 / 34.40	310181
41 x 41 x 2,50	Double	PG	6000	22,3 / 0.89	14,0 x 27 / 0.55 x 1.06	50,0 / 1.97	5	31,20 / 68.78	310191
62 x 41 x 2,50	Double	PG*	6000	22,3 / 0.89	14,0 x 27 / 0.55 x 1.06	50,0 / 1.97	5	44,00 / 97.00	310650
83 x 41 x 2,50	Double	PG*	6000	22,3 / 0.89	14,0 x 27 / 0.55 x 1.06	50,0 / 1.97	5	58,80 / 129.63	310620

* Also Available in Hot-Dipped Galvanized finish

