



Blank End Cap

Class 7160 Blank End & 7160H End Cap

Technical Features


- **Available sizes (Pipe Size) :** Blank End: DN32/1 1/4" through DN300/12". End Cap DN350/14" through DN600/24".
- **Max Working Pressure :** Up to working pressure of pipe and gasket type being used.
- **Material :** Ductile Iron to ASTM A536, Gr. 65-45-12.
- **Finish :** Painted Red, Galvanised or Epoxy Coated.
- **Connections :** Grooved-end specifications conform to ANSI/AWWA C606-97 and can be used for fire sprinkler pipe systems in conjunction with any grooved coupling or component.



Class 7160
Blank End



Class 7160H
End Cap



1 1/4" - 12"



14" - 24"



Grooved Products

Blank End Cap - Class 7160 Blank End & 7160H End Cap

Physical Data

Nominal Size		Pipe O.D.		Class 7160 Blank End Cap & 7160H End Cap		Reference	
mm	inch	mm	inch	E-E (mm/inch)	Weight (Kgs/lbs)	Painted	Galvanized
32	1 1/4"	42.2	1.660	25 / 1.00	0.15 / 0.5	7160/042	7160/042G
40	1 1/2"	48.3	1.900	25 / 1.00	0.17 / 0.5	7160/048	7160/048G
50	2"	60.3	2.375	25 / 1.00	0.30 / 0.7	7160/063	7160/063G
-	2 1/2"	73.0	2.875	25 / 1.00	0.46 / 1.1	7160/073	7160/073G
65	3" OD	76.1	3.000	25 / 1.00	0.48 / 1.1	7160/076	7160/076G
80	3"	88.9	3.500	25 / 1.00	0.66 / 1.5	7160/089	7160/089G
-	4 1/4" OD	108.0	4.250	25 / 1.00	0.91 / 2.0	7160/108	7160/108G
100	4"	114.3	4.500	25 / 1.00	1.00 / 2.2	7160/114	7160/114G
-	5 1/4" OD	133.0	5.250	25 / 1.00	2.05 / 4.5	7160/133	7160/133G
125	5 1/2" OD	139.7	5.500	25 / 1.00	2.10 / 4.6	7160/139	7160/139G
125	5"	141.3	5.563	25 / 1.00	2.14 / 4.6	7160/141	7160/141G
-	6 1/4" OD	159.0	6.250	25 / 1.00	2.77 / 6.1	7160/159	7160/159G
150	6 1/2" OD	165.1	6.500	25 / 1.00	2.70 / 6.0	7160/165	7160/165G
150	6"	168.3	6.625	25 / 1.00	2.81 / 6.2	7160/168	7160/168G
200	8"	219.1	8.625	30 / 1.18	5.00 / 11.0	7160/219	7160/219G
250	10"	273.0	10.750	32 / 1.25	9.5 / 20.9	7160/273	7160/273G
300	12"	323.9	12.750	32 / 1.25	12.0 / 26.4	7160/323	7160/323G
350	14" OD	355.6	14.000	165 / 6.50	17.7 / 39.0	7160/355*	7160/355G*
400	16" OD	406.4	16.000	165 / 6.50	21.8 / 48.0	7160/406*	7160/406G*
450	18" OD	457.2	18.000	178 / 7.00	28.6 / 63.0	7160/457*	7160/457G*
500	20" OD	508.0	20.000	178 / 7.00	35.0 / 77.0	7160/508*	7160/508G*
600	24" OD	609.6	24.000	203 / 8.00	52.7 / 116.0	7160/609*	7160/609G*

* Class 7160H End Cap