



# Viking Dry Sprinkler Order Form

Customer: \_\_\_\_\_ Date: \_\_\_\_\_

Ship To: \_\_\_\_\_ P.O. #: \_\_\_\_\_




\_\_\_\_\_ Ship Via: \_\_\_\_\_


\_\_\_\_\_ Tag: \_\_\_\_\_





Standard Adjustable	Available Finishes: Chrome, White, White with chrome escutcheon and sleeve		
	Available Temperatures: B, D, E, G		Order in 1/2" increments
	VK154 (SR) VK163 (SR LO) VK176 (QR) VK177 (QR LO) VK286 (QR LO*)  *Fusible Link (165°, 205°, 280°)  <input type="checkbox"/>	 VK156 (SR) VK252 (SR OH) VK178 (QR) VK277 (QR OH) VK288 (QR OH*)  *Fusible Link (165°, 205°, 280°)  <input type="checkbox"/>	 VK157 (SR) Available in Chrome only.  <input type="checkbox"/>
	Pendent A Dimension	Horizontal Sidewall A Dimension	Vertical Sidewall A Dimension

**Follow these steps to order:**

1. **Check** box next to desired head and **circle** SIN.
2. **Circle** Type, Temperature and Finish.
3. **Indicate** quantities and dimensions required.
4. **Sign** and **return** by fax to:

Recessed Adjustable	Available Finish: Chrome, White		
	Available Temperatures: B, D, E		Order in 1/4" increments
	 VK158 (SR) VK164 (SR LO) VK186 (SR**) VK169 (SR***) VK180 (QR) VK181 (QR LO) VK186 (QR**) VK290 (QR LO*)  *Fusible Link (165°, 205°) **Extended Coverage (B, D only) ***Stainless Steel  <input type="checkbox"/>	 VK162 (SR) VK254 (SR OH) VK188 (SR**) VK182 (QR) VK279 (QR OH) VK188 (QR**) VK292 (QR OH*)  *Fusible Link (165°, 205°) **Extended Coverage (B, D only)  <input type="checkbox"/>	 VK161 (SR)  <input type="checkbox"/>
	Pendent A Dimension	Horizontal Sidewall A Dimension	Vertical Sidewall A Dimension

Concealed	Chrome, White, Ivory, Black
	Sprinkler B, D, E; Cover A, C
	Order in 1/4" increments
	Order cover separately (p/n 12381)
 VK190 (SR) VK192 (SR LO) VK196 (SR**) VK194 (QR) VK196 (QR***)  **SR Ext Cov (B only) ***QR Ext Cov (A, B, D)  <input type="checkbox"/>	Pendent A Dimension

Plain Barrel	Available Finish: Chrome, Brass			
	Available Temperatures: B, D, E, G		Order in 1/2" increments	
	 VK150 (SR) VK166 (SR LO) VK168 (SR**) VK172 (QR) VK173 (QR LO) VK282 (QR LO*)  *Fusible Link (165°, 205°, 280°) **Stainless Steel  <input type="checkbox"/>	 VK152 (SR) VK250 (SR OH) VK174 (QR) VK275 (QR OH) VK284 (QR OH*)  *Fusible Link (165°, 205°, 280°)  <input type="checkbox"/>	 VK153 (SR)  <input type="checkbox"/>	 VK160 (SR) VK184 (QR) Available in Brass only.  <input type="checkbox"/>
	Pendent A Dimension	Horizontal Sidewall A Dimension	Vertical Sidewall B Dimension	Upright B Dimension

Type:	Standard Response	/	Quick Response		Extended Coverage (Recessed and Concealed only)		Y / N
Temperatures (°F/°C):	135°/57°=A		155°/68°=B	165°/74°=C	175°/79°=D	200°/93°=E	286°/141°=G
Available Finishes:	Brass		Chrome	White	Ivory	Black	Stainless

Quantity	A/B Dimension	Quantity	A/B Dimension	Quantity	A/B Dimension

Dry sprinklers are custom made and are NOT RETURNABLE. Please check the information carefully before ordering. Refer to Viking Data Book for detailed product information.

Authorized by: \_\_\_\_\_  
(Customer Signature)

NOTE: A Dimension is the distance from the face of the fitting (tee) to desired finished surface of ceiling.  
B Dimension is the distance from the face of the fitting (tee) to the top of the deflector.