

	EC Flat Concealed HSW Light Hazard Quick Response Extended Coverage Fusible Link Flat Concealed Sidewall				VK680 Cover Plate <i>Diameter = 3-5/16 inches</i>	
	SIN: VK680 K Factor: 8.0 (115) Thread Size: 3/4 inch NPT Base Part #: 17114AC					
Finish	Temp	Part #	IPG	List Price		
Standard Brass	165°F	17114AC	V16.3	\$88.51		
Heavy Duty Spk Wrench		16208W/R	V20	\$65.87		
Limited Use Spk Wrench		16267	V20	\$21.15		

	Mirage^{®1} Quick Response Extended Coverage Glass Bulb Concealed Pendent			
	SIN: VK632 K Factor: 5.6 (81) Thread Size: 1/2 inch NPT Base Part #: 14613A			
Finish	Temp	Part #	IPG	List Price
Standard Brass	135°F	14613AA	V16.4	\$56.57
Standard Brass	155°F	14613AB	V16.4	\$56.57
Standard Brass	175°F	14613AD	V16.4	\$56.57
Standard Brass	200°F	14613AE	V16.4	\$56.57
Heavy Duty Spk Wrench		14047W/B	V20	\$103.21
Cabinet Wrench/Cap Tool		14031	V20	\$21.15

	Mirage^{®1} Quick Response Extended Coverage Glass Bulb Concealed Pendent			
	SIN: VK634 K Factor: 8.0 (115) Thread Size: 3/4 inch NPT Base Part #: 14535A			
Finish	Temp	Part #	IPG	List Price
Standard Brass	135°F	14535AA	V16.4	\$56.57
Standard Brass	155°F	14535AB	V16.4	\$56.57
Standard Brass	175°F	14535AD	V16.4	\$56.57
Standard Brass	200°F	14535AE	V16.4	\$56.57
Heavy Duty Spk Wrench		14047W/B	V20	\$103.21
Cabinet Wrench/Cap Tool		14031	V20	\$21.15

	ELO Mirage^{®1} Quick Response Extended Coverage Fusible Link Concealed Pendent			
	SIN: VK636 K Factor: 11.2 (161) Thread Size: 3/4 inch NPT Base Part #: 16102A			
Finish	Temp	Part #	IPG	List Price
Standard Brass	165°F	16102AC	V16.4A	\$62.24
Standard Brass	205°F	16102AE	V16.4A	\$62.24
Heavy Duty Spk Wrench		15467W/B	V20	\$103.21
Cabinet Wrench/Cap Tool		15466	V20	\$21.15

(1) Cover plates sold separately. See following page for details.