

Phone: 708-202-0033 / sales@cbmarketing.com

Legend 13D Selection Chart

		Flow (0	SPM)		To see curve, select and click							
		20	25	30	35	40	45	50	55	60	65	70
PSI	25	13D-70/17 3⁄4 hp	13D-70/17 3⁄4 hp	13D-70/310 1 hp	13D-70/310 1 hp	13D-120/315 1.5 hp	13D-120/315 1.5 hp	13D-120/315 1.5 hp	13D-120/315 1.5 hp	13D-200/320 2 hp	13D-200/320 2 hp	13D-200/320 2 hp
	30	13D-70/310 1 hp	13D-70/310 1 hp	13D-70/310 1 hp	13D-70/310 1 hp	13D-120/315 1.5 hp	13D-120/315 1.5 hp	13D-120/315 1.5 hp	13D-200/320 2 hp	13D-200/320 2 hp	13D-200/320 2 hp	13D-200/320 2 hp
	35	13D-70/310 1 hp	13D-70/310 1 hp	13D-70/310 1 hp	13D-120/315 1.5 hp	13D-120/315 1.5 hp	13D-200/320 2 hp	13D-200/320 2 hp	13D-200/320 2 hp	13D-200/320 2 hp	13D-200/530 3 hp	13D-200/530 3 hp
	40	13D-70/310 1 hp	13D-70/515 1.5 hp	13D-70/515 1.5 hp	13D-200/320 2 hp	13D-200/320 2 hp	13D-200/320 2 hp	13D-120/530 3 hp	13D-200/530 3 hp	13D-200/530 3 hp	13D-200/530 3 hp	13D-200/530 3 hp
	45	13D-70/515 1.5 hp	13D-70/515 1.5 hp	13D-120/530 3 hp	13D-120/530 3 hp	13D-120/530 3 hp	13D-120/530 3 hp	13D-120/530 3 hp	13D-200/530 3 hp	13D-200/530 3 hp	13D-200/530 3 hp	13D-200/530 3 hp
	50	13D-70/515 1.5 hp	13D-70/515 1.5 hp	13D-120/530 3 hp	13D-120/530 3 hp	13D-120/530 3 hp	13D-120/530 3 hp	13D-200/530 3 hp	13D-3U-32- 160B 5 hp	13D-3U-32- 160B 5 hp	13D-3U-32- 160B 5 hp	13D-3U-32- 160B 5 hp
	55	13D-2-70/206 2 hp	13D-120/530 3 hp	13D-120/530 3 hp	13D-120/530 3 hp	13D-2-120/306 3 hp	13D-2-120/306 3 hp	13D-2-120/306 3 hp	13D-3U-32- 160B 5 hp	13D-3U-32- 160B 5 hp	13D-3U-32- 160B 5 hp	13D-3U-32- 160B 5 hp
	60	13D-2-70/206 2 hp	13D-2-70/206 2 hp	13D-2-120/306 3 hp	13D-2-120/306 3 hp	13D-2-120/306 3 hp	13D-2-120/306 3 hp	13D-3U-32- 160B 5 hp	13D-3U-32- 160B 5 hp	13D-3U-32- 160B 5 hp	13D-3U-32- 160B 5 hp	13D-3U-32- 160B 5 hp
	65	13D-2-70/206 2 hp	13D-2-70/206 2 hp	13D-2-120/306 3 hp	13D-2-120/306 3 hp	13D-2-120/306 3 hp	13D-3U-32- 160B 5 hp	13D-3U-32- 160B 5 hp	13D-3U-32- 160B 5 hp	13D-3U-32- 160B 5 hp	13D-3U-32- 160B 5 hp	13D-3U-32- 160B 5 hp
	70	13D-2-70/206 2 hp	13D-2-120/306 3 hp	13D-2-120/306 3 hp	13D-2-120/306 3 hp	13D-3U-32- 160B 5 hp	13D-3U-32- 160B 5 hp	13D-3U-32- 160B 5 hp	13D-3U-32- 160B 5 hp	13D-3U-32-200 7.5 hp	13D-3U-32-200 7.5 hp	13D-3U-32-200 7.5 hp
	75	13D-2-70/306 3 hp	13D-2-120/306 3 hp	13D-2-120/306 3 hp	13D-3U-32- 160B 5 hp	13D-3U-32- 200 7.5 hp	13D-3U-32-200 7.5 hp	13D-3U-32-200 7.5 hp	13D-3U-32-200 7.5 hp	13D-3U-32-200 7.5 hp	13D-3U-32-200 7.5 hp	13D-3U-32-200 7.5 hp

Note: standard pressure switch range is 5 - 80 psi. Call for different range.

Subject to change without notice.

Additional sizes are available, as well as custom designs to meet your needs