



TABLE OF CONTENTS

Institutional – VK426/VK427, VK650/VK651 5.6 (81) K factor, flush pendent/flush horizontal sidewall...E-1
 Model V-BB specific application attic sprinkler - VK684, VK685, VK686, VK681, VK682, VK683E-2
 Model V-SD specific application attic sprinkler - VK693, VK694, VK695E-2
 Attic upright specific application sprinkler – VK696, VK697.....E-2
 Model V-HIP specific application attic sprinkler – VK660E-2
 Combustible Interstitial Space - VK900, VK950, COIN®, uprightE-3
 Window Sprinklers – VK960, VK962 pendent vertical sidewall and horizontal sidewall.....E-3

Notes

1. Unless otherwise indicated, all cover plates and escutcheons are sold separately.
2. Cover plates, escutcheons, and sprinklers are available in custom colors at an additional charge. See page F-8 for details.
3. Refer to Viking technical data pages for complete product specifications. You may print or download technical data by visiting www.vikinggroupinc.com.
4. List prices effective January 20, 2020. Supersedes January 2019 list price book.
5. All sales by Viking are subject to the Terms & Conditions found on the last page of this book.

COIN® is a registered trademark of The Viking Corporation
Micromatic® is a registered trademark of The Viking Corporation



Institutional
Quick Response
Standard Coverage
Fusible Link
Flush Pendent

SIN: VK426
K Factor: 5.6 (81)
Thread Size: 1/2 inch NPT
Base Part #: 19663

Finish	Temp	Part #	IPG	List Price
Polished Chrome	165°F	19663FC	V173	\$98.93
Polished Chrome	205°F	19663FE	V173	\$98.93
Painted White	165°F	19663MC/W	V173	\$98.93
Painted White	205°F	19663ME/W	V173	\$98.93
Painted Gray	165°F	19663MC/RAL9006	V173	\$98.93
Painted Gray	205°F	19663ME/RAL9006	V173	\$98.93
Socket Wrench		22847MB	V207	\$250.27



Institutional
Quick Response
Standard Coverage
Fusible Link
Flush Horizontal Sidewall

SIN: VK427
K Factor: 5.6 (81)
Thread Size: 1/2 inch NPT
Base Part #: 22885

Finish	Temp	Part #	IPG	List Price
Polished Chrome	165°F	22885FC	V173	\$114.15
Polished Chrome	205°F	22885FE	V173	\$114.15
Painted White	165°F	22885MC/W	V173	\$114.15
Painted White	205°F	22885ME/W	V173	\$114.15
Painted Gray	165°F	22885MC/RAL9006	V173	\$114.15
Painted Gray	205°F	22885ME/RAL9006	V173	\$114.15
Socket Wrench		22847MB	V207	\$250.27



Institutional
Quick Response
Extended Coverage
Fusible Link
Flush Pendent

SIN: VK650
K Factor: 5.6 (81)
Thread Size: 1/2 inch NPT
Base Part #: 19876

Finish	Temp	Part #	IPG	List Price
Polished Chrome	165°F	19876FC	V173	\$106.54
Polished Chrome	205°F	19876FE	V173	\$106.54
Painted White	165°F	19876MC/W	V173	\$106.54
Painted White	205°F	19876ME/W	V173	\$106.54
Painted Gray	165°F	19876MC/RAL9006	V173	\$106.54
Painted Gray	205°F	19876ME/RAL9006	V173	\$106.54
Socket Wrench		22847MB	V207	\$250.27



Institutional
Quick Response
Extended Coverage
Fusible Link
Flush Horizontal Sidewall

SIN: VK651
K Factor: 5.6 (81)
Thread Size: 1/2 inch NPT
Base Part #: 22884

Finish	Temp	Part #	IPG	List Price
Polished Chrome	165°F	22884FC	V173	\$121.76
Polished Chrome	205°F	22884FE	V173	\$121.76
Painted White	165°F	22884MC/W	V173	\$121.76
Painted White	205°F	22884ME/W	V173	\$121.76
Painted Gray	165°F	22884MC/RAL9006	V173	\$121.76
Painted Gray	205°F	22884ME/RAL9006	V173	\$121.76
Socket Wrench		22847MB	V207	\$250.27



Institutional
Escutcheon

Finish	Part #	IPG	List Price
Polished Chrome	3" 23196F	V173	\$11.42
Painted White	3" 23196M/W	V173	\$11.42
Painted Gray	3" 23196M/RAL9006	V173	\$21.56
Polished Chrome	4" 23197F	V173	\$15.22
Painted White	4" 23197M/W	V173	\$15.22
Painted Gray	4" 23197M/RAL9006	V173	\$24.10



Institutional
Optional Retaining Flange and Screw Assembly¹

Finish	Part #	IPG	List Price
Polished Chrome	10599	V173	\$45.65

(1) Set screw requires a 1/8" allen wrench not available from Viking.

Specific Application Attic Sprinklers ¹



Back-to-Back (Model V-BB) Attic Sprinkler, Specific Application, Glass Bulb, ½ and ¾ inch NPT

K Factor	Roof Pitch	SIN	Part #	Temp	Finish ¹	IPG	List Price
5.6 (81)	4:12 < 7:12	VK684	19627AE	200°F	Standard Brass	V174	\$ 392.96
5.6 (81)	7:12 < 10:12	VK685	19801AE	200°F	Standard Brass	V174	\$ 392.96
5.6 (81)	10:12 ≤ 12:12	VK686	19754AE	200°F	Standard Brass	V174	\$ 392.96
8.0 (115)	4:12 < 7:12	VK681	19626AE	200°F	Standard Brass	V174	\$ 458.68
8.0 (115)	7:12 < 10:12	VK682	19798AE	200°F	Standard Brass	V174	\$ 458.68
8.0 (115)	10:12 ≤ 12:12	VK683	19751AE	200°F	Standard Brass	V174	\$ 458.68



Single Directional (Model V-SD) Attic Sprinkler, Specific Application, Glass Bulb, ½ inch NPT

K Factor	Roof Pitch	SIN	Part #	Temp	Finish ¹	IPG	List Price
5.6 (81)	4:12 < 7:12	VK693	19578AE	200°F	Standard Brass	V174	\$ 392.96
5.6 (81)	7:12 < 10:12	VK694	19799AE	200°F	Standard Brass	V174	\$ 392.96
5.6 (81)	10:12 ≤ 12:12	VK695	19759AE	200°F	Standard Brass	V174	\$ 392.96



Attic Upright Sprinkler, Specific Application, Glass Bulb, ½ inch NPT

K Factor	Roof Pitch	SIN	Part #	Temp	Finish ¹	IPG	List Price
4.2 (57)	4:12 to 12:12	VK696	19538AE	200°F	Standard Brass	V175	\$ 57.49
5.6 (81)	4:12 to 12:12	VK697	21716AE	200°F	Standard Brass	V175	\$ 65.67



Attic HIP (Model V-HIP), Specific Application, Glass Bulb, ½ inch NPT

K Factor	Roof Pitch	SIN	Part #	Temp	Finish ¹	IPG	List Price
5.6 (81)	4:12 to 12:12	VK660	20952AE	200°F	Standard Brass	V174	\$ 392.96

Installation Wrench	Part #	IPG	List Price
Standard Wrench	21475M/B	V207	\$ 77.63

(1) Also available with Electroless Nickel PTFE (ENT) plating for corrosion resistance (special order with extended lead time).
Please contact customer service for price and availability.



COIN®
Quick Response
COmbustible INterstitial
Glass Bulb
Upright (Specific Application)
SIN: VK900
K Factor: 4.2 (60)
Thread Size: 1/2 inch NPT
Base Part #: 12493

Finish	Temp	Part #	IPG	List Price
Standard Brass	175°F	12493AD	V172	\$72.09
FUSIBLE LINK - VK901 (4.2 (60) K Factor)				
Standard Brass	205°F	12676AE	V172	\$80.09
Std Sprinkler Wrench		21475M/B	V207	\$77.63



COIN®
Quick Response
COmbustible INterstitial
Glass Bulb
Upright (Specific Application)
SIN: VK950
K Factor: 5.6 (80)
Thread Size: 1/2 inch NPT
Base Part #: 20757

Finish	Temp	Part #	IPG	List Price
Standard Brass	200°F	20757AE	V172	\$88.30
Std Sprinkler Wrench		21475M/B	V207	\$77.63



Window Sprinkler
Quick Response
Glass Bulb
Pendant Vertical Sidewall
(Specific Application)
SIN: VK960
K Factor: 5.6 (81)
Thread Size: 1/2 inch NPT
Base Part #: 23017

Finish	Temp	Part #	IPG	List Price
Standard Brass	155°F	23017AB	V193	\$461.00
Standard Brass	200°F	23017AE	V193	\$461.00
Polished Chrome	155°F	23017FB	V193	\$479.44
Polished Chrome	200°F	23017FE	V193	\$479.44
White-Polyester	155°F	23017MB/W	V193	\$479.44
White-Polyester	200°F	23017ME/W	V193	\$479.44
Black-Polyester	155°F	23017MB/B	V193	\$479.44
Black-Polyester	200°F	23017ME/B	V193	\$479.44
Nickel PTFE (ENT)	155°F	23017JNB	V193	\$534.76
Nickel PTFE (ENT)	200°F	23017JNE	V193	\$534.76
Std Sprinkler Wrench		22940MB	V207	\$77.63



Window Sprinkler
Quick Response
Glass Bulb
Horizontal Sidewall
(Specific Application)
SIN: VK962
K Factor: 5.6 (81)
Thread Size: 1/2 inch NPT
Base Part #: 23019

Finish	Temp	Part #	IPG	List Price
Standard Brass	155°F	23019AB	V193	\$461.00
Standard Brass	200°F	23019AE	V193	\$461.00
Polished Chrome	155°F	23019FB	V193	\$479.44
Polished Chrome	200°F	23019FE	V193	\$479.44
White-Polyester	155°F	23019MB/W	V193	\$479.44
White-Polyester	200°F	23019ME/W	V193	\$479.44
Black-Polyester	155°F	23019MB/B	V193	\$479.44
Black-Polyester	200°F	23019ME/B	V193	\$479.44
Nickel PTFE (ENT)	155°F	23019JNB	V193	\$534.76
Nickel PTFE (ENT)	200°F	23019JNE	V193	\$534.76
Std Sprinkler Wrench		22940MB	V207	\$77.63