



Dry Sprinkler | VK482 Recessed Concealed Dry Pendent Sprinkler

Viking's new Model VK482 quick response dry pendent sprinkler is an ideal solution for unheated areas with finished ceilings such as vestibules, stadiums, porte-cochères, overhangs, and parking garages. The Model VK482 has a 5.6(81) K-factor, is cULus Listed for both Light and Ordinary Hazard occupancies, and is an aesthetically pleasing option for concealed dry sprinkler applications.

- The optional insulating boot assembly can be used to satisfy NFPA 13 requirements for sealing around the barrel of a sprinkler when protecting areas below 40°F with a wet pipe system.
- When installed with the insulating boot assembly, the VK482 meets Quick Response sprinkler requirements.
- Available in 165°F (74°C) and 205°F (96°C) temperature ratings.
- Includes an innovative escutcheon that hangs from the sprinkler body to help prevent separation due to equipment vibration or foot traffic above the ceiling.
- Custom painted finishes are available with extended lead time.
- Barrel lengths available from 4-1/2" to 48" (114mm to 1,219mm).

Contact your local Viking SupplyNet office for pricing today!

Model Number: VK482

Base Part Number: 18385M(t)/W(L)
 t = desired temperature
 L = length in inches

Listings/Approvals: cULus

K Factor: 5.6 (81)

Connection: Threaded 1" NPT
25mm BSP

Temperature: 165°F (74°C)
205°F (96°C)

Operating Element: Fusible Link

Finish: White Polyester

Item Price Group: V19.2 Dry Flush Sprinklers

Occupancy/Hazard: Light and Ordinary

Technical Datasheet: 111a-g

Scan to view
technical datasheet



Viking Corporation

210 N Industrial Park Drive, Hastings, Michigan 49058

Telephone: (800) 968-9501

Email: products@vikingcorp.com

www.vikinggroupinc.com

Trusted above all.™

