

# Valves and Systems

4" Model G-4000 Dry System



## Introducing a revolutionary dry pipe system – From the most trusted name in fire protection.

### Innovative

Viking's new Model G-4000 dry valve includes an innovative external reset feature. To reset the valve, simply re-establish air pressure to the system and pressurize the valve's unique priming chamber. In a fire condition, air pressure is lost and the priming chamber compresses allowing water to pass through the valve and into the sprinkler system piping.

### Simple

The G-4000 is offered completely pre-assembled including the water supply control valve, air supervisory switch, and alarm pressure switch. Additionally, the pre-trimmed dry valve weighs less and has a smaller footprint than competitors' products. With less than eight inches between the center of the dry valve and the back of the trim, the new G-4000 can be installed in even the tightest spaces.

### Trusted

For over 80 years, Viking has led the industry in the design and manufacture of the finest fire protection products. The new G-4000's innovative design and ease of installation further enhances Viking's reputation as the most trusted name in fire protection.

| Part Number  | 15647-1 |
|--|---------|
| <b>Complete, pre-assembled dry valve and trim. Includes the following:</b> |         |
| - Model G-4000 Dry Valve   |         |
| - Model G-4000 Trim Package  |         |
| - Water Supply Control Valve   |         |
| - Air Pressure Supervisory Switch (PS40-2A)                                |         |
| - Alarm Pressure Switch (PS10-1A)  |         |
| - Connection Tee – Drain Manifold  |         |
| - 12 inch (0,3 m) Section of Galvanized Schedule 10 Pipe (with Coupling)   |         |

*G-4000 system also offered in basic valve and trim package (does not include control valve, switches, and pipe section).*

*\* See technical data sheet "Dry 119a-I" for complete product specifications.*



Contact your local Viking SupplyNet location or visit our online sourcing tool, VSN eSource, to order! [www.vikinggroupinc.com](http://www.vikinggroupinc.com)

**Trusted above all.™**

**VIKING®**