



Protect combustible concealed spaces without draft curtains

The enhanced cULus Listing for the 5.6 (80) k-factor Quick Response COIN® sprinkler allows the sprinkler to protect combustible concealed spaces without the use of draft curtains in most applications! This makes it an ideal replacement for competitive sprinklers that have more stringent and expensive draft curtain requirements.

Features and advantages of Viking's VK950 COIN® sprinkler:

No draft curtains required when:

- *Sprinkler spacing is up to 16 x 16 ft (4,9 x 4,9 m) for truss construction with top chord member on face (not edge) for wet or dry systems*
- *Sprinkler spacing is up to 14 x 14 ft (4,3 x 4,3 m) for truss construction with top chord member on edge or solid wood joists for wet systems*
- For use in concealed spaces up to 60" in height and roof pitches up to 2/12
- Remote area design calculation of 1,000 square feet or six sprinklers, whichever is greater
- Listed for use with Viking BlazeMaster® CPVC
- Available with a corrosion resistant Electroless Nickel PTFE (ENT) coating

For more information, please contact your Viking sales representative or visit our website at vikinggroupinc.com.

TECHNICAL SPECIFICATIONS

Model Number:	VK950
Base Part Number:	20757
Listings/Approvals:	cULus Listed
K-factor:	K5.6 (80)
Connection:	1/2" NPT 15 mm BSP
Temperatures:	200°F (93°C)
Operating Element:	Glass Bulb
Finish:	Brass Electroless Nickel PTFE (ENT)
Item Price Group:	V172
Occupancy/Hazard:	Special
Technical Datasheet:	F_081216

DIGITAL TOOLS



Viking's revolutionary Sprinkler Selector ensures that you can find the right sprinkler for the job — every time. Get started by visiting webtools.vikingcorp.com/sprinklerselector.

MKT-0014

