

Residential — VK471 K3.7 Residential Pendant



cULus Listed K3.7 sprinkler rounds out lineup of residential offerings

The cULus Listed VK471 K3.7 Residential Pendant Sprinkler addresses significant challenges where water supply concerns are an issue with its flow rates optimizing at the 14 x 14 ft. coverage area. With the addition of the VK471, Viking now offers a substantially large breadth of K-factors in its residential lineup!

Features and advantages of the VK471 K3.7 sprinkler:

- Completes the residential pendant sprinkler offering as its seventh K-factor, and the market's only 3.7K residential pendant sprinkler
- cULus listed for residential applications
- Optimized at the 14 x 14 ft. coverage area, making it ideal for applications where water supply concerns exist
- Available in an Electroless Nickel PTFE (ENT) corrosion resistant coating for areas where corrosion is a concern
- Also available in brass, chrome, and white or black polyester

For more information, please contact your Viking sales representative or visit our website at vikinggroupinc.com.

TECHNICAL SPECIFICATIONS

Model Number:	VK471
Base Part Number:	25642
Listings/Approvals:	cULus Listed
K-factor:	K3.7 (53)
Connection:	1/2" NPT
Temperatures:	155°F (68°C) 200°F (93°C)
Operating Element:	Glass Bulb
Finish:	Brass, Chrome, White Polyester, Black Polyester, Electroless Nickel PTFE (ENT)
Item Price Group:	V176
Occupancy/Hazard:	Residential
Technical Datasheet:	F_060624

DIGITAL TOOLS



Viking's revolutionary Sprinkler Selector ensures that you can find the right sprinkler for the job — every time. Get started by visiting webtools.vikingcorp.com/sprinklerselector.



General reference only. Prior to the design, layout, and/or installation of any sprinkler system, please refer to Viking's technical documentation and consult with the AHJ.

MKT-0021