



Concealed 5.6K pendent sprinkler offers easy install

The FM Approved and cULus Listed VK4621 Quick and Standard Response concealed pendent sprinkler is a 5.6K commercial sprinkler protecting Light and Ordinary hazards, utilizing a glass bulb operating element.

Features and advantages of Viking's VK4621 Concealed Pendent Sprinkler:

- Features compatible heavy-duty and light-duty wrenches for easy installation
- Protective cap is designed to withstand rough usage and protect the sprinkler from paint overspray
- cULus Listed as a Quick Response sprinkler and FM Approved as a Standard Response sprinkler for both light and ordinary occupancies
- The sprinkler consists of a permanently mounted and threaded adapter cup designed to be installed with a low-profile cover assembly that provides up to 1/2" (13 mm) of vertical adjustment
- Available in both brass and an Electroless Nickel PTFE (ENT) coating for environments in which corrosion is more likely to occur

For more information, please contact your Viking sales representative or visit our website at vikinggroupinc.com.

TECHNICAL SPECIFICATIONS

Model Number:	VK4621
Base Part Number:	24682
Listings/Approvals:	FM Approved cULus Listed
K-factor:	K5.6 (80.6)
Connection:	1/2" NPT 15 mm BSPT
Temperatures:	155°F (68°C) 175°F (79°C) 200°F (93°C)
Operating Element:	Glass Bulb
Finish:	Brass, ENT Coated
Item Price Group:	V129
Occupancy/Hazard:	Light & Ordinary
Technical Datasheet:	F_092121
Installation Wrench:	23143, 22978M/B

DIGITAL TOOLS



Viking's revolutionary Sprinkler Selector ensures that you can find the right sprinkler for the job — every time. Get started by visiting webtools.vikingcorp.com/sprinklerselector.

VKG-1000

