

# FM Approved Synthetic Fluorine Free Foam



## Environmental responsibility meets industry-leading protection capabilities

The industry's first FM Approved Synthetic Fluorine Free fixed foam system for Hydrocarbon and Polar Solvent applications is available at Viking. The system approval includes non- aspirated sprinkler discharge devices for use in closed or open sprinkler configurations such as warehouses, chemical manufacturing areas, loading racks, aircraft hangars and more.

In addition to 5.6, 8.0 and 11.2 K-factor upright and pendent sprinklers, there is SFFF foam concentrate, 6" and 8" Model VNR Wide Range Proportioners, and Model VFT Bladder Tanks as a part of a complete foam system package.



### Viking's New LoEx Estimator Now Available

Easily calculate your FM Approved SFFF low expansion foam systems with the LoEX Estimator, the latest in a line of exclusive digital tools from Viking! Scan the QR code or visit [webtools.vikingcorp.com/fff](http://webtools.vikingcorp.com/fff).

