

1. DESCRIPTION

The pressure reducer is part of the listed/approved system Oxeo PR, CF. It reduces the pressure in the occupiable space protection kit to allow activation of the pneumatic horn (Makrofon). The pressure reducer includes a pressure gauge to allow visual inspection of the outgoing pressure.

2. LISTINGS AND APPROVALS



cULus Listed: EX5248 (Oxeo PR, CF)



FM Approved: (Oxeo PR, CF)

3. TECHNICAL DATA

Part number: 888050

Specifications

Operating medium (gaseous): Argon (IG-01), Nitrogen (IG-100)

Inlet pressure: Maximum 2900 PSI (200 bar)

Outlet pressure: 362.6 PSI (25 bar) permanently adjusted, secured with hexagon nut, and sealed with wire

Temperature range: -4 °F to 122 °F (-20 °C to +50 °C)

Connection thread G1/4: in accordance with ISO 228

Material standards:

Housing: brass

Membrane: SBR

Dimensions

