



Pressure Gauge

GAU

Technical Features

- Connections : $\frac{3}{8}$ " BSP male threaded.
- Specifications : complies to BS1780 and IP65.

Note : Can be supplied with company name on gauge face, subject to minimum order.



Gauges

Pressure Gauge - GAU

Physical Data

Pressure Range (bar)		Internal	Dimension A (mm/inch)	Reference
min	max			
0.0	16.0	Dry	102 / 4.0	GAU022DRY0-16
0.0	16.0	Glycerine	102 / 4.0	GAU022GLY0-16
0.0	10.0	Dry	102 / 4.0	GAU022DRY0-10
0.0	10.0	Glycerine	102 / 4.0	GAU022GLY0-10
-1.0	1.0	Glycerine	102 / 4.0	GAU022GLY-1+1

No Loss Connector : Order separately - Reference: GAU022NLC

Pressure Gauge - GAU

Materials List

Item	Part	Material
1	Pointer	Black Enamelled Aluminium
2	Window	Polycarbonate
3*	Bourdon Tube	Copper Alloy
4*	Movement	Brass
5	Dial	Black Lettering on White Background
6	Connection	Brass
7	Casing	Stainless Steel

* Not visible

