
NKING[®] TECHNICAL DATA

PNEUMATIC RELEASE MODULE TRIM CHART

Maximum 250 psi Water Working Pressure

The Viking Corporation, 210 N Industrial Park Drive, Hastings MI 49058 Telephone: 269-945-9501 | Technical Services: 877-384-5464 | Fax: 269-818-1680 | Email: techsvcs@vikingcorp.com Visit the Viking website for the latest edition of this technical data page www.vikinggroupinc.com

Available since 1999.



For Use on	For Use on	For Use on	For Use on
Standard	Galvanized	Brass*	Stainless
Trim	Trim	Trim	Steel Trim
10809	10809USA	10811	10810

NOTE: Order pneumatic actuator separately. Pneumatic Release Module is used with the Viking Model H-1 (part no. 06459B) and R-1 (part no. 09733) pneumatic actuator.

The Viking Pneumatic Release Module is only for Viking deluge and flow control valves. Verify that the control valves use conventional trim and that the trim is installed in accordance with the valve's current conventional trim chart. Install the Electric Release Module by using the provided connections and Figure 1 (left).

*Where brass and stainless steel trim are recommended, refer to Viking Corp's website for a description on the Halar[®] Coated Deluge Valve and associated trim diagrams.



WARNING: Cancer and Reproductive Harmwww.P65Warnings.ca.gov

ORDER DELUGE VALVE, TRIM, PNEUMATIC ACTUATOR, AND RELEASE MODULE TRIM SEPARATELY.

FIGURE 1: PNEUMATIC RELEASE MODULE