

## Sprinkler Identification Number (SIN) Directory



210 N. Industrial Park Drive Hastings, MI 49058 U.S.A. Telephone: (269) 945-9501 | Technical Services: (877) 384-5464 | Fax: (269) 818-1680 | E-mail: techsvcs@vikingcorp.com

SIN*	Technical Data Page(s)	Sprinkler Base Part Number	Nominal K-Factor		Sprinkler Model and Type	Maximum Pressure Rating (UL/FM)
			U.S.	metric		
<b>ITEMS WITH THIS COLOR ARE DISCONTINUED PRODUCTS</b>						
VK1001	F_020316	19914 19926	5.6	80.6	K5.6 SR UP & HP, 1/2", 5.6K	250/175
VK1021	F_020416	19915 19927	5.6	80.6	K5.6 SR PD & HP, 1/2", 5.6K	250/175
VK3001	F_020516	19916 19928	5.6	80.6	K5.6 QR UP & HP, 1/2", 5.6K	175
VK3021	F_020616	19917 19929	5.6	80.6	K5.6 QR PD & HP, 1/2", 5.6K	175
VK2001	F_020716	19922 19934	8.0	115.2	K8.0 SR UP, 8K, 3/4"	175
VK2002	F_020816	19918 19930	8.0	115.2	K8.0 SR UP, 8K, 1/2"	175
VK2021	F_020916	19923 19935	8.0	115.2	K8.0 SR PD, 8K, 3/4"	175
VK2022	F_021016	19919 19931	8.0	115.2	K8.0 SR PD, 8K, 1/2"	175
VK3501	F_021117	19924 19936	8.0	115.2	K8.0 QR UP, 8K, 3/4"	175
VK3502	F_021216	19920 19932	8.0	115.2	K8.0 QR UP, 8K, 1/2"	175
VK3521	F_021316	19925 19937	8.0	115.2	K8.0 QR PD, 8K, 3/4"	175
VK3522	F_021416	19921 19933	8.0	115.2	K8.0 QR PD, 8K, 1/2"	175
VK001	F_052814	10192 13007	2.8	40.3	Standard Response Upright, Small Orifice, 15 mm BSP (discontinued product)	175 psi
VK001	F_052814	10218 13006	2.8	40.3	Standard Response Upright, Small Orifice, 1/2" NPT (discontinued product)	175 psi
VK002	N/A	10176	4.2	57	Standard Response Upright, Small Orifice, 10 mm BSP (discontinued product)	175 psi
VK002	F_081314	10191	4.2	57	Standard Response Upright, Small Orifice, 15 mm BSP (discontinued product)	175 psi
VK002	F_081314	10219	4.2	57	Standard Response Upright, Small Orifice, 1/2" NPT (discontinued product)	175 psi
VK003	F_052914	10189 12992	2.8	40.3	Standard Response Pendent, Small Orifice, 15 mm BSP (discontinued product)	175 psi
VK003	F_052914	10221 12994	2.8	40.3	Standard Response Pendent, Small Orifice, 1/2" NPT (discontinued product)	175 psi
VK004	N/A	10175	4.2	57	Standard Response Pendent, Small Orifice, 10 mm BSP (discontinued product)	175 psi
VK004	N/A	10188	4.2	57	SR Pendent, Small Orifice, 15 mm BSP (discontinued product)	175 psi
VK004	F_081614	10222	4.2	57	Standard Response Pendent, Small Orifice, 1/2" NPT (discontinued product)	175 psi
VK005	N/A	05569	2.8	40.3	SR Fusible Link Upright, Small Orifice, 1/2" NPT (discontinued product)	175 psi
VK005	N/A	12975	2.8	40.3	SR Fusible Link Upright, Small Orifice, 1/2" NPT (discontinued product)	175 psi
VK006	N/A	05510	4.2	57	Standard Response Fusible Link Upright, Small Orifice, 10 mm BSP (discontinued product)	175 psi
VK006	F_082214	05574	4.2	57	Standard Response Fusible Link Upright, Small Orifice, 1/2" NPT (discontinued product)	175 psi
VK007	N/A	05570	2.8	40.3	SR Fusible Link Pendent, Small Orifice, 1/4" NPT (discontinued product)	175 psi
VK007	N/A	12976	2.8	40.3	SR Fusible Link Pdt, Small Orifice, 1/2" NPT (discontinued product)	175 psi
VK008	N/A	05512	4.2	57	Standard Response Fusible Link Pendent, Small Orifice, 10 mm BSP (discontinued product)	175 psi
VK008	F_082314	05575	4.2	57	Standard Response Fusible Link Pendent, Small Orifice, 1/2" NPT (discontinued product)	175 psi
VK015	F_082114	09997	2.8	40.3	HP Standard Response Horizontal Sidewall, Small Orifice, 1/2" NPT (discontinued product)	250 psi
VK016	N/A	09126	4.2	57	Standard Response Horizontal Sidewall, Small Orifice, 10 mm BSP (discontinued)	175 psi
VK018	N/A	09127	4.2	57	Standard Response Vertical Sidewall, Small Orifice, 10 mm BSP (discontinued)	175 psi
VK021	F_081514	09995	2.8	40.3	HP Standard Response HP Upright, Small Orifice, 1/2" NPT (discontinued product)	250 psi
VK023	F_081814	09994	2.8	40.3	HP Standard Response HP Pendent, Small Orifice, 1/2" NPT (discontinued product)	250 psi
VK030	N/A	09284	4.2	57	Special Response Upright, Small Orifice, 10 mm BSP (discontinued product)	175 psi
VK032	N/A	09285	4.2	57	Special Response Pendent, Small Orifice, 10 mm BSP (discontinued product)	175 psi
VK100	F_052014	10138 12986	5.6	80.6	Standard Response Upright, 1/2" NPT	175 psi
VK100	F_052014	10193 12993	5.6	80.6	Standard Response Upright, 15 mm BSP	175 psi
VK102	F_031414	10139 12987	5.6	80.6	Standard Response Pendent, 1/2" NPT	175 psi
VK102	F_031414	10173 12989	5.6	80.6	Standard Response Pendent, 1/2" NPT	175 psi
VK102-D	F_101912	10139A-X	5.6	80.6	Standard Response Domed Concealed Pendent, 1/2" NPT (discontinued product)	175 psi
VK104	F_033514	10171 12988 20230	5.6	80.6	Standard Response Horizontal Sidewall, 15 mm BSP	175 psi

SIN*	Technical Data Page(s)	Sprinkler Base Part Number	Nominal K-Factor		Sprinkler Model and Type	Maximum Pressure Rating (UL/FM)
			U.S.	metric		
VK104	F_033514	10224 12995 19777	5.6	80.6	Standard Response Horizontal Sidewall, ½" NPT	175 psi
VK106	F_052414	10186 12991	5.6	80.6	Standard Response Vertical Sidewall, 15 mm BSP	175 psi
VK106	F_052414	10226 12996 17496	5.6	80.6	Standard Response Vertical Sidewall, ½" NPT	175 psi
VK108	F_052214	05506 12971	5.6	80.6	Standard Response Fusible Element Upright, 15 mm BSP	175 psi
VK108	F_052214	05557 12973	5.6	80.6	Standard Response Fusible Element Upright, ½" NPT	175 psi
VK110	F_052314	05508 12972	5.6	80.6	Standard Response Fusible Element Pendant, ½" NPT	175 psi
VK112	F_060404	05559 12974	5.6	80.6	Standard Response Fusible Element Horizontal Sidewall, ½" NPT	175 psi
VK114	N/A	06347 and 12977	5.6	80.6	Standard Response Fusible Element Vertical Sidewall, ½" NPT (discontinued product)	175 psi
VK116	F_082014	09849	5.6	80.6	HP Standard Response -5 HSW, ½" NPT	250 psi
VK118	F_022414	10172 19384	5.6	80.6	Standard Response Conventional, 15 mm BSP	175 psi
VK118	F_022414	10227 19383	5.6	80.6	Standard Response Conventional, ½" NPT	175 psi
VK120	F_032914	10168 18265	8.0	115.2	Standard Response Conventional, 20 mm BSP	175 psi
VK120	F_032914	10228 18270	8.0	115.2	Standard Response Conventional, 3/4" NPT	175 psi
VK120	N/A	12106	8.0	115.2	Standard Response Conv., 3/4" NPT (discontinued product)	175 psi
VK122	F_081714	09992	5.6	80.6	HP Standard Response HP Pendant, ½" NPT	250 psi
VK124	F_081414	09993	5.6	80.6	HP Standard Response HP Upright, ½" NPT	250 psi
VK130	F_060691	05012B	5.6	80.6	Standard Response Model N-2 Stainless Steel Upright, ½" NPT	175 psi
VK130	F_060691	06501BZ	5.6	80.6	Standard Response Open Model N-2 Stainless Steel Upright, ½" NPT	175 psi
VK132	F_060691	06483B	5.6	80.6	Standard Response Model N-2 Stainless Steel Pendant, ½" NPT	175 psi
VK132	F_060691	06502BZ	5.6	80.6	Standard Response Open Model N-2 Stainless Steel Pendant, ½" NPT	175 psi
VK134	N/A	09224	5.6	80.6	Special Response Pendant, ½" NPT (discontinued product)	175 psi
VK134	N/A	09956	5.6	80.6	Special Response Pendant, 15 mm BSP (discontinued product)	175 psi
VK136	N/A	09225	5.6	80.6	Special Response Conventional, ½" NPT (discontinued product)	175 psi
VK136	N/A	09958	5.6	80.6	Special Response Conventional, 15 mm BSP (discontinued product)	175 psi
VK138	N/A	09226	5.6	80.6	Special Response Upright, ½" NPT (discontinued product)	175 psi
VK138	N/A	09959	5.6	80.6	Special Response Upright, 15 mm BSP (discontinued product)	175 psi
VK145	F_032714	10174 12990 20228	5.6	80.6	Standard Response Upright, 15 mm BSP	175 psi
VK145	F_032714	10233 13001 19778	5.6	80.6	Standard Response Upright, ½" NPT	175 psi
VK150	F_071591	07852U	5.6	80.6	Standard Response Plain Barrel Dry Pendant, 1" NPT	175 psi
VK150	F_071591	07855U	5.6	80.6	Standard Response Plain Barrel Dry Pendant, 25 mm BSP	175 psi
VK151	F_071591	09343	5.6	80.6	Plain Barrel Dry Pendant, 1" NPT	175 psi
VK1510	F_101811	17389	5.6	80.6	Plain Barrel Dry Pendant, 25 mm BSP	175 psi
VK1510	F_101811	17388	5.6	80.6	Plain Barrel Dry Pendant, 1" NPT	175 psi
VK152	F_073091	07858U	5.6	80.6	Standard Response Plain Barrel Dry Horizontal Sidewall, 1" NPT	175 psi
VK152	F_073091	07861U	5.6	80.6	Standard Response Plain Barrel Dry Horizontal Sidewall, 25 mm BSP	175 psi
VK153	F_011194	09125U	5.6	80.6	Standard Response Plain Barrel Dry Vertical Sidewall, 1" NPT	175 psi
VK153	F_011194	08930U	5.6	80.6	Standard Response Plain Barrel Dry Vertical Sidewall, 25 mm BSP	175 psi
VK154	F_071591	07740U	5.6	80.6	Standard Response Adjustable Standard Dry Pendant, 1" NPT	175 psi
VK154	F_071591	07854U	5.6	80.6	Standard Response Adjustable Standard Dry Pendant, 25 mm BSP	175 psi
VK155	F_071591	09341	5.6	80.6	Adjustable Standard Dry Pendant, 1" NPT	175 psi
VK1550	F_101811	17391	5.6	80.6	Adjustable Standard Dry Pendant, 25 mm BSP	175 psi
VK1550	F_101811	17390	5.6	80.6	Adjustable Standard Dry Pendant, 1" NPT	175 psi
VK156	F_073091	07857U	5.6	80.6	Standard Response Adjustable Standard Dry Horizontal Sidewall, 1" NPT	175 psi
VK156	F_073091	07860U	5.6	80.6	Standard Response Adjustable Standard Dry Horizontal Sidewall, 1" NPT	175 psi
VK157	F_011194	09123U	5.6	80.6	Standard Response Adjustable Standard Dry Vertical Sidewall, 1" NPT	175 psi
VK157	F_011194	08961U	5.6	80.6	Standard Response Adjustable Standard Dry Vertical Sidewall, 25 mm BSP	175 psi
VK158	F_071591	06530U	5.6	80.6	Standard Response Adjustable Recessed Dry Pendant, 1" NPT	175 psi
VK158	F_071591	07853U	5.6	80.6	Standard Response Adjustable Recessed Dry Pendant, 25 mm BSP	175 psi
VK159	F_071591	09342	5.6	80.6	Adjustable Recessed Dry Pendant, 1" NPT	175 psi
VK1590	F_101811	17387	5.6	80.6	Adjustable Recessed Dry Pendant, 25 mm BSP	175 psi
VK1590	F_101811	17386	5.6	80.6	Adjustable Recessed Dry Pendant, 1" NPT	175 psi
VK160	F_033192	08050	5.6	80.6	Standard Response Plain Barrel Dry Upright, 1" NPT	175 psi
VK160	F_033192	08079	5.6	80.6	Standard Response Plain Barrel Dry Upright, Std. Orifice, 25 mm BSP	175 psi
VK161	F_011194	09124U	5.6	80.6	Standard Response Adjustable Recessed Dry Vertical Sidewall, 1" NPT	175 psi
VK161	F_011194	08962U	5.6	80.6	Standard Response Adjustable Recessed Dry Vertical Sidewall, 25 mm BSP	175 psi
VK162	F_073091	07856U	5.6	80.6	Standard Response Adjustable Recessed Dry Horizontal Sidewall, 1" NPT	175 psi
VK162	F_073091	07859U	5.6	80.6	Standard Response Adjustable Recessed Dry HSW, 25 mm BSP Dry Horizontal Sidewall, 25 mm BSP	175 psi
VK163	F_090110	12810U	8.0	115.2	Standard Response Adjustable Standard Dry Pendant, 1" NPT	175 psi
VK163	F_090110	12813U	8.0	115.2	Standard Response Adjustable Standard Dry Pendant, 25 mm BSP	175 psi
VK164	F_090110	12811U	8.0	115.2	Standard Response Adjustable Recessed Dry Pendant, 1" NPT	175 psi
VK164	F_090110	12814U	8.0	115.2	Standard Response Adjustable Recessed Dry Pendant, 25 mm BSP	175 psi
VK166	F_090110	12741U	8.0	115.2	Standard Response Plain Barrel Dry Pendant, 1" NPT	175 psi
VK166	F_090110	12812U	8.0	115.2	Standard Response Plain Barrel Dry Pendant, 25 mm BSP	175 psi
VK168	F_060796	09798U	5.6	80.6	Standard Response Stainless Steel Plain Barrel Dry Pendant, 1" NPT	175 psi
VK168	F_060796	09799U	5.6	80.6	Standard Response Stainless Steel Plain Barrel Dry Pendant, 25 mm BSP	175 psi
VK169	F_060796	10360U	5.6	80.6	Standard Response Stainless Steel Adjustable Recessed Dry Pendant, 1" NPT	175 psi
VK169	F_060796	10377U	5.6	80.6	Standard Response Stainless Steel Adjustable Recessed Dry Pendant, 25 mm BSP	175 psi
VK172	F_031793	08387U	5.6	80.6	Quick Response Plain Barrel Dry Pendant, 1" NPT	175 psi
VK172	F_031793	16455U	5.6	80.6	Quick Response Plain Barrel Dry Pendant, 25 mm BSP	175 psi
VK173	F_010305	13248U	8.0	115.2	Quick Response Ordinary Hazard Plain Barrel Dry Pendant, 1" NPT	175 psi
VK173	F_010305	13251U	8.0	115.2	Quick Response Ordinary Hazard Plain Barrel Dry Pdt, 25 mm BSP	175 psi
VK174	F_031993	08388U	5.6	80.6	Quick Response Plain Barrel Dry HSW, 1" NPT	175 psi
VK174	F_031993	16456U	5.6	80.6	Quick Response Plain Barrel Dry HSW, 25 mm BSP	175 psi
VK176	F_031793	08383U	5.6	80.6	Quick Response Adjustable Standard Dry Pendant, 1" NPT	175 psi
VK176	F_031793	16457U	5.6	80.6	Quick Response Adjustable Standard Dry Pendant, 25 mm BSP	175 psi
VK177	F_010305	13249U	8.0	115.2	Quick Response Ordinary Hazard Adjustable Standard Dry Pendant, 1" NPT	175 psi

SIN*	Technical Data Page(s)	Sprinkler Base Part Number	Nominal K-Factor		Sprinkler Model and Type	Maximum Pressure Rating (UL/FM)
			U.S.	metric		
VK177	F_010305	13252U	8.0	115.2	Quick Response Ordinary Hazard Adjustable Standard Dry Pendent, 25 mm BSP	175 psi
VK178	F_031993	08384U	5.6	80.6	Quick Response Adjustable Standard Dry Horizontal Sidewall, 1" NPT	175 psi
VK178	F_031993	16458U	5.6	80.6	Quick Response Adjustable Standard Dry Horizontal Sidewall, 25 mm BSP	175 psi
VK180	F_031793	08385U	5.6	80.6	Quick Response Adjustable Recessed Dry Pendent, 1" NPT	175 psi
VK180	F_031793	16453U	5.6	80.6	Quick Response Adjustable Recessed Dry Pendent, 25 mm BSP	175 psi
VK181	F_010305	13250U	8.0	115.2	Quick Response Ordinary Hazard Adjustable Recessed Dry Pendent, 1" NPT	175 psi
VK181	F_010305	13253U	8.0	115.2	Quick Response Ordinary Hazard Adjustable Recessed Dry Pendent, 25 mm BSP	175 psi
VK182	F_031993	08386U	5.6	80.6	Quick Response Adjustable Recessed Dry Horizontal Sidewall, 1" NPT	175 psi
VK182	F_031993	16454U	5.6	80.6	Quick Response Adjustable Recessed Dry Horizontal Sidewall, 25 mm BSP	175 psi
VK184	F_031693	08417UA	5.6	80.6	Quick Response Dry Upright, 1" NPT	175 psi
VK186	F_051498	10541U	5.6	80.6	Standard Response/Quick Response Extended Coverage Adjustable Recessed Dry Pendent, 1" NPT or 25 mm BSP	175 psi
VK188	F_051598	10542U	5.6	80.6	Standard Response/Quick Response Extended Coverage Adjustable Recessed Dry Horizontal Sidewall, 1" NPT	175 psi
VK190-D	F_092003	12421UA	5.6	80.6	Standard Response Dry Domed Concealed Pendent, 1" NPT	175 psi
VK190-D	F_092003	12429UA	5.6	80.6	Standard Response Dry Domed Concealed Pendent, 25 mm BSP	175 psi
VK192-D	F_081311	12424UA	8.0	115.2	Standard Response Dry Domed Concealed Pendent, 1" NPT	175 psi
VK192-D	F_081311	12432UA	8.0	115.2	Standard Response Dry Domed Concealed Pendent, 25 mm BSP	175 psi
VK194-D	F_092103	12422UA	5.6	80.6	Quick Response Dry Domed Concealed Pendent, 1" NPT	175 psi
VK194-D	F_092103	12430UA	5.6	80.6	Quick Response Dry Domed Concealed Pendent, 25 mm BSP	175 psi
VK196-D	F_092203	12423UA	5.6	80.6	Standard/QR EC Dry Domed Concealed Pendent, 1" NPT	175 psi
VK196-D	F_092203	12431UA	5.6	80.6	Standard/QR EC Dry Domed Concealed Pendent, 25 mm BSP	175 psi
VK200	F_032814	10141	8.0	115.2	Standard Response Upright, 3/4" NPT	175 psi
VK200	F_032814	10169	8.0	115.2	Standard Response Upright, 20 mm BSP	175 psi
VK200	N/A	10190	8.0	115.2	Standard Response Upright, 15 mm BSP (discontinued product)	175 psi
VK200	F_032814	10220	8.0	115.2	Standard Response Upright, 1/2" NPT (retrofit)	175 psi
VK200	F_032814	18266	8.0	115.2	Standard Response Upright, 20 mm BSP	175 psi
VK200	F_032814	20377	8.0	115.2	Standard Response Upright, 20 mm BSP	175 psi
VK200	F_032814	18263	8.0	115.2	Standard Response Upright, 3/4" NPT	175 psi
VK200	F_032814	20381	8.0	115.2	Standard Response Upright, 3/4" NPT	175 psi
VK200	F_032814	18268	8.0	115.2	Standard Response Upright, 1/2" NPT (retrofit)	175 psi
VK202	F_032614	10142	8.0	115.2	Standard Response Pendent, 3/4" NPT	175 psi
VK202	F_032614	10170	8.0	115.2	Standard Response Pendent, 20 mm BSP	175 psi
VK202	N/A	10187	8.0	115.2	Standard Response Pendent, 15 mm BSP (discontinued product)	175 psi
VK202	F_032614	10223	8.0	115.2	Standard Response Pendent, 1/2" NPT (retrofit)	175 psi
VK202	N/A	12105	8.0	115.2	Standard Response Pendent, 3/4" NPT (discontinued product)	175 psi
VK202	F_032614	18269	8.0	115.2	Standard Response Pendent, 1/2" NPT (Retrofit)	175 psi
VK202	F_032614	18264	8.0	115.2	Standard Response Pendent, 3/4" NPT	175 psi
VK202	F_032614	18267	8.0	115.2	Standard Response Pendent, 20 mm BSP	175 psi
VK202	F_032614	20380	8.0	115.2	Standard Response Pendent, 3/4" NPT (CCCC)	175 psi
VK202	F_032614	20376	8.0	115.2	Standard Response Pendent, 20 mm BSP (CCCC)	175 psi
VK202-D	F_101912	10142A-X	8.0	115.2	Standard Response Domed Concealed Pendent, 3/4" NPT	175 psi
VK204	F_060414	05514	8.0	115.2	Standard Response Fusible Link Upright, 3/4" NPT	175 psi
VK204	F_060414	05576	8.0	115.2	Standard Response Fusible Link Upright, 1/2" NPT (retrofit)	175 psi
VK204	F_060414	18253	8.0	115.2	Standard Response Fusible Link Upright, 3/4" NPT	175 psi
VK204	F_060414	18255	8.0	115.2	Standard Response Fusible Link Upright, 1/2" NPT (retrofit)	175 psi
VK206	F_060514	05578	8.0	115.2	Standard Response Fusible Link Pendent, 1/2" NPT (retrofit)	175 psi
VK206	F_060514	05516	8.0	115.2	Standard Response Fusible Link Pendent, 3/4" NPT	175 psi
VK206	F_060514	18254	8.0	115.2	Standard Response Fusible Link Pendent, 1/2" NPT (retrofit)	175 psi
VK206	F_060514	18256	8.0	115.2	Standard Response Fusible Link Pendent, 3/4" NPT	175 psi
VK210	N/A	09227	8.0	115.2	Special Response Upright, 3/4" NPT (discontinued product)	175 psi
VK212	N/A	09228	8.0	115.2	Special Response Pendent, 3/4" NPT (discontinued product)	175 psi
VK214	N/A	09229	8.0	115.2	Special Response Conventional, 3/4" NPT (discontinued product)	175 psi
VK2773		21489U	8.0	115.2	Quick Response Ordinary Hazard Adjustable Standard Dry HSW, 1" NPT	175 psi
VK2773		21490U	8.0	115.2	Quick Response Ordinary Hazard Adjustable Standard Dry HSW, 25 mm BSP	175 psi
VK2793	F_022617	21483U	8.0	115.2	Quick Response Ordinary Hazard Adjustable Recessed Dry HSW, 1" NPT	175 psi
VK2793		21484U	8.0	115.2	Quick Response Ordinary Hazard Adjustable Recessed Dry HSW, 25 mm BSP	175 psi
VK2753		21495U	8.0	115.2	Quick Response Ordinary Hazard Plain Barrell Dry HSW, 1" NPT	175 psi
VK2753		21496U	8.0	115.2	Quick Response Ordinary Hazard Plain Barrell Dry HSW, 25 mm BSP	175 psi
VK2883		21491U	8.0	115.2	Quick Response Ordinary Hazard Adjustable Standard Dry HSW Fusible Link, 1" NPT	175 psi
VK2883	F_022717	21492U	8.0	115.2	Quick Response Ordinary Hazard Adjustable Standard Dry HSW Fusible Link, 25 mm BSP	175 psi
VK2923		21485U	8.0	115.2	Quick Response Ordinary Hazard Adjustable Recessed Dry HSW Fusible Link, 1" NPT	175 psi
VK2923		21486U	8.0	115.2	Quick Response Ordinary Hazard Adjustable Recessed Dry HSW Fusible Link, 25 mm BSP	175 psi
VK2843		21497U	8.0	115.2	Quick Response Ordinary Hazard Plain Barrell Dry HSW Fusible Link, 1" NPT	175 psi
VK2843		21498U	8.0	115.2	Quick Response Ordinary Hazard Plain Barrell Dry HSW Fusible Link, 25 mm BSP	175 psi
VK2523		21487U	8.0	115.2	Standard Response Ordinary Hazard Adjustable Standard Dry HSW, 1" NPT	175 psi
VK2523		21488U	8.0	115.2	Standard Response Ordinary Hazard Adjustable Standard Dry HSW, 25 mm BSP	175 psi
VK2543	F_022817	21481U	8.0	115.2	Standard Response Ordinary Hazard Adjustable Recessed Dry HSW, 1" NPT	175 psi
VK2543		21482U	8.0	115.2	Standard Response Ordinary Hazard Adjustable Recessed Dry HSW, 25 mm BSP	175 psi
VK2503		21493U	8.0	115.2	Standard Response Ordinary Hazard Plain Barrell Dry HSW, 1" NPT	175 psi
VK2503		21494U	8.0	115.2	Standard Response Ordinary Hazard Plain Barrell Dry HSW, 25 mm BSP	175 psi
VK250	F_081511	13173U	8.0	115.2	Standard Response Ordinary Hazard Plain Barrel Dry HSW, 1" NPT	175 psi
VK250	F_081511	13179U	8.0	115.2	Standard Response Ordinary Hazard Plain Barrel Dry HSW, 25 mm BSP	175 psi
VK252	F_081511	13172U	8.0	115.2	Standard Response Ordinary Hazard Adjustable Standard Dry HSW, 1" NPT	175 psi
VK252	F_081511	13178U	8.0	115.2	Standard Response Ordinary Hazard Adjustable Standard Dry HSW, 25 mm BSP	175 psi
VK254	F_081511	13174U	8.0	115.2	Standard Response Ordinary Hazard Adjustable Recessed Dry HSW, 1" NPT	175 psi
VK254	F_081511	13180U	8.0	115.2	Standard Response Ordinary Hazard Adjustable Recessed Dry HSW, 25 mm BSP	175 psi
VK275	F_081111	13170U	8.0	115.2	Quick Response Ordinary Hazard Plain Barrel Dry HSW, 1" NPT	175 psi
VK275	F_081111	13176U	8.0	115.2	Quick Response Ordinary Hazard Plain Barrel Dry HSW, 25 mm BSP	175 psi
VK277	F_081111	13169U	8.0	115.2	Quick Response Ordinary Hazard Adjustable Standard Dry HSW, 1" NPT	175 psi
VK277	F_081111	13175U	8.0	115.2	Quick Response Ordinary Hazard Adjustable Standard Dry HSW, 25 mm BSP	175 psi
VK279	F_081111	13171U	8.0	115.2	Quick Response Ordinary Hazard Adjustable Recessed Dry HSW, 1" NPT	175 psi
VK279	F_081111	13177U	8.0	115.2	Quick Response Ordinary Hazard Adjustable Recessed Dry HSW, 25 mm BSP	175 psi
VK282	F_010505	13254U	8.0	115.2	Quick Response Plain Barrel Dry Pendent Fusible Link, 1" NPT	175 psi
VK282	F_010505	13257U	8.0	115.2	Quick Response Plain Barrel Dry Pendent Fusible Link, 25 mm BSP	175 psi
VK284	F_081211	13239U	8.0	115.2	Quick Response Ordinary Hazard Plain Barrel Dry HSW Fusible Link, 1" NPT	175 psi
VK284	F_081211	13242U	8.0	115.2	Quick Response Ordinary Hazard Plain Barrel Dry HSW Fusible Link, 25 mm BSP	175 psi
VK286	F_010505	13255U	8.0	115.2	Quick Response Adjustable Standard Dry Pendent Fusible Link, 1" NPT	175 psi
VK286	F_010505	13258U	8.0	115.2	Quick Response Adjustable Standard Dry Pendent Fusible Link, 25 mm BSP	175 psi
VK288	F_081211	13240U	8.0	115.2	Quick Response Ordinary Hazard Adjustable Standard Dry HSW Fusible Link, 1" NPT	175 psi
VK288	F_081211	13243U	8.0	115.2	Quick Response Adjustable Standard Dry Pendent Fusible Link, 25 mm BSP	175 psi
VK290	F_010505	13256U	8.0	115.2	Quick Response Adjustable Recessed Dry Pendent Fusible Link, 1" NPT	175 psi
VK290	F_010505	13259U	8.0	115.2	Quick Response Adjustable Recessed Dry Pendent Fusible Link, 25 mm BSP	175 psi
VK292	F_081211	13241U	8.0	115.2	Quick Response Ordinary Hazard Adjustable Recessed Dry HSW Fusible Link, 1" NPT	175 psi
VK292	F_081211	13244U	8.0	115.2	Quick Response Ordinary Hazard Adjustable Recessed Dry HSW Fusible Link, 25 mm BSP	175 psi

SIN*	Technical Data Page(s)	Sprinkler Base Part Number	Nominal K-Factor		Sprinkler Model and Type	Maximum Pressure Rating (UL/FM)
			U.S.	metric		
VK300	F_052114	06661B 12978	5.6	80.6	Quick Response Upright, ½" NPT	175 psi
VK301	F_062414	12279 17535 19779	5.6	80.6	Quick Response Fusible Element Upright, ½" NPT	175 psi
VK302	F_033314	06662B 19780 18021 12979	5.6	80.6	Quick Response Pendant, ½" NPT	175 psi
VK302-D	F_033614	06662BA-X	5.6	80.6	Standard/Quick Response Domed Concealed Pendant, ½" NPT (discontinued part number)	175 psi
VK302-D	F_033614	12979-X	5.6	80.6	Standard/Quick Response Domed Concealed Pendant, ½" NPT	
VK303	F_062514	12275 17536 19781	5.6	80.6	Quick Response Fusible Element Pendant, ½" NPT	175 psi
VK304	N/A	12982	5.6	80.6	Quick Response Horizontal Sidewall, ½" NPT	175 psi
VK305	F_060914	12121 19782 12997	5.6	80.6	Quick Response Horizontal Sidewall, ½" NPT	175 psi
VK306	F_060614	06727B 12983	5.6	80.6	Quick Response Vertical Sidewall, ½" NPT	175 psi
VK307	F_062714	13947 13948	5.6	80.6	Quick Response Fusible Element Horizontal Sidewall, ½" NPT	175 psi
VK308	F_021301	13949 13950	5.6	80.6	Quick Response Fusible Element HSW, ½" NPT	175 psi
VK309	F_020407	13951	5.6	80.6	Quick Response Fusible Element VSW, ½" NPT	175 psi
VK310	F_022514	06766B 19391	5.6	80.6	Quick Response Conventional, ½" NPT	175 psi
VK311	F_022614	13952 19392	5.6	80.6	Quick Response Fusible Element Conventional, ½" NPT	175 psi
VK315	F_060714	12281	5.6	80.6	HP Quick Response Upright, ½" NPT	250 psi
VK316	F_062814	13953	5.6	80.6	Quick Response Fusible Element Upright, 1/2" NPT	250 psi
VK317	F_060814	12282	5.6	80.6	HP Quick Response Pendant, ½" NPT	250 psi
VK318	F_062914	13954	5.6	80.6	HP Quick Response Fusible Element Pendant, ½" NPT	250 psi
VK319	F_030103	12285	5.6	80.6	HP -5 Quick Response Horizontal Sidewall, ½" NPT	250 psi
VK320	F_020307	13955	5.6	80.6	Quick Response Fusible Element HSW, ½" NPT	175 psi
VK325	F_061414	06717B 12980	2.8	40.3	Quick Response Upright, Small Orifice, ½" NPT	175 psi
VK326	F_063014	13956 13957	2.8	40.3	Quick Response Fusible Element Upright, Small Orifice, ½" NPT	175 psi
VK3271	F_061614	06931B	4.2	57	Quick Response Upright, Small Orifice, 10 mm BSP	175 psi
VK327	F_061514	06719B	4.2	57	Quick Response Upright, Small Orifice, ½" NPT	175 psi
VK328	F_071114	13958	4.2	57	Quick Response Upright, Small Orifice, 1/2" NPT	175 psi
VK329	F_061714	06718B 12981	2.8	40.3	Quick Response Pendant, Small Orifice, ½" NPT	175 psi
VK330	F_071014	13959 13960	2.8	40.3	Quick Response Fusible Element Pendant, Small Orifice, ½" NPT	175 psi
VK3311	F_061914	06932B	4.2	57	Quick Response Pendant, Small Orifice, 10 mm BSP	175 psi
VK331	F_061814	06720B	4.2	57	Quick Response Pendant, Small Orifice, ½" NPT	175 psi
VK332	F_071214	13961	4.2	57	Quick Response Fusible Element Pendant, Small Orifice, ½" NPT	175 psi
VK333	F_062014	10035	2.8	40.3	Quick Response Horizontal Sidewall, Small Orifice, ½" NPT	175 psi
VK334	F_071314	13962	2.8	40.3	Quick Response Fusible Element Horizontal Sidewall, Small Orifice, 1/2" NPT	175 psi
VK335	F_011012	08983	4.2	57	Quick Response Horizontal Sidewall, Small Orifice, 10 mm BSP	175 psi
VK337	F_050300	08985	4.2	57	Quick Response Vertical Sidewall, Small Orifice, 10 mm BSP	175 psi
VK338	F_073107	14692	5.6	80.6	Quick Response Stainless Steel Upright, ½" NPT	175 psi
VK339	F_073107	14693	5.6	80.6	Quick Response Stainless Steel Pendant, ½" NPT	175 psi
VK340	F_062114	12286	2.8	40.3	HP Quick Response Upright, Small Orifice, ½" NPT	250 psi
VK341	F_071414	13963	2.8	40.3	Quick Response Upright, Small Orifice, 1/2" NPT	250 psi
VK342	F_062214	12290	2.8	40.3	HP Quick Response Pendant, Small Orifice, ½" NPT	250 psi
VK343	F_071514	13964	2.8	40.3	HP Quick Response Fusible Element Pendant, Small Orifice, ½" NPT	250 psi
VK344	F_080688	12287	2.8	40.3	HP Quick Response Horizontal Sidewall, Small Orifice, ½" NPT	250 psi
VK345	F_033114	07060 12984 19783	5.6	80.6	Quick Response Upright, 15 mm BSP	175 psi
VK346	F_071614	13965	2.8	40.3	HP Quick Response Fusible Element Horizontal Sidewall, Small Orifice, 1/2" NPT	250 psi
VK350	F_033014	06665B	8.0	115.2	Quick Response Upright, 3/4" NPT	175 psi
VK350	F_033014	14817	8.0	115.2	Quick Response Upright, 20 mm BSP	175 psi
VK350	F_033014	06764B	8.0	115.2	Quick Response Upright, ½" NPT	175 psi
VK351	F_071714	13976 18275	8.0	115.2	Quick Response Fusible Element Upright, 3/4" NPT	175 psi
VK351	F_071714	13966 18272	8.0	115.2	Quick Response Fusible Element Upright, 1/2" NPT (Retrofit)	175 psi
VK352	F_033414	06666B 18258 20383	8.0	115.2	Quick Response Pendant, 3/4" NPT	175 psi
VK352	F_033414	06765B 18260	8.0	115.2	Quick Response Pendant, 1/2" NPT (Retrofit)	175 psi
VK352-D	N/A	06666BA-X	8.0	115.2	Standard/Quick Response Domed Concealed Pendant, 3/4" NPT (discontinued part number)	175 psi
VK352-D	F_102212	18258	8.0	115.2	Standard/Quick Response Domed Concealed Pendant, 3/4" NPT (discontinued part number)	175 psi
VK352	N/A	12104	8.0	115.2	Quick Response Pendant, 3/4" NPT (discontinued part number)	175 psi
VK353	F_071814	13975 18274	8.0	115.2	Quick Response Fusible Element Pendant, 3/4" NPT	175 psi
VK353	F_071814	13967 18273	8.0	115.2	Quick Response Fusible Element Pendant, 1/2" NPT (Retrofit)	175 psi
VK353-D	N/A	13975A-X	8.0	115.2	Quick Response Concealed Fusible Element Pendant, 3/4" NPT (discontinued part number)	175 psi
VK353-D	F_102212	18274A-X	8.0	115.2	Quick Response Concealed Fusible Element Pendant, 3/4" NPT	175 psi
VK354	F_033214	06768B 18261	8.0	115.2	Quick Response Conventional, 3/4" NPT	175 psi
VK355	F_071914	13979 18276	8.0	115.2	Quick Response Fusible Element Conventional, 3/4" NPT	175 psi
VK360	F_092508	15591	8.0	115.2	Quick Response Horizontal Sidewall, 3/4" NPT	175 psi
VK368	F_071917	21928	8.0	115.2	Standard Response Stainless Steel Pendant Sprinkler	175 psi
VK375	N/A	08338	11.2	161.3	Quick Response ELO Upright, Extra-Large Orifice, 3/4 NPT (discontinued product)	175 psi
VK377	F_030993	08337 17489	11.2	161.3	Quick Response ELO Pendant, (Special Application), 3/4" NPT	175 psi
VK400	F_081788	06697B	5.6	80.6	Standard Response Model H Fusible Link Flush Pendant, Std. Orifice, ½" NPT	175 psi



SIN*	Technical Data Page(s)	Sprinkler Base Part Number	Nominal K-Factor		Sprinkler Model and Type	Maximum Pressure Rating (UL/FM)
			U.S.	metric		
VK401	N/A	07937	5.6	80.6	Standard Response Model H Fusible Link Flush Pendant, Std. Orifice, 1/2" NPT (discontinued product)	175 psi
VK402	F_081888	06702B	5.6	80.6	Quick Response Model H-1 Fusible Link Flush Pendant, 1/2" NPT	175 psi
VK403	N/A	10741	5.6	80.6	Quick Response Model H-4 Fusible Link Flush Horizontal Sidewall, 1/2" NPT (discontinued product)	175 psi
VK404	N/A	09783A	5.6	80.6	Standard Response/Quick Response Model B-2 Fusible Link Concealed Pendant, 1/2" NPT (discontinued product)	175 psi
VK405	N/A	09782A	5.6	80.6	HP Standard Response/Quick Response Model B-2 Fusible Link Concealed Pendant, 1/2" NPT (discontinued product)	250 psi
VK406	N/A	10491A	8.0	115.2	Quick Response Model B-2 Fusible Link Concealed Pendant, Lrg. Orifice, 1/2" NPT (discontinued product)	175 psi
VK406	N/A	10681A	8.0	115.2	Quick Response Model B-2 Fusible Link Concealed Pendant, 3/4" NPT (discontinued product)	175 psi
VK407	N/A	08617A	5.5	80.6	LPCB Approved Model B-1 Concealed Sprinkler (discontinued product)	175 psi
VK408	N/A	11262A	5.6	80.6	Quick Response Concealed Horizontal Sidewall Sprinkler, Std. Orifice, 1/2" NPT (discontinued product)	175 psi
VK410	F_100998	10554	5.6	80.6	Quick Response Model HQR-2 Fusible Link Flush Pendant,	175 psi
VK412	F_101098	10579	5.6	80.6	Quick Response Model HQR-2 Fusible Link Flush Horizontal Sidewall, 1/2" NPT	175 psi
VK413	F_081888	11487	5.6	80.6	Quick Response Model H Fusible Link Flush Pendant, 1/2" NPT	175 psi
VK416	N/A	11600A	4.2	80.6	Quick Response Concealed Pendant, 1/2" NPT (discontinued product)	175 psi
VK420	F_062395	09458	3.8	54.8	Residential Model H-3 Fusible Link Flush Pendant, 1/2" NPT	175 psi
VK421	N/A	06858B	5.5	80.6	Residential Model H Fusible Link Flush Pendant, 1/2" NPT (discontinued product)	175 psi
VK425	N/A	10784A	4.1	59.1	Residential Model B-3 Fusible Link Flush Concealed, 1/2" NPT (discontinued product)	175 psi
VK426	F_032319	19663 20110	5.6	80.6	Quick Response Pendant Institutional Sprinkler, 1/2" NPT or 15mm BSPT	175 psi
VK427	F_032319	22885 22908	5.6	80.6	Quick Response Horizontal Sidewall Institutional Sprinkler, 1/2" NPT or 15mm BSPT	175 psi
VK430	F_082095	09530	4.3	62.0	Residential -4 Pendant, 1/2" NPT	175 psi
VK432	N/A	10050	5.5	79.3	Residential -5 Pendant, 1/2" NPT (discontinued product)	175 psi
VK434	N/A	10149	3.1	44.7	Residential -6 Pendant, 1/2" NPT (discontinued product)	175 psi
VK436	N/A	12166	5.2	75.0	Residential Pendant, 1/2" NPT (discontinued product)	175 psi
VK436	N/A	12166A-X	5.2	75.0	Residential Domed Concealed Pendant, 1/2" NPT (discontinued product)	175 psi
VK438	N/A	12224	4.9	70.6	Residential Pendant, 1/2" NPT (discontinued product)	175 psi
VK438	N/A	12224A-X	4.9	70.6	Residential Domed Concealed Pendant, 1/2" NPT (discontinued product)	175 psi
VK440	N/A	09787	4.3	62.0	Residential -4 Horizontal Sidewall, 1/2" NPT (discontinued product)	175 psi
VK442	N/A	12119	5.5	79.3	Residential -5 Horizontal Sidewall, 1/2" NPT (discontinued product)	175 psi
VK444	N/A	10210	3.7	53.3	Residential -7 Horizontal Sidewall, 1/2" NPT (discontinued product)	175 psi
VK446	N/A	06769B	5.5	79.3	Quick Response Light Hazard Horizontal Sidewall Sprinkler, 15 mm BSP (discontinued product)	175 psi
VK446	N/A	10037	5.6	80.6	Quick Response Light Hazard Horizontal Sidewall Sprinkler, 15 mm BSP (discontinued product)	175 psi
VK448	N/A	11810	4.3	62.0	Residential Horizontal Sidewall, 1/2" NPT (discontinued product)	175 psi
VK450	N/A	12357	4.2	57	Residential Horizontal Sidewall Sprinkler VK450 (K4.2) (discontinued product)	175 psi
VK454	N/A	12292	5.6	80.6	HP Quick Response Model B-2 Fusible Link Concealed Pendant, 1/2" NPT (discontinued product)	250 psi
VK456	N/A	13620A	4.9	70.6	Residential Fusible Link Concealed Pendant, 1/2" NPT (discontinued product)	175 psi
VK456	N/A	106871AJ	4.9	70.6	Residential Fusible Link Concealed Lead Free Pendant, 1/2" NPT (discontinued product)	175 psi
VK457	F_072607	14694A	4.9	70.6	Residential Fusible Element Concealed Pendant, 1/2" NPT	175 psi
VK457	F_100710	16872AC	4.9	70.6	Residential Fusible Element Concealed Lead Free Pendant, 1/2" NPT	175 psi
VK458	F_042005	13230	7.4	106.7	Residential Pendant, 3/4" NPT	175 psi
VK458-D	F_092305	13230ABX	7.4	106.7	Residential Domed Concealed Pendant, 3/4" NPT (discontinued product)	175 psi
VK460	F_110205	13933	5.8	83.6	Residential Horizontal Sidewall, 1/2" NPT	175 psi
VK461	F_091506	13831A	2.8	40.3	Standard/Quick Response Concealed Pendant, Small Orifice, 1/2" NPT	175 psi
VK461	F_010408	14927	2.8	40.3	Adjustable Concealed Sprinkler Assembly, 1" NPT Male Connection	175 psi
VK461	F_010408	14928	2.8	40.3	Adjustable Concealed Sprinkler Assembly, 1" NPT Female Connection	175 psi
VK462	F_103005	13503A 19785A	5.6	80.6	Quick Response Concealed Pendant, 1/2" NPT	175 psi
VK462-MRI	F_062908	15480A	5.6	80.6	Quick Response Concealed Pendant MRI, 1/2" NPT	175 psi
VK462	F_010408	14918	5.6	80.6	Adjustable Concealed Sprinkler Assembly, 1" NPT Male Connection	175 psi
VK462	F_010408	14919	5.6	80.6	Adjustable Concealed Sprinkler Assembly, 1" NPT Female Connection	175 psi
VK462	F_022409	13642/CR	5.6	80.6	Cleanroom Sprinkler (Cover Assembly)	175 psi
VK463	F_103005	13667A	5.6	80.6	HP Quick Response Concealed Pendant, 1/2" NPT	250 psi
VK464	F_021606	13614A	8.0	115.2	Quick Response Concealed Pendant, 3/4" NPT	175 psi
VK464	F_062908	15481A	8.0	115.2	Quick Response Concealed Pendant MRI, 3/4" NPT	175 psi
VK465	F_032107	14282A	4.2	57	Quick Response Concealed Pendant, Small Orifice, 1/2" NPT	175 psi
VK465	F_010408	14929	4.2	57	Adjustable Concealed Sprinkler Assembly, 1" NPT Male Connection	175 psi
VK465	F_010408	14930	4.2	57	Adjustable Concealed Sprinkler Assembly, 1" NPT Female Connection	175 psi
VK466	F_091406	13781	5.2	74.9	Residential Pendant, 1/2" NPT	175 psi
VK466-D	F_091606	13781A-X	5.2	74.9	Residential Concealed Pendant, 1/2" NPT (discontinued product)	175 psi
VK468	F_012706	13637	4.9	70.6	Residential Pendant, 1/2" NPT	175 psi
VK467	F_090413	19154	4.9	70.6	Residential Upright, 1/2" NPT	175 psi
VK467	F_061314	19442	4.9	70.6	Residential Lead Free Upright, 1/2" NPT	175 psi
VK468	F_101010	16876	4.9	70.6	Residential Lead Free Pendant, 1/2" NPT	175 psi
VK468-D	F_020206	13637A-X	4.9	70.6	Residential Concealed Pendant, 1/2" NPT (discontinued product)	175 psi
VK469	F_120508	15764A	11.2	161.3	Quick Response ELO Concealed Pendant, Extra Large Orifice, 3/4" NPT	175 psi
VK470	F_061011	17147	3.0	43.2	Residential Pendant, 1/2" NPT	175 psi
VK470	F_100611	17492	3.0	43.2	Residential Lead Free Pendant, 1/2" NPT	175 psi
VK472	F_121409	16130	5.8	83.6	Residential Pendant, 1/2" NPT	175 psi
VK474	F_012109	15790AC	5.8	83.6	Residential Concealed Pendant, 1/2" NPT (discontinued product)	175 psi
VK476	F_120608	15630MC/-	4.9	70.6	Residential Flush Pendant, 1/2" NPT	175 psi
VK478	F_042612	19995	5.6	80.6	Quick Response Flush Pendant, 1/2" NPT	175 psi
VK478	F_042612	20112	5.6	80.6	Quick Response Flush Pendant, 15 mm BSP	175 psi
VK479	F_012915	19707	3.0	43.2	Residential Horizontal Sidewall, 1/2" NPT	175 psi
VK480	F_121609	16116AC	4.0	57.7	Residential Concealed Horizontal Sidewall, 1/2" NPT	175 psi
VK480	F_100810	16880AC	4.0	57.7	Residential Lead Free Concealed Horizontal Sidewall, 1/2" NPT	175 psi
VK481	F_020312	17555A	5.6	80.6	Quick Response Concealed Horizontal Sidewall, 1/2" NPT	175psi
VK482	F_081512	18385	5.6	80.6	Quick Response Flush Concealed Dry Pendant, 1" NPT	175psi
VK484	F_050310	16240	4.2	57	Residential Horizontal Sidewall, 1/2" NPT	175 psi
VK484	F_100510	16881	4.2	57	Residential Lead Free Horizontal Sidewall, 1/2" NPT	175 psi
VK486	F_082411	17315	4.0	57.7	Residential Horizontal Sidewall, 1/2" NPT	175 psi
VK488	F_073012	18325	3.0	43.2	Freedom Residential Concealed Pendant, 1/2" NPT	175 psi
VK488	F_061214	18326	3.0	43.2	Freedom Residential Lead Free Concealed Pendant, 1/2" NPT	175 psi
VK490	F_032116	20409	5.8	83.6	Freedom Residential Concealed Pendant, 1/2" NPT	175 psi
VK492	F_101615	20034	5.6	80.6	Standard Response Concealed Pendant, 1/2" NPT	175 psi
VK494	F_012116	20759	4.9	70.6	Residential Concealed Pendant, 1/2" NPT	175 psi
VK494	F_120517	22043	4.9	70.6	Lead Free Residential Concealed Pendant, 1/2" NPT (not offered)	175 psi
VK496	F_032218	22773	3.0	43.2	Residential Concealed Pendant, 1/2" NPT	175 psi
VK496	F_012419	22774	3.0	43.2	Lead Free Residential Concealed Pendant, 1/2" NPT (not offered)	175 psi
VK498	F_112817	22037AB 22037AE 22037JNB 22037JNE	5.8	83.6	Freedom Residential Concealed Pendant, 1/2" NPT	175 psi

SIN*	Technical Data Page(s)	Sprinkler Base Part Number	Nominal K-Factor		Sprinkler Model and Type	Maximum Pressure Rating (UL/FM)
			U.S.	metric		
VK4980	F_120617	22037AB 22037AE 22037JNB 22037JNE	5.8	83.6	Lead Free Freedom Residential Concealed Pendent, ½" NPT (not offered)	175 psi
VK500	F_060198	10284	14.0	–	Model S-1 ESFR Pendent, ¾" NPT	175 psi
VK500	F_060198	11350 19855	–	202	Model S-1 ESFR Pendent, 20 mm NPT	175 psi
VK500	N/A	14779	14.0	–	Model S-1 ESFR Pendent, ¾" NPT (discontinued product)	175 psi
VK501	N/A	14909	14.0	202	ESFR Dry Pendent, 2" Grooved Connection (discontinued product)	175 psi
VK501	N/A	14910	14.0	202	ESFR Dry Pendent, 1-1/2" NPT Threaded Connection (discontinued product)	175 psi
VK501	N/A	14911	14.0	202	ESFR Dry Pendent, 1-1/2" BSP Threaded Connection (discontinued product)	175 psi
VK502	F_042012	18702 18706 18710 18176 19908 19909 19910 19895	14.0	202	ESFR Dry Pendent, 2" Grooved Connection	175psi
VK502	F_042012	18703 18707 18711 18177	14.0	202	ESFR Dry Pendent, 1-1/2" NPT Threaded Connection	175psi
VK502	F_042012	18704 18708 18712 18178 19901	14.0	202	ESFR Dry Pendent, 1-1/2" BSP Threaded Connection	175psi
VK503	F_120106	14073	16.8	242	ESFR Pendent, ¾" NPT	175 psi
VK503	F_120106	14818 19856 20372	16.8	242	ESFR Pendent, 20 mm BSP	175 psi
VK504	F_062613	19015 19905 19907 19911 19913 19229 19912 19225	16.8	242	ESFR Dry Pendent, 1-1/2" Grooved Connection	175 psi
VK504	F_062613	19016 19234 19226 19230	16.8	242	ESFR Dry Pendent, 1-1/2" NPT Threaded Connection	175 psi
VK504	F_062613	19017 19235 19231 19227 19225	16.8	242	ESFR Dry Pendent, 1-1/2" BSP Threaded Connection	175 psi
VK506	F_081612	18493 18494	22.4	320	ESFR Pendent, 1" NPT, 25mm BSP	175 psi
VK510	F_100102	12080 19857 45224	25.2	363.3	ESFR Pendent, 1" NPT (Part No. 15221 discontinued)	175 psi
VK510	F_100102	12200 20373 44958	25.2	363.3	ESFR Pendent, 25 mm BSP (Part No. 14958 discontinued)	175 psi
VK514	F_010715	19591 19592 22894 22954	28.0	404	Specific Application ESFR Pendent, 1" NPT, 25 mm BSP	175 psi
VK520	F_060298	10625 19786	14.0	202	Model A-4 ESFR Upright, ¾" NPT	175 psi
VK530	F_010692	09679	11.2	161.3	Standard Response ELO Upright (Special Application), ¾" NPT	175 psi
VK530	F_010692	14819	11.2	161.3	Standard Response ELO Upright (Special Application), 20 mm BSP	175 psi
VK531	F_120699	10633	11.2	161.3	Quick Response ELO Upright (Special Application), ¾" NPT	175 psi
VK5311	F_120699	19304 19305	11.2	161.3	Quick Response ELO Upright (Special Application), 1/2" NPT	175 psi
VK532	F_053114	08687	11.2	161.3	Standard/Quick Response EC LH/OH ELO Upright, ¾" NPT	175 psi
VK533	F_021807	13978	11.2	161.3	Quick Response ELO Fusible Element Upright (Special Application), ¾" NPT	175 psi
VK534	F_051393	08340	11.2	161.3	Standard and QR ECOH ELO Pendent, ¾" NPT	175 psi
VK535	F_072014	14139	11.2	161.3	Standard and QR ECOH ELO Fusible Element Upright, ¾" NPT	175 psi
VK536	F_072213	07961	11.2	161.3	Standard Response ELO Upr (Special Application) and Pdt, ¾" NPT	175 psi
VK536	F_072213	14820	11.2	161.3	Standard Response ELO Upr (Special Application) and Pdt, 20 mm BSP	175 psi
VK537	F_021907	14611	11.2	161.3	Standard and QR ECOH ELO Fusible Element Pendent, ¾" NPT	175 psi
VK538	F_050511	17115A	11.2	161.3	EC/QREC OH Concealed Pendent, Extra-Large Orifice, ¾" NPT	175 psi
VK540	F_090595	13167	11.2	161.3	Model A-2 Standard Response High Challenge® Upright Large Drop, ELO, ¾" NPT	175 psi
VK540	F_090595	13166	11.2	161.3	Model A-2 Standard Response High Challenge® Upright Large Drop, ELO, ½" NPT	175 psi
VK544	F_040815	19830 19831	11.2	161.3	Standard Response Dry Pendent ELO, 1-1/4" NPT, 32 mm BSP	175 psi
VK545	F_040815	19835 19836	11.2	161.3	Standard Response Dry Pendent ELO, 1-1/4" NPT, 32 mm BSP	175 psi
VK546	F_040815	19840 19841	11.2	161.3	Standard Response Dry Pendent ELO, 1-1/4" NPT, 32 mm BSP	175 psi
VK547	F_040915	19828 19829	11.2	161.3	Quick Response Dry Pendent ELO, 1-1/4" NPT, 32 mm BSP	175 psi
VK548	F_040915	19833 19834	11.2	161.3	Quick Response Dry Pendent ELO, 1-1/4" NPT, 32 mm BSP	175 psi
VK549	F_040915	19838 19839	11.2	161.3	Quick Response Dry Pendent ELO, 1-1/4" NPT, 32 mm BSP	175 psi
VK550	F_012498	10138–U 12986–U	5.6	80.6	Standard Response Upright Intermediate Level, ½" NPT	175 psi
VK551	F_012498	12279–U	5.6	80.6	Quick Response Fusible Element Upright Intermediate Level, ½" NPT	175 psi
VK552	F_012498	05557–U 12973–U	5.6	80.6	Standard Response Fusible Link Upright Intermediate Level, ½" NPT	175 psi

SIN*	Technical Data Page(s)	Sprinkler Base Part Number	Nominal K-Factor		Sprinkler Model and Type	Maximum Pressure Rating (UL/FM)
			U.S.	metric		
VK556	F_012498	06661B-U 12978-U	5.6	80.6	Quick Response Upright Intermediate Level, 1/2" NPT	175 psi
VK558	F_012498	12281-U	5.6	80.6	HP Quick Response Upright Intermediate Level, 1/2" NPT	250 psi
VK560	F_012498	10141-U	8.0	115.2	Standard Response Upright Intermediate Level, 3/4" NPT	175 psi
VK560	F_012498	10220-U	8.0	115.2	Standard Response Upright Intermediate Level, 1/2" NPT	175 psi
VK562	F_012498	05514-U	8.0	115.2	Standard Response Fusible Link Upright Intermediate Level, 3/4" NPT	175 psi
VK566	F_012498	06665B-U	8.0	115.2	Quick Response Upright Intermediate Level, 3/4" NPT	175 psi
VK567	F_012498	13976-U	8.0	115.2	Quick Response Upright Intermediate Level, 3/4" NPT	175 psi
VK570	F_010104	13840	14.0	202	Extended Coverage Ordinary Hazard Upright, 3/4" NPT	175 psi
VK572	F_072313	13722	14.0	202	Extended Coverage Ordinary Hazard Pendant, 3/4" NPT	175 psi
VK580	F_041904	12739	16.8	242.2	Standard Response Upright, 3/4" NPT	175 psi
VK592	F_033108	14243A	19.6	282.6	Standard Response Pendant, 1" NPT	175 psi
VK592	N/A	15483	19.6	282.6	Standard Response Pendant, 1" NPT (discontinued product)	175 psi
VK592	F_033108	15468	19.6	282.6	Standard Response Pendant, 25 mm BSP	175 psi
VK592	N/A	15484	19.6	282.6	Standard Response Pendant, 25 mm BSP (discontinued product)	175 psi
VK595	F_121610	16859	25.2	363.3	EC Upright (Storage-Density/Area), 1" NPT	175 psi
VK595	F_121610	16885	25.2	363.3	EC Upright (Storage-Density/Area), 25 mm BSP	175 psi
VK598	F_090414	19522A 19764A	25.2	363.3	Standard Response Upright, 1" NPT, 25 mm BSP	175 psi
VK600	F_080988	06778B	5.6	80.6	Standard Response/Quick Response Extended Coverage Pendant, 1/2" NPT	175 psi
VK601	F_072114	13969	5.6	80.6	Quick Response EC Fusible Element Pendant, 1/2" NPT	175 psi
VK602	F_102412	07077B 18262	8.0	115.2	Standard Response/Quick Response Extended Coverage Pendant, 3/4" NPT	175 psi
VK603	F_102512	14140 18277	8.0	115.2	Quick Response Extended Coverage Pendant, 3/4" NPT	175 psi
VK604	F_062314	10335	5.6	80.6	Standard Response/Quick Response -5 Extended Coverage Pendant, 1/2" NPT	175 psi
VK605	F_072414	12120	5.6	80.6	-5 HSW (with EC, QREC, and Specific Application Listings), 1/2" NPT	175 psi
VK606	F_102612	13005 18271	8.0	115.2	Standard Response/Quick Response Extended Coverage Horizontal Sidewall, 3/4" NPT	175 psi
VK607	F_072214	13970	5.6	80.6	Standard Response/Quick Response Extended Coverage Fusible Element Pendant, 1/2" NPT	175 psi
VK608	F_052793	08339	11.2	161.3	Standard Response/Quick Response Extended Coverage Light Hazard Extra-Large Orifice Pendant, 3/4" NPT	175 psi
VK609	F_072314	13971	5.6	80.6	Standard Response/Quick Response Extended Coverage Fusible Element Horizontal Sidewall, 1/2" NPT	175 psi
VK610	F_022098	12294	5.6	80.6	HP Standard Response/Quick Response -5 Extended Coverage Pendant, 1/2" NPT	250 psi
VK611	F_020807	13972	5.6	80.6	HP Standard Response/Quick Response Extended Coverage Fusible Element Pendant, 1/2" NPT	250 psi
VK612	F_030203	12295	5.6	80.6	HP Standard Response/Quick Response -5 EC HSW, 1/2" NPT	250 psi
VK613	F_020907	13973	5.6	80.6	HP Standard Response/Quick Response Extended Coverage Fusible Element Horizontal Sidewall, 1/2" NPT	250 psi
VK614-D	F_061603	06778BA-X	5.6	80.6	Standard Response/Quick Response Extended Coverage Domed Concealed Pendant, 1/2" NPT	175 psi
VK616-D	F_061603	07077BA-X	8.0	115.2	Standard Response/Quick Response Extended Coverage	175 psi
VK617	F_021207	14141	11.2	161.3	Standard Response/Quick Response Extended Coverage Light Hazard Extra-Large Orifice Fusible Element Pendant, 3/4" NPT	175 psi
VK618-D	F_061503	08339A-X	11.2	161.3	Standard Response/Quick Response Extended Coverage Domed Concealed Light Hazard Extra-Large Orifice Pendant, 3/4" NPT	175 psi
VK625	N/A	08498A	5.6	80.6	Standard Response/Quick Response Model B-1 Fusible Link Extended Coverage Concealed Pendant, 1/2" NPT (discontinued product)	175 psi
VK627	N/A	10485A	8.0	115.2	Standard Response/Quick Response Model B-2 Fusible Link Extended Coverage Concealed Pendant, 1/2" NPT (discontinued product)	175 psi
VK627	N/A	10680A	8.0	115.2	Standard Response/Quick Response Model B-2 Fusible Link Extended Coverage Concealed Pendant, 3/4" NPT (discontinued product)	175 psi
VK630	F_102905	13500	8.0	115.2	Quick Response Extended Coverage Horizontal Sidewall, 3/4" NPT	175 psi
VK630-D	F_102805	13500A-X	8.0	115.2	Quick Response EC Domed Concealed HSW, 3/4" NPT	175 psi
VK631	N/A	16112	8.0	115.2	HP Quick Response Extended Coverage HSW, 3/4" NPT (discontinued product)	300 psi
VK631-D	N/A	16112A-X	8.0	115.2	HP Quick Response EC Domed Concealed HSW, 3/4" NPT (discontinued product)	300 psi
VK632	F_080107	14613A	5.6	80.6	Quick Response EC Concealed Pendant, 1/2" NPT	175 psi
VK634	F_080107	14635A	8.0	115.2	Quick Response EC Concealed Pendant, 3/4" NPT	175 psi
VK636	F_121009	16102A	11.2	161.3	Quick Response EC LH Concealed Pendant, Extra-Large Orifice, 3/4" NPT	175 psi
VK638	F_081911	17375	8.0	115.2	Quick Response EC Horizontal Sidewall, 3/4" NPT	175psi
VK650	F_032319	19876 20111	5.6	80.6	Quick Response Extended Coverage Pendant Institutional Sprinkler 1/2" NPT or 15mm BSPT	175psi
VK651	F_032319	22884 22907	5.6	80.6	Quick Response Extended Coverage Horizontal Sidewall Institutional Sprinkler 1/2" NPT or 15mm BSPT	175psi
VK638	F_082211	17375	8.0	115.2	Quick Response EC Concealed Horizontal Sidewall, 3/4" NPT	175psi
VK660	F_092116	20952	5.6	80.6	V-HIP Quick Response Specific Application Attic Sprinkler	175psi
VK680	F_050611	17114AC	8.0	115.2	Quick Response EC Concealed HSW, 3/4" NPT	175 psi
VK681	F_042915	19626	8.0	115.2	V-BB Specific Application Attic Sprinkler, 3/4" NPT (4:12 < 7:12)	175 psi
VK682	F_042915	19798	8.0	115.2	V-BB Specific Application Attic Sprinkler, 3/4" NPT (7:12 < 10:12)	175 psi
VK683	F_042915	19751	8.0	115.2	V-BB Specific Application Attic Sprinkler, 3/4" NPT (10:12 < 12:12)	175 psi
VK684	F_042915	19627	5.6	80.6	V-BB Specific Application Attic Sprinkler, 1/2" NPT (4:12 < 7:12)	175 psi
VK685	F_042915	19801	5.6	80.6	V-BB Specific Application Attic Sprinkler, 1/2" NPT (7:12 < 10:12)	175 psi
VK686	F_042915	19754	5.6	80.6	V-BB Specific Application Attic Sprinkler, 1/2" NPT (10:12 < 12:12)	175 psi
VK693	F_043015	19578	5.6	80.6	V-SD Specific Application Attic Sprinkler, 1/2" NPT (4:12 < 7:12)	175 psi
VK694	F_043015	19799	5.6	80.6	V-SD Specific Application Attic Sprinkler, 1/2" NPT (7:12 < 10:12)	175 psi
VK695	F_043015	19759	5.6	80.6	V-SD Specific Application Attic Sprinkler, 1/2" NPT (10:12 < 12:12)	175 psi
VK696	F_042815	19538	4.2	57	Attic Upright Specific Application Attic Sprinkler, 1/2" NPT (4:12 to 12:12)	175 psi
VK697	F_042517	21716	5.6	80.6	Attic Upright Specific Application Attic Sprinkler, 1/2" NPT (4:12 to 12:12)	175psi
VK740	F_030789	05133AAJ or AJJ	1.2	17.3	30° Model A-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK741	F_030789	05133AAK or AJK	1.2	17.3	60° Model A-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK742	F_030789	05133AAL or AJL	1.2	17.3	90° Model A-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK743	F_030789	05133AAM or AJM	1.4	20.2	120° Model A-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK744	F_030789	05133AAN or AJN	1.4	20.2	140° Model A-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK750	F_030789	05134AAJ or AJJ	2.0	28.8	30° Model A-2X Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK751	F_030789	05134AAK or AJK	2.0	28.8	60° Model A-2X Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK752	F_030789	05134AAL or AJL	2.0	28.8	90° Model A-2X Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK753	F_030789	05134AAM or AJM	2.2	31.7	120° Model A-2X Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK754	F_030789	05134AAN or AJN	2.2	31.7	140° Model A-2X Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A

SIN*	Technical Data Page(s)	Sprinkler Base Part Number	Nominal K-Factor		Sprinkler Model and Type	Maximum Pressure Rating (UL/FM)
			U.S.	metric		
VK760	F_030789	05135AAJ or AJJ	2.8	40.3	30° Model B-2 Spray Nozzle, ½" NPT, Brass or Nickel	N/A
VK761	F_030789	05135AAK or AJK	2.8	40.3	60° Model B-2 Spray Nozzle, ½" NPT, Brass or Nickel	N/A
VK762	F_030789	05135AAL or AJL	2.8	40.3	90° Model B-2 Spray Nozzle, ½" NPT, Brass or Nickel	N/A
VK763	F_030789	05135AAM or AJM	3.3	47.6	120° Model B-2 Spray Nozzle, ½" NPT, Brass or Nickel	N/A
VK764	F_030789	05135AAN or AJN	3.3	47.6	140° Model B-2 Spray Nozzle, ½" NPT, Brass or Nickel	N/A
VK770	F_030789	05136AAJ or AJJ	3.4	49	30° Model C-2 Spray Nozzle, ½" NPT, Brass or Nickel	N/A
VK771	F_030789	05136AAK or AJK	3.4	49	60° Model C-2 Spray Nozzle, ½" NPT, Brass or Nickel	N/A
VK772	F_030789	05136AAL or AJL	3.8	54.8	90° Model C-2 Spray Nozzle, ½" NPT, Brass or Nickel	N/A
VK773	F_030789	05136AAM or AJM	3.9	56.2	120° Model C-2 Spray Nozzle, ½" NPT, Brass or Nickel	N/A
VK774	F_030789	05136AAN or AJN	3.9	56.2	140° Model C-2 Spray Nozzle, ½" NPT, Brass or Nickel	N/A
VK780	F_030789	05137AAJ or AJJ	4.7	67.8	30° Model D-2 Spray Nozzle, ½" NPT, Brass or Nickel	N/A
VK781	F_030789	05137AAK or AJK	4.7	67.8	60° Model D-2 Spray Nozzle, ½" NPT, Brass or Nickel	N/A
VK782	F_030789	05137AAL or AJL	5.0	72.1	90° Model D-2 Spray Nozzle, ½" NPT, Brass or Nickel	N/A
VK783	F_030789	05137AAM or AJM	5.2	75.0	120° Model D-2 Spray Nozzle, ½" NPT, Brass or Nickel	N/A
VK784	F_030789	05137AAN or AJN	5.2	75.0	140° Model D-2 Spray Nozzle, ½" NPT, Brass or Nickel	N/A
VK790	F_051800	01320B	1.5	21.6	Model C-1 Window Sprinkler, 1/4" Orifice, ½" NPT	N/A
VK791	F_051800	01321B	2.1	30.3	Model C-1 Window Sprinkler, 5/16" Orifice, ½" NPT	N/A
VK792	F_051800	01322B	3.0	43.2	Model C-1 Window Sprinkler, 3/8" Orifice, ½" NPT	N/A
VK793	F_051800	01323B	4.3	62	Model C-1 Window Sprinkler, 7/16" Orifice, ½" NPT	N/A
VK794	F_051800	01324B	5.8	83.6	Model C-1 Window Sprinkler, ½" Orifice, ½" NPT	N/A
VK795	F_051800	01325B	7.3	105.2	Model C-1 Window Sprinkler, 5/8" Orifice, 3/4" NPT	N/A
VK796	F_051800	01326B	8.1	117.3	Model C-1 Window Sprinkler, 3/4" Orifice, 3/4" NPT	N/A
VK800	F_051091	07848	-	-	HP Fixed Temperature Release, ½" NPT	250 psi
VK810	F_062104	12867	7.2	103.8	65° Model E Spray Nozzle, ½" NPT	175 psi
VK810	F_062104	12868	5.6	80.6	65° Model E Spray Nozzle, ½" NPT	175 psi
VK810	F_062104	12869	4.1	59.1	65° Model E Spray Nozzle, ½" NPT	175 psi
VK810	F_062104	12870	3.2	46.3	65° Model E Spray Nozzle, ½" NPT	175 psi
VK810	F_062104	12871	2.3	33.2	65° Model E Spray Nozzle, ½" NPT	175 psi
VK810	F_062104	12872	1.8	25.9	65° Model E Spray Nozzle, ½" NPT	175 psi
VK810	F_062104	12873	1.2	17.3	65° Model E Spray Nozzle, ½" NPT	175 psi
VK811	F_062104	12874	7.2	103.8	80° Model E Spray Nozzle, ½" NPT	175 psi
VK811	F_062104	12875	5.6	80.6	80° Model E Spray Nozzle, ½" NPT	175 psi
VK811	F_062104	12876	4.1	59.1	80° Model E Spray Nozzle, ½" NPT	175 psi
VK811	F_062104	12877	3.2	46.3	80° Model E Spray Nozzle, ½" NPT	175 psi
VK811	F_062104	12878	2.3	33.2	80° Model E Spray Nozzle, ½" NPT	175 psi
VK811	F_062104	12879	1.8	25.9	80° Model E Spray Nozzle, ½" NPT	175 psi
VK811	F_062104	12880	1.2	17.3	80° Model E Spray Nozzle, ½" NPT	175 psi
VK812	F_062104	12881	7.2	103.8	95° Model E Spray Nozzle, ½" NPT	175 psi
VK812	F_062104	12882	5.6	80.6	95° Model E Spray Nozzle, ½" NPT	175 psi
VK812	F_062104	12883	4.1	59.1	95° Model E Spray Nozzle, ½" NPT	175 psi
VK812	F_062104	12884	3.2	46.3	95° Model E Spray Nozzle, ½" NPT	175 psi
VK812	F_062104	12885	2.3	33.2	95° Model E Spray Nozzle, ½" NPT	175 psi
VK812	F_062104	12886	1.8	25.9	95° Model E Spray Nozzle, ½" NPT	175 psi
VK812	F_062104	12887	1.2	17.3	95° Model E Spray Nozzle, ½" NPT	175 psi
VK813	F_062104	12888	7.2	103.8	110° Model E Spray Nozzle, ½" NPT	175 psi
VK813	F_062104	12889	5.6	80.6	110° Model E Spray Nozzle, ½" NPT	175 psi
VK813	F_062104	12890	4.1	59.1	110° Model E Spray Nozzle, ½" NPT	175 psi
VK813	F_062104	12891	3.2	46.3	110° Model E Spray Nozzle, ½" NPT	175 psi
VK813	F_062104	12892	2.3	33.2	110° Model E Spray Nozzle, ½" NPT	175 psi
VK813	F_062104	12893	1.8	25.9	110° Model E Spray Nozzle, ½" NPT	175 psi
VK813	F_062104	12894	1.2	17.3	110° Model E Spray Nozzle, ½" NPT	175 psi
VK814	F_062104	12895	7.2	103.8	125° Model E Spray Nozzle, ½" NPT	175 psi
VK814	F_062104	12896	5.6	80.6	125° Model E Spray Nozzle, ½" NPT	175 psi
VK814	F_062104	12897	4.1	59.1	125° Model E Spray Nozzle, ½" NPT	175 psi
VK814	F_062104	12898	3.2	46.3	125° Model E Spray Nozzle, ½" NPT	175 psi
VK814	F_062104	12899	2.3	33.2	125° Model E Spray Nozzle, ½" NPT	175 psi
VK814	F_062104	12900	1.8	25.9	125° Model E Spray Nozzle, ½" NPT	175 psi
VK814	F_062104	12901	1.2	17.3	125° Model E Spray Nozzle, ½" NPT	175 psi
VK815	F_062104	12902	7.2	103.8	140° Model E Spray Nozzle, ½" NPT	175 psi
VK815	F_062104	12903	5.6	80.6	140° Model E Spray Nozzle, ½" NPT	175 psi
VK815	F_062104	12904	4.1	59.1	140° Model E Spray Nozzle, ½" NPT	175 psi
VK815	F_062104	12905	3.2	46.3	140° Model E Spray Nozzle, ½" NPT	175 psi
VK815	F_062104	12906	2.3	33.2	140° Model E Spray Nozzle, ½" NPT	175 psi
VK815	F_062104	12907	1.8	25.9	140° Model E Spray Nozzle, ½" NPT	175 psi
VK815	F_062104	12908	1.2	17.3	140° Model E Spray Nozzle, ½" NPT	175 psi
VK816	F_062104	12909	7.2	103.8	160° Model E Spray Nozzle, ½" NPT	175 psi
VK816	F_062104	12910	5.6	80.6	160° Model E Spray Nozzle, ½" NPT	175 psi
VK816	F_062104	12911	4.1	59.1	160° Model E Spray Nozzle, ½" NPT	175 psi
VK816	F_062104	12912	3.2	46.3	160° Model E Spray Nozzle, ½" NPT	175 psi
VK816	F_062104	12913	2.3	33.2	160° Model E Spray Nozzle, ½" NPT	175 psi
VK816	F_062104	12914	1.8	25.9	160° Model E Spray Nozzle, ½" NPT	175 psi
VK816	F_062104	12915	1.2	17.3	160° Model E Spray Nozzle, ½" NPT	175 psi
VK817	F_062104	12916	7.2	103.8	180° Model E Spray Nozzle, ½" NPT	175 psi
VK817	F_062104	12917	5.6	80.6	180° Model E Spray Nozzle, ½" NPT	175 psi
VK817	F_062104	12918	4.1	59.1	180° Model E Spray Nozzle, ½" NPT	175 psi
VK817	F_062104	12919	3.2	46.3	180° Model E Spray Nozzle, ½" NPT	175 psi
VK817	F_062104	12920	2.3	33.2	180° Model E Spray Nozzle, ½" NPT	175 psi
VK817	F_062104	12921	1.8	25.9	180° Model E Spray Nozzle, ½" NPT	175 psi
VK817	F_062104	12922	1.2	17.3	180° Model E Spray Nozzle, ½" NPT	175 psi
VK824	F_051606	13633	.82	12.0	Model EM Spray Nozzle	175 psi



SIN*	Technical Data Page(s)	Sprinkler Base Part Number	Nominal K-Factor		Sprinkler Model and Type	Maximum Pressure Rating (UL/FM)
			U.S.	metric		
VK825	<a href="#">F_051606</a>	13872	.48	7.0	Model EM Spray Nozzle	175 psi
VK900	<a href="#">F_110503</a>	12493	4.2	57	Coin™ QR Upright (Specific Application), ½" NPT	175 psi
VK901	<a href="#">F_021607</a>	12676AE	4.2	57	Coin™ QR Fusible Element Upright (Specific Application), ½" NPT	175 psi
VK920	<a href="#">N/A</a>	15111	5.6	80.6	Flat Spray QR Pendent Sprinkler, 1/2" NPT (discontinued product)	175 psi
VK922	<a href="#">N/A</a>	15112	8.0	115.2	Flat Spray QR Pendent Sprinkler, 3/4" NPT (discontinued product)	175 psi
VK950	<a href="#">F_081216</a>	20757	5.6	80.6	Coin™ QR Upright (Specific Application), ½" NPT	175 psi

\* The Sprinkler Identification Number (SIN) is stamped on the sprinklers.