



Pressure Switch Identification Chart

Product Type	Product Description	Pressure Switch Part Number*	Factory Setting	Factory Differential
OL Plus Series (1/6 to 1/2 HP)	Our new oil less riser and tank mounted fire protection compressors. <i>Dark Blue in color.</i>	SWP60401U-C	30 psi on / 44 psi off	14 psi
OL Plus Series (3/4 to 2 HP)	Our new oil less riser and tank mounted fire protection compressors. <i>Dark Blue in color.</i>	SWP60601U	30 psi on / 44 psi off	14 psi
OL Series (OBSOLETE)	Our retired oil less riser and tank mounted compressors manufactured before 2012. <i>Light Blue in color.</i>	SWP60401U	27 psi on / 40 psi off	13 psi
LT Series	Lubricated Tank mounted air compressors	SWP60114	45 psi on / 60 psi off	15 psi
AMD-2	Air Maintenance Device with pressure switch.	SWP60113	30 psi on / 40 psi off	10 psi
Low Pressure OL Plus Series	Low Pressure version of our oil less riser mounted air compressors.	SWP60304-H	13 psi on / 18 psi off	5 psi
Dry Air Pac	Compressor Dryer Package for freezing conditions.	SWP60602	80 psi on / 100 psi off	20 psi
High Pressure OL Plus Series	High Pressure version of our oil less riser and tank mounted air compressors.	SWP60602	80 psi on / 100 psi off	20 psi
High Pressure LT Series	High Pressure version of our lubricated tank mounted air compressors.	SWP60602	80 psi on / 100 psi off	20 psi

* This information is subject to change without notice. Consult factory for most up to date information.