

TABLE OF CONTENTS

TotalPac®3 – Introduction.....K-1
 TotalPac®3 – Preaction Systems.....K-2
 TotalPac®3 – Deluge, Wet, and Dry Systems.....K-3
 TotalPac®3 – Firecycle® III and SureFire® Systems.....K-4
 TotalPac®3 – System Options / Release Control Panel OptionsK-5
 TotalPac®3 – Air Supply Options.....K-6
 TotalPac®3 – Terms and ConditionsK-7

Notes

1. Refer to Viking technical data pages for complete product specifications. You may print or download technical data by visiting www.vikinggroupinc.com.
2. List prices effective January 11, 2021. Supersedes January 2020 list price book.
3. All sales by Viking are subject to the terms & conditions found on the last page of this book.

SureFire® and Firecycle® are registered trademarks of The Viking Corporation.



NEW - TOTALPAC®3 Integrated Fire Protection Systems

Introduction:

Pricing of the TotalPac3 Product Line are priced by adding various options together until a complete unit is obtained.

A basic system now includes the system valve, its releasing trim and its supporting assembly, whether it is a skid, a remote-controlled T3ACCELE1D

cabinet without control panel or a self-contained unit with control panel. These are all included under a single part number.

The price list now resembles a matrix which facilitates its use. It is divided into 10 sections and is consistent with the User Manuals:

1. Preaction Systems (Non, Single & Double Interlock);
2. Deluge Systems;
3. Wet Pipe Systems;
4. Dry Pipe Systems (both normal & HP);
5. Cycling Systems (Firecycle III);
6. Surefire Systems.

Followed by:

7. System Options (Shut-off Valve, FD Connection, etc.);
8. VFR-400 Control Panel Options (zones, relays, batteries, etc.);
9. Air Supplies (the usual 4 styles – A,B,C & D), and then,
10. Air Supply Options (Dehydrator, Accelerator, etc.).

To order a TotalPac3:

First, select the type of system required (preaction, deluge, dry, etc...). Then, choose the style of system required (skid mounted, remote controlled or self-contained) and its release system (electric, pneumatic, etc.). Finally, follow this line to the proper part number under the column of the system size (TotalPac3 units are available in 6 sizes: 1½", 2", 3", 4", 6" and 8" diam.). This is the part number that should be ordered. Add the required system options to complete your order.

The Configuration/order Form (doc. # FM-08CD-0-17-D) uses the same format as the price list.

Provided are additional details on the three styles of TotalPac3 units available:

- **Skid Mounted Units:** Skid Units include only the basic Valve Trim and its required Releasing Trim. Electrical components have to be wired on-site by the contractor. Grooved or flanged connections are provided for water supply, drain and system riser. Remote releasing control panel and air compressor (if required) have to be purchased separately (*they are not provided by FireFlex Systems Inc.*) and installed by the contractor on-site. Every Skid Unit is supplied with its own User Manual and is also serialized for after sales support. Serial Number format is TOTSxxxx.

- **Remote Controlled Units:** These units are composed of the basic Valve, Trim and Releasing Trim, enclosed in a sturdy 14-gauge steel cabinet with one or two front doors and a contractor field wiring junction box on top of the cabinet. All electrical components are factory wired to the field wiring terminal strip. Wiring schematics are included on the inside of the front doors. Grooved or flanged connections are provided for water supply, drain and system riser. Four different air supply options are available, and factory assembled. Remote releasing control panel, if required, has to be purchased separately (*they are not provided by FireFlex Systems Inc.*) and installed by the contractor on-site. Every Remote-Controlled Unit is supplied with a User Manual and is serialized for after sales support. Serial Number format is TOT3xxxx.

- **Self-Contained Units:** These units are composed of a Remote-Controlled Unit as described above, plus a Release Control Panel Enclosure mounted on top of the cabinet. All electrical components are factory wired to the Viking VFR-400 Control Panel, with wiring schematics included on the inside of the front doors. Grooved or flanged connections are provided for water supply, drain and system riser. Four different air supply options are available, and factory assembled.

Every self-contained unit is supplied with a User Manual and is serialized for after sales support. Serial Number format is TOT3xxxx.

Refer to the Price List for various options available with each style & system type.

NEW - TOTALPAC®3 Integrated Fire Protection Systems

Preaction Systems:

SYSTEM TYPE	STYLE	RELEASE	SYSTEM SIZE						
			1½"	2"	3"	4"	6"	8"	
PREACTION NON INTERLOCK	Skid Mounted	Electric	T3PNELSK15 \$24,026	T3PNELSK20 \$26,919	T3PNELSK30 \$30,093	T3PNELSK40 \$35,723.46	T3PNELSK60 \$41,791	N/A	
		Pneumatic	T3PNPNSK15 \$22,381	T3PNPNSK20 \$25,170	T3PNPNSK30 \$28,338	T3PNPNSK40 \$33,975	T3PNPNSK60 \$40,060	N/A	
	Without Panel (Remote)	Electric	T3PNELNP15 \$32,892	T3PNELNP20 \$36,424	T3PNELNP30 \$39,556	T3PNELNP40 \$45,140	T3PNELNP60 \$51,164	T3PNELNP80 \$74,878	
		Pneumatic	T3PNPNNP15 \$31,247	T3PNPNNP20 \$34,592	T3PNPNNP30 \$37,790	T3PNPNNP40 \$42,505	T3PNPNNP60 \$48,564	T3PNPNNP80 \$73,330	
	With VFR-400 – 120V/60Hz	Electric	T3PNELWP15 \$40,355	T3PNELWP20 \$43,893	T3PNELWP30 \$47,037	T3PNELWP40 \$52,059	T3PNELWP60 \$58,007	T3PNELWP80 \$83,155	
	PREACTION SINGLE INTERLOCK	Skid Mounted	Electric	T3PSELSK15 \$21,603	T3PSELSK20 \$24,552	T3PSELSK30 \$27,720	T3PSELSK40 \$33,357	T3PSELSK60 \$39,436	N/A
			Pneumatic	T3PSPNSK15 \$21,433	T3PSPNSK20 \$24,655	T3PSPNSK30 \$27,817	T3PSPNSK40 \$33,466	T3PSPNSK60 \$39,544	N/A
		Without Panel (Remote)	Electric	T3PSELNP15 \$30,525	T3PSELNP20 \$34,069	T3PSELNP30 \$37,207	T3PSELNP40 \$42,383	T3PSELNP60 \$48,466	T3PSELNP80 \$71,389
			Pneumatic	T3PSPNNP15 \$30,616	T3PSPNNP20 \$34,107	T3PSPNNP30 \$37,310	T3PSPNNP40 \$42,031	T3PSPNNP60 \$48,930	T3PSPNNP80 \$71,839
With VFR-400 – 120V/60Hz		Electric	T3PSELWP15 \$37,380	T3PSELWP20 \$40,846	T3PSELWP30 \$44,127	T3PSELWP40 \$48,056	T3PSELWP60 \$54,712	T3PSELWP80 \$79,656	
PREACTION DOUBLE INTERLOCK Note: NYFD Accepted & FM Approved for use in refrigerated areas only.		Skid Mounted	Elect-Pnelect.	T3PDEPSK15 \$21,660	T3PDEPSK20 \$24,547	T3PDEPSK30 \$27,721	T3PDEPSK40 \$33,358	T3PDEPSK60 \$39,442	N/A
			Elect-Pneum.	T3PDPASK15 \$22,247	T3PDPASK20 \$25,366	T3PDPASK30 \$28,528	T3PDPASK40 \$34,170	T3PDPASK60 \$40,255	N/A
			Pneum-Pneum.	T3PDPPSK15 \$21,768	T3PDPPSK20 \$25,282	T3PDPPSK30 \$28,438	T3PDPPSK40 \$34,093	T3PDPPSK60 \$40,166	N/A
		Without Panel (Remote)	Elect-Pnelect.	T3PDEPNP15 \$30,526	T3PDEPNP20 \$34,075	T3PDEPNP30 \$37,203	T3PDEPNP40 \$42,467	T3PDEPNP60 \$48,544	T3PDEPNP80 \$71,388
	Elect-Pneum.		T3PDPANP15 \$31,339	T3PDPANP20 \$34,876	T3PDPANP30 \$38,026	T3PDPANP40 \$42,641	T3PDPANP60 \$48,335	T3PDPANP80 \$73,075	
	Pneum-Pneum.		T3PDPPNP15 \$30,634	T3PDPPNP20 \$33,735	T3PDPPNP30 \$37,077	T3PDPPNP40 \$41,392	T3PDPPNP60 \$47,861	T3PDPPNP80 \$73,444	
	With VFR-400 – 120V/60Hz	Elect-Pnelect.	T3PDEPWP15 \$37,474	T3PDEPWP20 \$40,925	T3PDEPWP30 \$44,193	T3PDEPWP40 \$49,043	T3PDEPWP60 \$55,109	T3PDEPWP80 \$79,660	
		Elect-Pneum.	T3PDPAWP15 \$37,956	T3PDPAWP20 \$41,211	T3PDPAWP30 \$44,320	T3PDPAWP40 \$48,816	T3PDPAWP60 \$55,108	T3PDPAWP80 \$80,900	

NEW - TOTALPAC®3 Integrated Fire Protection Systems

Deluge Systems:

SYSTEM TYPE	STYLE	RELEASE	SYSTEM SIZE					
			1½"	2"	3"	4"	6"	8"
DELUGE	Skid Mounted	Electric	T3DEELSK15 \$20,706	T3DEELSK20 \$24,163	T3DEELSK30 \$27,141	T3DEELSK40 \$32,772	T3DEELSK60 \$37,710	N/A
		Pneumatic	T3DEPNK15 \$20,721	T3DEPNK20 \$24,265	T3DEPNK30 \$27,238	T3DEPNK40 \$32,875	T3DEPNK60 \$37,813	N/A
		Hydraulic	T3DEHYSK15 \$18,644	T3DEHYSK20 \$21,652	T3DEHYSK30 \$24,625	T3DEHYSK40 \$30,255	T3DEHYSK60 \$35,200	N/A

SYSTEM TYPE	STYLE	RELEASE	SYSTEM SIZE					
			1½"	2"	3"	4"	6"	8"
DELUGE	Without Panel (Remote)	Electric	T3DEELNP15 \$30,182	T3DEELNP20 \$33,519	T3DEELNP30 \$36,545	T3DEELNP40 \$41,384	T3DEELNP60 \$46,321	T3DEELNP80 \$67,788
		Pneumatic	T3DEPNNP15 \$30,214	T3DEPNNP20 \$33,179	T3DEPNNP30 \$36,324	T3DEPNNP40 \$40,761	T3DEPNNP60 \$47,039	T3DEPNNP80 \$68,266
		Hydraulic	T3DEHYNP15 \$27,684	T3DEHYNP20 \$31,198	T3DEHYNP30 \$34,153	T3DEHYNP40 \$39,429	T3DEHYNP60 \$44,342	T3DEHYNP80 \$67,057
	With VFR-400 – 120V/60Hz	Electric	T3DEELWP15 \$37,107	T3DEELWP20 \$40,055	T3DEELWP30 \$43,076	T3DEELWP40 \$48,056	T3DEELWP60 \$52,969	T3DEELWP80 \$76,052

Wet Pipe Systems:

WET PIPE	Skid Mounted	N/A	N/A	N/A	T3WETESK30 \$13,135	T3WETESK40 \$16,195	T3WETESK60 \$18,266	N/A
	In Cabinet	N/A	N/A	N/A	T3WETENP30 \$22,031	T3WETENP40 \$25,058	T3WETENP60 \$27,106	T3WETENP80 \$34,450
System Options:	Constant Pressure Trim	T3CONPRESS POA		Excess Pressure Pump 1/3 HP (120V/60Hz)		T3WETEPP03 POA		
	Retard Chamber	T3WETRET00 POA		Excess Pressure Pump 1/2 HP (120V/60Hz)		T3WETEPP05 POA		

Dry Pipe Systems:

DRY PIPE 175 psi	Skid Mounted	N/A	N/A	N/A	N/A	T3DRYESK40 \$20,643	T3DRYESK60 \$24,011	N/A
	In Cabinet (Remote)	N/A	N/A	N/A	N/A	T3DRYENP40 \$29,057	T3DRYENP60 \$32,984	N/A
HP DRY PIPE 250 psi	Skid Mounted	N/A	T3DHPESK15 POA	T3DHPESK20 POA	T3DHPESK30 POA	T3DHPESK40 POA	T3DHPESK60 POA	N/A
	In Cabinet (Remote)	N/A	T3DHPENP15 \$30,536	T3DHPENP20 \$34,481	T3DHPENP30 \$38,102	T3DHPENP40 \$43,436	T3DHPENP60 \$50,271	T3DHPENP80 \$70,499

NEW - TOTALPAC®3 Integrated Fire Protection Systems

Firecycle® III Systems:

SYSTEM TYPE	STYLE	RELEASE	SYSTEM SIZE					
			1½"	2"	3"	4"	6"	8"
PREACTION SINGLE INTERLOCK	Skid Mounted	Firecycle III	T3FSINSK15 \$30,325	T3FSINSK20 \$34,999	T3FSINSK30 \$38,814	T3FSINSK40 \$45,352	T3FSINSK60 \$52,710	N/A
	Without Panel (Remote)		T3FSINNP15 \$39,326	T3FSINNP20 \$44,415	T3FSINNP30 \$48,206	T3FSINNP40 \$54,685	T3FSINNP60 \$61,977	T3FSINNP80 \$78,845
	With VFR-400 – 120V/60Hz		T3FSINWP15 \$47,575	T3FSINWP20 \$52,882	T3FSINWP30 \$57,105	T3FSINWP40 \$62,839	T3FSINWP60 \$69,493	T3FSINWP80 \$86,712
PREACTION DOUBLE INTERLOCK	Skid Mounted	Firecycle III	T3FDOUSK15 \$30,325	T3FDOUSK20 \$34,999	T3FDOUSK30 \$38,814	T3FDOUSK40 \$45,352	T3FDOUSK60 \$52,710	N/A
	Without Panel (Remote)		T3FDOUNP15 \$39,326	T3FDOUNP20 \$44,415	T3FDOUNP30 \$48,206	T3FDOUNP40 \$54,685	T3FDOUNP60 \$61,977	T3FDOUNP80 \$78,845
	With VFR-400 – 120V/60Hz		T3FDOWP15 \$47,575	T3FDOWP20 \$52,882	T3FDOWP30 \$57,105	T3FDOWP40 \$62,839	T3FDOWP60 \$69,493	T3FDOWP80 \$86,769

SureFire® Fail Safe Preaction Systems:

SYSTEM TYPE	STYLE	RELEASE	SYSTEM SIZE					
			1½"	2"	3"	4"	6"	8"
PREACTION SINGLE INTERLOCK	Skid Mounted	Surefire	T3SFSISK15 \$28,155	T3SFSISK20 \$31,568	T3SFSISK30 \$34,996	T3SFSISK40 \$41,058	T3SFSISK60 \$47,592	N/A
	Without Panel (Remote)		T3SFSINP15 \$37,227	T3SFSINP20 \$41,031	T3SFSINP30 \$44,406	T3SFSINP40 \$50,421	T3SFSINP60 \$56,894	T3SFSINP80 \$76,851
	With VFR-400 - 120V/60Hz		T3SFSIWP15 \$44,719	T3SFSIWP20 \$48,517	T3SFSIWP30 \$51,892	T3SFSIWP40 \$57,522	T3SFSIWP60 \$64,049	T3SFSIWP80 \$84,202
PREACTION DOUBLE INTERLOCK <small>Note: NYFD & FM Approved for use in refrigerated areas only.</small>	Skid Mounted	Surefire	T3SFDOSK15 \$28,155	T3SFDOSK20 \$31,370	T3SFDOSK30 \$34,780	T3SFDOSK40 \$40,811	T3SFDOSK60 \$47,319	N/A
	Without Panel (Remote)		T3SFDONP15 \$37,026	T3SFDONP20 \$40,824	T3SFDONP30 \$44,196	T3SFDONP40 \$50,187	T3SFDONP60 \$55,543	T3SFDONP80 \$76,851
	With VFR-400 - 120V/60Hz		T3SFDOWP15 \$44,520	T3SFDOWP20 \$48,294	T3SFDOWP30 \$51,676	T3SFDOWP40 \$57,217	T3SFDOWP60 \$63,740	T3SFDOWP80 \$84,180

NEW - TOTALPAC®3 Integrated Fire Protection Systems

System Options:

Shut-off Valve & Sight Glass (Not available for Wet & Dry Pipe systems)	T3SHUTV015 \$1,697	T3SHUTV020 \$1,948	T3SHUTV030 \$2,183	T3SHUTV040 \$2,249	T3SHUTV060 \$2,685	N/A
Fire Department Connection (Always on right hand side)	T3FIRDPT15 \$561	T3FIRDPT20 \$578	T3FIRDPT30 \$660	T3FIRDPT40 \$758	T3FIRDPT60 \$1,010	N/A
Semi-Flanged Inlets & Outlet:	T3SEMFLG15 \$1,382	T3SEMFLG20 \$1,262	T3SEMFLG30 \$1,470	T3SEMFLG40 \$1,666	T3SEMFLG60 \$1,967	T3SEMFLG80 \$2,705
Full-Flanged Inlets & Outlet:	PRICE ON REQUEST ONLY					
Elevator Option	T3ELEVATOR			PRICE ON REQUEST ONLY SPECIAL CONDITIONS APPLY		
Anti Column device	T3ANTCOLD1			\$1,381		
Galvanized Main Inlet & Riser	T3GALVOPTI			\$1,351		
OSHPD Seismic Option	T3SISMIQ00			\$1,604.56		

VFR-400 Releasing Panel Options:

Available with 120V / 60Hz or 220V / 50Hz

Emergency Batteries:	Standard Systems:	7 AH (Included with unit, use for replacement only) T3BAT02407 \$300	12 AH (FM's 90 Hrs Stand-by) T3BAT02412 \$529
	Surefire & Firecycle III Systems:	12 AH (Included with unit, use for replacement only) T3BAT02412 \$529	17 AH (FM's 90 Hrs Stand-by) T3BAT02417 POA
VFR-400 Panel Options:	L.A. Auxiliary Contacts – T3LAOPTION \$134	Chicago Auxiliary Contacts – T3CHOPTION \$134	NYFD Kit – T3VFRPNYOP \$404 (Class A Modules included do not duplicate)
	Rem. Annunciator – T3VFRP4410 \$1,298		
	Class "A" Initiating Ccts – T3VFRPCA2Z \$404	Class "A" Indicating Ccts – T3VFRPCAM2 \$518	Relay Module – T3OPTARM44 \$1,386

NEW - TOTALPAC®3 Integrated Fire Protection Systems

Air Supplies:

Air Supplies for Skids (Trim only – NO compressor)	For Preaction – Surefire Firecycle III & HP Dry Pipe	Deluge Pneum. Release	Single Pneum. & Double Int'lk Pneum-Pneum. Release
	T3ARTITSK1 \$1,294	T3ARTITSK2 \$1,072	T3ARTITSK3 \$2,057

Air Supplies for Cabinets	Style "A" (Tankless Air Compressor)						Style "B" Air Pressure Maintenance Device for Sprinkler Piping	Style "C" Air Pressure Maintenance Device for Pilot Line	Style "D" Air Shut-off Valve, Pressure Gauge, & Pressure Switch Only
	1/6 HP	1/3 HP	1/2 HP	1 HP	1 1/2 HP (8" unit only)	2 HP (8" unit only)			
120 V / 60 Hz:	T3AIRK0A02 \$5,404	T3AIRK0A03 \$6,191	T3AIRK0A05 \$7,054	T3AIRK0A10 \$8,685	T3AIRK0A15 \$11,494	T3AIRK0A20 POA	T3AIRK0B00 \$2,531	T3AIRK0C00 \$2,419	T3AIRK0D00 \$727
220V / 50 Hz	T3AIRK2A02 \$6,083	T3AIRK2A03 \$7,095	T3AIRK2A05 \$8,414	T3AIRK2A10 \$9,660	T3AIRK2A15 POA	N/A			

Notes:

1. Style "A" Air Supply cannot be mixed with Style "B".
2. In the case of a Preaction System with Pilot Line, order either one Style "A" with one Style "C" if you need a tankless air compressor in the cabinet for the sprinklers piping, OR, one Style "B" and one Style "C" if you want both air supplies to be located outside the system cabinet.
3. Pilot Line Air Supply will always be provided by a source located outside the TP3 Cabinet, supplied by others (not FireFlex).
4. Air Supply Style "D" is used when air supply and regulation is provided by others, as is the case with plant air, or with refrigerated areas when a dry air supply as described in NFPA-13 is required.
5. 1 HP Air compressor available on 4" & 6" systems only.
6. 1 ½ HP & 2 HP Air compressors available on 8" systems only.

Air Supply Options:

Accelerator E-1	Without Anti-flood Device (For Preaction, Pneum. Rel. Pilot Line & HP Dry only)	With Anti-flood Device (For Standard Dry Pipe only)
	T3ACCELE1P \$3,546	T3ACCELE1D \$5,261
Dehydrator	T3DEHYDRAT \$3,890	

NEW - TOTALPAC®3 Integrated Fire Protection Systems

Terms and Conditions

This price list should be used in conjunction with the VIKING TotalPac3 Configuration/Order Form (FM-08CD-0-17-D latest revision).

All prices are NET and are indicated in US dollars, FOB our plant in Boisbriand, Quebec (Canada). For special discounts or configurations, please contact FireFlex Systems Customer Service.

Listings and Approvals: Most TotalPac3 Configurations in our product range are cUL_{US} Listed & FM Approved as factory-built complete units. Any system modification, to meet project specs or local AHJ requirements, ordered as a custom-built system will void the Listing on the TotalPac3 as an assembly but individual components Listings/Approvals will remain.

Special Order Item: Every TotalPac3 Unit is a Special-Order Item which is built to order. It can therefore not be cancelled nor returned without FireFlex Systems explicit consent or authorization.

Returns & Credits: The following conditions shall apply to all TotalPac3 units returned for credit:

- Unit(s) shall be of current design, three months old maximum after shipping date from the factory;
- Unit(s) shall still be in its (their) original packing (never unpacked), unused and not installed. Any unit not in this condition is subject to additional charges to cover inspection, handling, repackaging, refurbishment, or any other expenses incurred by FireFlex Systems in accepting the unit(s).
- The customer is responsible for freight charges to return overstocked unit(s), unit(s) no longer required, or ordered by mistake. Any damage incurred in transit will be deducted from the credit value.

NOTE: An RMA Number shall be obtained from FireFlex' Customer Service PRIOR to returning any unit. Please provide unit(s) serial number(s) as indicated on the shipping label of the unit(s) (format: TOTSxxxx or TOT3xxxx) as well as the address for us to make arrangements for pick-up.

Please note that a minimum restocking charge of \$ 1,500.00 is applicable on all TotalPac3 returns. Systems older than 3 months after date of shipment will NOT be accepted for credit.

Upon receiving returned unit(s), FireFlex Systems will inspect each unit. If any damage is found, the credit amount will be adjusted accordingly.

Contractor must ascertain the unit is returned in its original packing, including the internal plastic liner. This liner protects the unit finish against abrasion damage during transport.

Warranty: FireFlex Systems provides warranty on all TotalPac3 Units for a period of 1 (one) year from time of shipping. Warranty does not cover labor. We will replace any component found defective at no charge during this period but will NOT reimburse labor charges incurred by the contractor. In the case of unauthorized modification of, or tampering with the unit, the warranty is void.

The warranty on batteries warranty is limited to 3 (three) months. Refer to the terms of our Standard Warranty for all details (provided with every TotalPac3 User's Manual).