

Residential | Freedom® VK494 Flat Plate Concealed Pendent Sprinkler

The Freedom[®] Model VK494 is Viking's next generation residential concealed pendent sprinkler, featuring "ultra-fast" glass bulb technology. The 4.9 K-factor sprinkler is the first residential concealed sprinkler with the same cULus Listed flow rates for both ordinary and intermediate temperature ratings. As a result, you can now standardize on an intermediate temperature-rated sprinkler without sacrificing either performance or aesthetics.

Rated for ambient temperatures up to 150°F, the intermediate temperature VK494 model offers greater flexibility when positioning sprinklers around potential heat sources.

- Flat plate concealed design with a nearly unlimited variety of custom color finishes, for a smooth ceiling look that doesn't compromise aesthetics.
- Available in both ordinary (155°F) and intermediate (200°F) temperature ratings.
- Minimum achievable flow rates for 16' x 16', 18' x 18', and 20' x 20' coverage areas at both temperature ratings (0.05 gpm/sq. ft. density requirements).
- Because VK494 ordinary and intermediate temperature flow rates are identical, you can standardize on the intermediate temperature models, simplifying inventory and reducing job site confusion.

Contact your local Viking SupplyNet office to place an order today!

Model Number:	VK494
Base Part Number:	20759
Listings/Approvals:	cULus
K-factor:	4.9 (70.6)
Connection:	1/2" NPT
Temperature:	155°F (68°C) 200°F (93°C)
Operating Element:	Glass bulb
Finish:	Brass
Item Price Group:	V182

MKT-0005

The Viking Corporation 210 N Industrial Park Drive, Hastings, Michigan 49058

Telephone: (800) 968-9501 Email: products@vikingcorp.com www.vikinggroupinc.com



Trusted above all.™