

## Concealed 5.6K pendent sprinkler offers easy install

The FM Approved and cULus Listed VK4621 Quick and Standard Response concealed pendent sprinkler is a 5.6K commercial sprinkler protecting Light and Ordinary hazards, utilizing a glass bulb operating element.

Features and advantages of Viking's VK4621 Concealed Pendent Sprinkler:

- Features a compatible wrench for easy installation
- Protective cap is designed to withstand rough usage and protect the sprinkler from paint overspray
- cULus Listed as a Quick Response sprinkler and FM Approved as a Standard Response sprinkler for both light and ordinary occupancies
- The sprinkler consists of a permanently mounted and threaded adapter cup designed to be installed with a low-profile cover assembly that provides up to 1/2" (13 mm) of vertical adjustment
- Available in both brass and an Electroless Nickel PTFE (ENT) coating for environments in which corrosion is more likely to occur

For more information, please contact your Viking sales representative or visit our website at **vikinggroupinc.com**.

## **TECHNICAL SPECIFICATIONS**

Model Number: VK4621

Base Part Number: 24682

**Listings/Approvals:** FM Approved

K-factor: K5.6 (80.6)

Connection: 1/2" NPT
15 mm BSPT

Temperatures: 155°F (68°C)

175°F (79°C) 200°F (93°C)

Operating Element: Glass Bulb

Finish: Brass, ENT Coated

Item Price Group: V129

Occupancy/Hazard: Light & Ordinary

Technical Datasheet: F\_092121

Installation Wrench: 23143

## **DIGITAL TOOLS**



Viking's revolutionary Sprinkler Selector ensures that you can find the right sprinkler for the job — every time. Get started by visiting webtools.vikingcorp.com/sprinklerselector.

MKT-0011

General reference only. Prior to the design, layout, and/or installation of any sprinkler system, please refer to Viking's technical documentation and consult with the AHJ.





