



Concealed Pendent | VK4621 Concealed Pendent Sprinkler

Viking's VK4621 Quick and Standard Response concealed pendent sprinkler is designed for installation on concealed pipe systems where the appearance of a smooth ceiling is desired. Installation has never been easier, now that the innovative wrench and cap have been re-imagined. The wrench allows the VK4621 to be installed with its protective cap still in place, and prevents overspray.

- Advanced, lightweight reinforced nylon wrench allows for installation with protective cap in place.
- Protective cap is designed to withstand rough usage and protect the sprinkler from paint overspray.
- cULus Listed as a Quick Response sprinkler and FM Approved as a Standard Response sprinkler for both light and ordinary occupancies.
- The sprinkler consists of a permanently mounted and threaded adapter cup designed to be installed with a low-profile cover assembly that provides up to 1/2" (13 mm) of vertical adjustment.
- Available in both brass and an Electroless Nickel PTFE (ENT) coating for environments in which corrosion is more likely to occur.
- Innovative cap removal tool enables contractors to finish the job from the ground.
- Limited time offer: each box will be shipped with a free wrench!

Contact your local Viking SupplyNet team to place an order today!

The Viking Corporation
www.vikinggroupinc.com

Trusted above all.™

Base Part Number: 24682

Listings/Approvals: FM Approved
cULus Listed

K-factor: 5.6 (80.6)

Connection: 1/2" NPT
15 mm BSPT

Temperature: 155°F (68°C)
175°F (79°C)
200°F (93°C)

Operating Element: Glass Bulb

Finish: Brass, ENT Coated

Item Price Group: V129

Occupancy/Hazard: Light and Ordinary

Technical Datasheet: F_092121

Installation Wrench: 24339

Cap Removal Tool: 24340

MKT-0011

General reference only. Prior to the design, layout, and/or installation of any sprinkler system, please refer to Viking's technical documentation and consult with the AHJ.



VIKING®