



COIN® VK950
Interstitial Space
Quick Response
5.6 K-factor

Protect Combustible Concealed Spaces Without Draft Curtains

Viking's enhanced cULus Listing for the 5.6 (80) K-factor quick response COIN® sprinkler allows the sprinkler to protect combustibles concealed spaces without the use of draft curtains in most applications. This makes it an ideal replacement for competitive sprinklers that have more stringent and expensive draft curtain requirements.

- No draft curtains required when:
 - Sprinkler spacing is up to 16' X 16' (4,9 m X 4,9 m) for truss construction with top chord member on face (not on edge) for wet or dry systems.
 - Sprinkler spacing is up to 14' X 14' (4,3 m X 4,3 m) for trusses with top chord member on edge or solid wood joists for wet systems.
- For use in concealed spaces up to 60" in height and roof pitches up to 2/12.
- Remote area design calculation of 1,000 square feet or six sprinklers, whichever is greater.
- Listed for use with Viking BlazeMaster® CPVC.
- Available with a corrosion resistant ENT coating.

Model Number:	VK950
Base Part Number:	20757
Listings/Approvals:	cULus Listed
K-factor:	5.6 (80)
Connection:	1/2" NPT 15 mm BSP
Temperature:	200°F (93°C)
Operating Element:	Glass Bulb
Finish:	Brass, Electroless Nickel PTFE (ENT)
Item Price Group:	V172
Occupancy/Hazard:	Special
Technical Datasheet:	F_081216

MKT-0014

General reference only. Prior to the design, layout, and/or installation of any sprinkler system, please refer to Viking's technical documentation and consult with the AHJ.

Contact your local Viking SupplyNet to place an order today!

The Viking Corporation

5150 Beltway Dr. SE, Caledonia, MI 49316

Telephone: (269) 945-9501

www.vikinggroupinc.com

Trusted above all.™

