



Viking Plastics | InstaSeal® CPVC Sprinkler Head Adapter

Viking's new sprinkler head adapter allows for installation without the use of thread tape or sealant, making installation a breeze.

Manufactured with BlazeMaster® CPVC compound, the proven leader in CPVC technology, the InstaSeal® head adapter allows for fast and easy sprinkler installation.

- Features full brass threads with an EPDM seat for efficient installation.
- To install, hand tighten until the sprinkler makes contact with the adapter's rubber seat. An additional 1/2 to 1-1/4 turn by hand or with the recommended wrench completes the installation.
- The final position of the sprinkler is adjustable, making pendent or horizontal sidewall sprinkler alignment simple.

Connect with Confidence with Viking Plastics. Viking's industry-leading line of CPVC sprinkler pipe and fittings now includes three unique sprinkler head adapters, providing flexible options for unique fire protection challenges. And when you install CPVC sprinkler piping from Viking Plastics, you are assured of quality in every link of the supply chain - from manufacturing, to distribution, and to the job site.

Threaded InstaSeal® Fittings:

V5003SBG, S x FNPSH Adapter
V50032SBG, SPG x FNPSH Adapter

Adapter Sizes:

3/4" x 1/2" (19 x 13 mm)
1" x 1/2" (25 x 13 mm)

Item Price Group:

SR217

InstaSeal® adapters can be used with sprinklers having a K-factor of 5.8 (83.6 metric) or less.

MKT-0054

General reference only. Prior to the design, layout, and/or installation of any sprinkler system, please refer to Viking's technical documentation and consult with the AHJ.

Freedom
Residential Fire Sprinkler Systems

Contact your local Viking SupplyNet team to place an order today!

The Viking Corporation

210 N. Industrial Park Drive, Hastings, MI 49058

Telephone: (269) 945-9501

www.vikinggroupinc.com

Trusted above all.™

VIKING