



**TABLE OF CONTENTS**

Institutional – VK426/VK427, VK650/VK651 5.6 (81) K factor, flush pendent/flush horizontal sidewall... E-1  
 Model V-BB specific application attic sprinkler - VK684, VK685, VK686, VK681, VK682, VK683 ..... E-2  
 Model V-SD specific application attic sprinkler - VK693, VK694, VK695 ..... E-2  
 Attic upright specific application sprinkler – VK696, VK697..... E-2  
 Model V-HIP specific application attic sprinkler – VK660 ..... E-2  
 Model V-EP specific application attic sprinkler – VK690 ..... E-2  
 Combustible Interstitial Space - VK900, VK950, COIN®, upright..... E-3  
 Window Sprinklers – VK960, VK962 pendent vertical sidewall and horizontal sidewall ..... E-3

**Notes**

1. Unless otherwise indicated, all cover plates and escutcheons are sold separately.
2. Cover plates, escutcheons, and sprinklers are available in custom colors at an additional charge. See page F-8 for details.
3. Refer to Viking technical data pages for complete product specifications. You may print or download technical data by visiting [www.vikinggroupinc.com](http://www.vikinggroupinc.com).
4. List prices effective January 11, 2021. Supersedes January 2020 list price book.
5. All sales by Viking are subject to the Terms & Conditions found on the last page of this book.

*COIN® is a registered trademark of The Viking Corporation*  
*Micromatic® is a registered trademark of The Viking Corporation*



**Institutional**  
**Quick Response**  
**Standard Coverage**  
**Fusible Link**  
**Flush Pendent**

**SIN:** VK426  
**K Factor:** 5.6 (81)  
**Thread Size:** 1/2 inch NPT  
**Base Part #:** 19663

Finish	Temp	Part #	IPG	List Price
Polished Chrome	165°F	19663FC	V173	\$103.88
Polished Chrome	205°F	19663FE	V173	\$103.88
Painted White	165°F	19663MC/W	V173	\$103.88
Painted White	205°F	19663ME/W	V173	\$103.88
Painted Gray	165°F	19663MC/RAL9006	V173	\$103.88
Painted Gray	205°F	19663ME/RAL9006	V173	\$103.88
Socket Wrench		22847MB	V207	\$261.28



**Institutional**  
**Quick Response**  
**Standard Coverage**  
**Fusible Link**  
**Flush Horizontal Sidewall**

**SIN:** VK427  
**K Factor:** 5.6 (81)  
**Thread Size:** 1/2 inch NPT  
**Base Part #:** 22885

Finish	Temp	Part #	IPG	List Price
Polished Chrome	165°F	22885FC	V173	\$119.86
Polished Chrome	205°F	22885FE	V173	\$119.86
Painted White	165°F	22885MC/W	V173	\$119.86
Painted White	205°F	22885ME/W	V173	\$119.86
Painted Gray	165°F	22885MC/RAL9006	V173	\$119.86
Painted Gray	205°F	22885ME/RAL9006	V173	\$119.86
Socket Wrench		22847MB	V207	\$261.28



**Institutional**  
**Quick Response**  
**Extended Coverage**  
**Fusible Link**  
**Flush Pendent**

**SIN:** VK650  
**K Factor:** 5.6 (81)  
**Thread Size:** 1/2 inch NPT  
**Base Part #:** 19876

Finish	Temp	Part #	IPG	List Price
Polished Chrome	165°F	19876FC	V173	\$111.87
Polished Chrome	205°F	19876FE	V173	\$111.87
Painted White	165°F	19876MC/W	V173	\$111.87
Painted White	205°F	19876ME/W	V173	\$111.87
Painted Gray	165°F	19876MC/RAL9006	V173	\$111.87
Painted Gray	205°F	19876ME/RAL9006	V173	\$111.87
Socket Wrench		22847MB	V207	\$261.28



**Institutional**  
**Quick Response**  
**Extended Coverage**  
**Fusible Link**  
**Flush Horizontal Sidewall**

**SIN:** VK651  
**K Factor:** 5.6 (81)  
**Thread Size:** 1/2 inch NPT  
**Base Part #:** 22884

Finish	Temp	Part #	IPG	List Price
Polished Chrome	165°F	22884FC	V173	\$127.85
Polished Chrome	205°F	22884FE	V173	\$127.85
Painted White	165°F	22884MC/W	V173	\$127.85
Painted White	205°F	22884ME/W	V173	\$127.85
Painted Gray	165°F	22884MC/RAL9006	V173	\$127.85
Painted Gray	205°F	22884ME/RAL9006	V173	\$127.85
Socket Wrench		22847MB	V207	\$261.28



**Institutional**  
**Escutcheon**

Finish		Part #	IPG	List Price
Polished Chrome	3"	23196F	V173	\$11.99
Painted White	3"	23196M/W	V173	\$11.99
Painted Gray	3"	23196M/RAL9006	V173	\$22.64
Polished Chrome	4"	23197F	V173	\$15.98
Painted White	4"	23197M/W	V173	\$15.98
Painted Gray	4"	23197M/RAL9006	V173	\$25.30



**Institutional**  
**Optional Retaining Flange and Screw Assembly<sup>1</sup>**

Finish	Part #	IPG	List Price
Polished Chrome	10599	V173	\$47.93

(1) Set screw requires a 1/8" allen wrench not available from Viking.

**Specific Application Attic Sprinklers <sup>1</sup>**



**Back-to-Back (Model V-BB) Attic Sprinkler, Specific Application, Glass Bulb, ½ and ¾ inch NPT**

K Factor	Roof Pitch	SIN	Part #	Temp	Finish <sup>1</sup>	IPG	List Price
5.6 (81)	4:12 < 7:12	VK684	19627AE	200°F	Standard Brass	V174	\$ 408.28
5.6 (81)	7:12 < 10:12	VK685	19801AE	200°F	Standard Brass	V174	\$ 408.28
5.6 (81)	10:12 ≤ 12:12	VK686	19754AE	200°F	Standard Brass	V174	\$ 408.28
8.0 (115)	4:12 < 7:12	VK681	19626AE	200°F	Standard Brass	V174	\$ 476.57
8.0 (115)	7:12 < 10:12	VK682	19798AE	200°F	Standard Brass	V174	\$ 476.57
8.0 (115)	10:12 ≤ 12:12	VK683	19751AE	200°F	Standard Brass	V174	\$ 476.57



**Single Directional (Model V-SD) Attic Sprinkler, Specific Application, Glass Bulb, ½ inch NPT**

K Factor	Roof Pitch	SIN	Part #	Temp	Finish <sup>1</sup>	IPG	List Price
5.6 (81)	4:12 < 7:12	VK693	19578AE	200°F	Standard Brass	V174	\$ 408.28
5.6 (81)	7:12 < 10:12	VK694	19799AE	200°F	Standard Brass	V174	\$ 408.28
5.6 (81)	10:12 ≤ 12:12	VK695	19759AE	200°F	Standard Brass	V174	\$ 408.28



**Attic Upright Sprinkler, Specific Application, Glass Bulb, ½ inch NPT**

K Factor	Roof Pitch	SIN	Part #	Temp	Finish <sup>1</sup>	IPG	List Price
4.2 (57)	4:12 to 12:12	VK696	19538AE	200°F	Standard Brass	V175	\$ 60.37
5.6 (81)	4:12 to 12:12	VK697	21716AE	200°F	Standard Brass	V175	\$ 68.95



**Attic HIP (Model V-HIP), Specific Application, Glass Bulb, ½ inch NPT**

K Factor	Roof Pitch	SIN	Part #	Temp	Finish <sup>1</sup>	IPG	List Price
5.6 (81)	4:12 to 12:12	VK660	20952AE	200°F	Standard Brass	V174	\$ 408.28



**Attic Sprinkler (Model V-EP), Specific Application (Eave Protection), Glass Bulb, ½ inch NPT**

K Factor	Roof Pitch	SIN	Part #	Temp	Finish <sup>1</sup>	IPG	List Price
5.6 (81)	2½:12 ≤ 6:12	VK690	22768AE	200°F	Standard Brass	V174	\$ 408.29
5.6 (81)	2½:12 ≤ 6:12	VK690	22768JNE	200°F	Nickel PTFE (ENT)	V188.A	\$ 471.07

Installation Wrench	Part #	IPG	List Price
Standard Wrench	21475M/B	V207	\$ 81.05

(1) Also available with Electroless Nickel PTFE (ENT) plating for corrosion resistance (special order with extended lead time).  
Please contact customer service for price and availability.



**COIN®**  
Quick Response  
**COmbustible INterstitial**  
Glass Bulb  
Upright (Specific Application)  
SIN: VK900  
K Factor: 4.2 (60)  
Thread Size: 1/2 inch NPT  
Base Part #: 12493

Finish	Temp	Part #	IPG	List Price
Standard Brass	175°F	12493AD	V172	\$74.54
<b>FUSIBLE LINK - VK901 (4.2 (60) K Factor)</b>				
Standard Brass	205°F	12676AE	V172	\$82.81
Std Sprinkler Wrench		21475M/B	V207	\$81.05



**COIN®**  
Quick Response  
**COmbustible INterstitial**  
Glass Bulb  
Upright (Specific Application)  
SIN: VK950  
K Factor: 5.6 (80)  
Thread Size: 1/2 inch NPT  
Base Part #: 20757

Finish	Temp	Part #	IPG	List Price
Standard Brass	200°F	20757AE	V172	\$91.30
Std Sprinkler Wrench		21475M/B	V207	\$81.05



**Window Sprinkler**  
Quick Response  
Glass Bulb  
Pendant Vertical Sidewall  
(Specific Application)  
SIN: VK960  
K Factor: 5.6 (81)  
Thread Size: 1/2 inch NPT  
Base Part #: 23017

Finish	Temp	Part #	IPG	List Price
Standard Brass	155°F	23017AB	V193	\$484.05
Standard Brass	200°F	23017AE	V193	\$484.05
Polished Chrome	155°F	23017FB	V193	\$503.41
Polished Chrome	200°F	23017FE	V193	\$503.41
White-Polyester	155°F	23017MB/W	V193	\$503.41
White-Polyester	200°F	23017ME/W	V193	\$503.41
Black-Polyester	155°F	23017MB/B	V193	\$503.41
Black-Polyester	200°F	23017ME/B	V193	\$503.41
Nickel PTFE (ENT)	155°F	23017JNB	V193	\$561.50
Nickel PTFE (ENT)	200°F	23017JNE	V193	\$561.50
Std Sprinkler Wrench		22940MB	V207	\$81.05



**Window Sprinkler**  
Quick Response  
Glass Bulb  
Horizontal Sidewall  
(Specific Application)  
SIN: VK962  
K Factor: 5.6 (81)  
Thread Size: 1/2 inch NPT  
Base Part #: 23019

Finish	Temp	Part #	IPG	List Price
Standard Brass	155°F	23019AB	V193	\$484.05
Standard Brass	200°F	23019AE	V193	\$484.05
Polished Chrome	155°F	23019FB	V193	\$503.41
Polished Chrome	200°F	23019FE	V193	\$503.41
White-Polyester	155°F	23019MB/W	V193	\$503.41
White-Polyester	200°F	23019ME/W	V193	\$503.41
Black-Polyester	155°F	23019MB/B	V193	\$503.41
Black-Polyester	200°F	23019ME/B	V193	\$503.41
Nickel PTFE (ENT)	155°F	23019JNB	V193	\$561.50
Nickel PTFE (ENT)	200°F	23019JNE	V193	\$561.50
Std Sprinkler Wrench		22940MB	V207	\$81.05