



Section T
Special Hazards

TABLE OF CONTENTS

VSH1230 T-1 and T-2
Flammable Liquid Storage Protection.....T-3

Notes

1. Refer to Viking technical data pages for complete product specifications. You may print or download technical data by visiting www.vikinggroupinc.com.
2. Pricing is per information supplied and includes only the items listed. Equipment list could vary after design.
3. No design or engineering is included unless noted.
4. No onsite checkout or supervision is included.
5. No installation material is included (i.e. pipe, fittings, hangers, wire, conduit, and electrical connections).
6. Price valid for 30 days.
7. List prices effective July 9, 2022. Supersedes February 2022 list price book.
8. All sales by Viking are subject to the Terms & Conditions found on the last page of this book.

VSH1230

Clean Agent				
Part Number	Description	IPG	List Price	
888054-275	3M NOVEC 1230	V522	\$	36.97

360 psi Welded Cylinders				
Part Number	Description	IPG	List Price	
910510-XXX	360 psi Tank & Valve Assembly 500 lb. Empty (Fill Capacity 159-476 lb.) 180L	V518	POR	
914147-XXX	360 psi Tank & Valve Assembly 60 lb. Empty (Fill Capacity 20-58 lb.) 22L	V519	POR	
889109-XXX	360 psi Tank & Valve Assembly 140 lb. Empty (Fill Capacity 46-137 lb.) 52L	V523	POR	
889111-XXX	360 psi Tank & Valve Assembly 280 lb. Empty (Fill Capacity 94-280 lb.) 106L	V523	POR	
889113-XXX	360 psi Tank & Valve Assembly 390 lb. Empty (Fill Capacity 130-388 lb.) 147L	V523	POR	

360 psi Welded Cylinders with Liquid Level Indicators				
Part Number	Description	IPG	List Price	
914151-XXX	360 psi Tank & Valve Assembly 280 lb. Empty (Fill Capacity 94-280 lb.) 106L w/Liquid Level Indicator	V513	POR	
914152-XXX	360 psi Tank & Valve Assembly 390 lb. Empty (Fill Capacity 130-388 lb.) 147L w/Liquid Level Indicator	V515	POR	
914153-XXX	360 psi Tank & Valve Assembly 500 lb. Empty (Fill Capacity 159-476 lb.) 180L w/Liquid Level Indicator	V517	POR	

725 psi Seamless Cylinders				
Part Number	Description	IPG	List Price	
926274-XXX	725 psi Tank & Valve Assembly 220 lb. Empty (Fill Capacity 71-211 lb.) 80L	V505	POR	
888591-XXX *	725 psi Tank & Valve Assembly 220 lb. Empty (Fill Capacity 71-211 lb.) 80L	V520	POR	
926278-XXX	725 psi Tank & Valve Assembly 390 lb. Empty (Fill Capacity 124-370 lb.) 140L	V505	POR	
888593-XXX *	725 psi Tank & Valve Assembly 390 lb. Empty (Fill Capacity 124-370 lb.) 140L	V521	POR	
926280-XXX	725 psi Tank & Valve Assembly 500 lb. Empty (Fill Capacity 159-476 lb.) 180L	V505	POR	
888595-XXX *	725 psi Tank & Valve Assembly 500 lb. Empty (Fill Capacity 159-476 lb.) 180L	V522	POR	

*Limited Access


Price On Request - Contact your local VSN location for list prices.

Tank Bracket Assembly				
Part Number	Description	IPG	List Price	
887639	Tank Bracket (Fits 280, 390 & 500 lb. 360 psi and all 725 psi)	V524	\$	62.08

Discharge Hoses & Fittings				
Part Number	Description	IPG	List Price	
17562	Swivel Tank to Pipe, DN40 to 1 1/2" NPT for 60, 140 lb. cylinders	V507	\$	67.95
17563	Swivel Tank to Pipe, DN50 to 2" NPT for 220, 280, 390, 500 lb cylinders	V507	\$	86.96
912071	2" Check Valve (NPT)	V507	\$	601.11
912076	Discharge Hose 90° 2" NPT for 220, 280, 390, 500 lb cylinders	V507	\$	561.89


Low Pressure Gauge with Switch/Replacement				
Part Number	Description	IPG	List Price	
889303	360 psi Gauge w/ Integrated Low Pressure Switch, NC at low pressure	V507	\$	227.64
889305	725 psi Gauge w/ Integrated Low Pressure Switch, NC at low pressure	V507	\$	291.04

VSH1230

Actuation Components				
	Part Number	Description	IPG	List Price
	826758D	Pneumatic Pressure Switch Assembly (Includes adaptors)	V500	\$ 852.85
	887645	Electric Release Screw Reset Tool	V507	\$ 71.45
	887668	Release Device Manual	V507	\$ 125.62
	887669	Release Device Pneumatic	V507	\$ 96.31
	887670	Release Device Pneumatic/Manual	V507	\$ 98.38
	887834	Pilot Hose 23.6 in. DN4	V507	\$ 120.98
	887835	Pilot Hose 39.3 in. DN4	V507	\$ 102.75
	887836	Pilot Hose 59 in. DN4	V507	\$ 124.66
	887644	Pilot Hose/Valve Adapter M12x1,5 – G1/8	V507	\$ 16.35
	889323D	Release Device Electric 24V	V507	\$ 1,040.14
	932437D	Electrical Actuator Removal Monitoring Switch for 220, 280,390,500 lb cylinders	V507	\$ 581.09
	932438D	Electrical Actuator Removal Monitoring Switch for 60, 140 lb cylinders	V507	\$ 581.75
	16010	Pressure Malfunction Safety Assembly	V513	\$ 160.61

VSH1230 Discharge Nozzles (Must Specify Orifice Size)				
Part Number	Description	IPG	List Price	
889061-XXXX	Nozzle – NCD RP ½ -180 VSH1230 brass	V508	POR	
889069-XXXX	Nozzle – NCD RP ½ -360 VSH1230 brass	V508	POR	
889075-XXXX	Nozzle – NCD RP 1 -360 VSH1230 XCrNi, stainless steel, call for lead time	V508	POR	
889065-XXXX	Nozzle – NCD RP ½ -180 VSH1230 XCrNi, stainless steel, call for lead time	V508	POR	
889066-XXXX	Nozzle – NCD RP 1 -180 VSH1230 XCrNi, stainless steel, call for lead time	V508	POR	
889062-XXXX	Nozzle – NCD RP 1 -180 VSH1230 brass	V508	POR	
889070-XXXX	Nozzle – NCD RP 1 -360 VSH1230 brass	V508	POR	
889063-XXXX	Nozzle – NCD RP 1½ -180 VSH1230 brass	V508	POR	
889071-XXXX	Nozzle – NCD RP 1½ -360 VSH1230 brass	V508	POR	
889064-XXXX	Nozzle – NCD RP 2 -180 VSH1230 brass	V508	POR	
889073-XXXX	Nozzle – NCD RP 2 -360 VSH1230 brass	V508	POR	

*Price On Request - Contact your local VSN location for list prices.

Nameplates				
	Part Number	Description	IPG	List Price
	16988	Sign VSH1230 Outside	V507	\$ 24.11
	16989	Sign VSH1230 Inside	V507	\$ 24.11
	16988-S	Sign VSH1230 Outside, Spanish	V507	\$ 24.11
	16989-S	Sign VSH1230 Inside, Spanish	V507	\$ 24.11

Recharge Adaptors				
	Part Number	Description	IPG	List Price
	18160	1 7/8" Valve Recharge Adaptor (60 lb & 140 lb. tank only)	V507	\$ 137.91
	18161	2" Valve, Recharge Adaptor	V507	\$ 157.84
	18793	Gauge Port Adaptor	V507	\$ 108.46

Flammable Liquid Storage Protection

IBC Spill Containment Unit



Part Number	Description	IPG	List Price
24050	Model 275 IBC without rollers	V325	\$ 20,116.84
24054	Model 275 IBC with rollers	V325	\$ 20,517.73
24119	Model 275 IBC without rollers (preassembled)	V325	\$ 20,535.95
24120	Model 275 IBC with rollers (preassembled)	V325	\$ 21,283.15
23973	Model 330 IBC without rollers	V325	\$ 22,157.68
24045	Model 330 IBC with rollers	V325	\$ 22,777.22
24121	Model 330 IBC without rollers (preassembled)	V325	\$ 22,959.45
24122	Model 330 IBC with rollers (preassembled)	V325	\$ 23,323.88

Spare/Replacment Parts

Part Number	Description	IPG	List Price
24147	Flame Barrier Filter	V325	\$ 1,272.93
23966	Catchment Basin Cover Plate	V325	\$ 1,180.08