



HMER7.EX1299 Check Valves Certified for Canada

[Page Bottom](#)

Check Valves Certified for Canada

[See General Information for Check Valves Certified for Canada](#)

VIKING CORP

EX1299

210 N INDUSTRIAL PARK RD
HASTINGS, MI 49058 USA

Swing type, iron body, Models D-1, E-1, sizes 2-1/2 in. rated for 250 psig.

Swing type, iron body, Model F-1, sizes 3, 4, 6 and 8 in. rated for 250 psig.

Swing type, iron body, Model G-1, sizes 3, 4, 6 and 8 in. rated for 250 psig.

Swing type, Model M-2, Groove/Groove, size 4 in. rated for 250 psig.

[Last Updated](#) on 2007-07-30

[Questions?](#)

[Notice of Disclaimer](#)

[Page Top](#)

[Copyright © 2008 Underwriters Laboratories Inc.®](#)

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Listed and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Designs and/or Listings (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from Underwriters Laboratories Inc." must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "Copyright © 2008 Underwriters Laboratories Inc.®"

An independent organization working for a safer world with integrity, precision and knowledge.

