




Pipe Clamp without Insulation

250

Technical Features

- Sizes (Pipe Accomodation Diameter): 12mm through 218mm
- Hanger Thread Size : M8/M10 Combination Boss.
- Closure Cylinder Head Screw Sizes : M6x20 to M8x25
- Materials :
Profile: Carbon steel
- Finish : Electro Zinc Plated



Pipe Support

Pipe Clamp without Insulation - 250

Physical Data

Reference	Nominal Pipe Size		Thread	B x S (mm)	Sc x L	d (mm)	Box Qty.	Weight (x1) (kg / lbs)
	metric (DN)	inch						
596210	DN10	3/8"	M8/M10	20x1,5	M6x20	14-18	100	0,05 / 0.12
596220	DN15	1/2"	M8/M10	20x1,5	M6x20	20-26	100	0,05 / 0.12
596230	DN20	3/4"	M8/M10	20x1,5	M6x20	23-30	100	0,05 / 0.12
596250	DN25	1"	M8/M10	20x1,5	M6x20	33-40	100	0,07 / 0.15
596260	DN32	1 1/4"	M8/M10	20x2,0	M6x20	41-47	100	0,08 / 0.18
596270	DN40	1 1/2"	M8/M10	20x2,0	M6x25	48-54	50	0,08 / 0.18
596280	DN50	2"	M8/M10	20x2,0	M6x25	56-62	50	0,09 / 0.20
596290	62-69mm	-	M8/M10	20x2,0	M6x25	62-69	50	0,09 / 0.20
596300	67-71mm	-	M8/M10	20x2,0	M6x25	67-71	50	0,13 / 0.29
596310	DN65	2 1/2"	M8/M10	20x2,0	M6x25	69-78	25	0,17 / 0.38
596320	DN80	3"	M8/M10	20x2,0	M6x25	85-91	25	0,17 / 0.38
596330	90-98mm	-	M8/M10	23x2,5	M6x25	90-98	25	0,17 / 0.38
596340	97-107mm	-	M8/M10	23x2,5	M6x25	97-107	25	0,18 / 0.40
596350	104-110mm	-	M8/M10	23x2,5	M6x25	104-110	25	0,20 / 0.44
596360	DN100	4"	M8/M10	23x2,5	M8x25	108-116	25	0,25 / 0.55
596370	116-126mm	-	M8/M10	23x2,5	M8x25	116-126	25	0,25 / 0.55
596380	129-140mm	-	M8/M10	23x2,5	M8x25	129-140	25	0,27 / 0.60
596390	DN125	5"	M8/M10	23x2,5	M8x25	133-141	25	0,28 / 0.62
596400	144-154mm	-	M8/M10	23x2,5	M8x25	144-154	25	0,30 / 0.66
596410	DN150	6"	M8/M10	23x2,5	M8x25	159-168	25	0,28 / 0.62
596420	168-176mm	-	M8/M10	30x3,0	M8x25	168-176	25	0,31 / 0.68
596430	174-184mm	-	M8/M10	30x3,0	M8x25	174-184	25	0,41 / 0.91
596435	DN200	8"	M8/M10	30x3,0	M8x25	207-218	10	0,56 / 1.24