




C-Channel - Single

Technical Features

- **Sizes available** : See table below
- **Material** : Carbon steel
- **Finish** : Pre-galvanized
- **Compatibility** : Compatible with Wall Brackets: Vertical APX, and Horizontal APY and Cantilever C-E0.



C-Channel - Single

Physical Data

Section (mm) BxAxS	Length (mm) L	Dimensions (mm / inch)				Box Qty.	Weight (ea.) (kg / lbs)	Reference
		C	O	D x E	H			
27 x 18 x 1,25	2000	15,5 / 0.61	10,5 / 0,41	8,5 x 20 / 0.33 x 0.79	30.0 / 1.18	10	1,27 / 2.80	599996
27 x 30 x 1,50	2000	15,5 / 0.61	10,5 / 0,41	8,5 x 20 / 0.33 x 0.79	30.0 / 1.18	10	2,07 / 4.56	599997
30 x 15 x 2,00	2000	15,5 / 0.61	5,0 / 0.20*	11,0 x 27 / 0.43 x 1.06	50.0 / 1.97	10	1,88 / 4.14	585500
34 x 20 x 1,50	2000	15,5 / 0.61	5,0 / 0.20*	11,0 x 27 / 0.43 x 1.06	50.0 / 1.97	10	1,80 / 3.99	585480
34 x 20 x 2,40	2000	15,5 / 0.61	5,0 / 0.20*	11,0 x 27 / 0.43 x 1.06	50.0 / 1.97	10	2,71 / 5.97	585470
35 x 35 x 2,00	2000	15,5 / 0.61	5,0 / 0.20*	11,0 x 27 / 0.43 x 1.06	50.0 / 1.97	10	3,45 / 7.60	585560
35 x 35 x 2,00	3000	15,5 / 0.61	5,0 / 0.20*	11,0 x 27 / 0.43 x 1.06	50.0 / 1.97	10	5,18 / 11.41	585550
35 x 35 x 2,00	6000	15,5 / 0.61	5,0 / 0.20*	11,0 x 27 / 0.43 x 1.06	50.0 / 1.97	10	10,35 / 22.82	585540
38 x 40 x 2,00	2000	15,5 / 0.61	N/A	14,0 x 27 / 0.55 x 1.06	50.0 / 1.97	10	5,10 / 11.24	599998
38 x 40 x 2,00	3000	15,5 / 0.61	N/A	14,0 x 27 / 0.55 x 1.06	50.0 / 1.97	10	7,65 / 16.86	600000
38 x 40 x 2,00	6000	15,5 / 0.61	N/A	14,0 x 27 / 0.55 x 1.06	50.0 / 1.97	10	15,30 / 33.73	599999

* Square Holes, diagonal measurement.

