




## Pipe Clamp with Insulation

### HDPCI

#### Technical Features

- **Sizes (Pipe Accomodation Diameter):** 14 mm through 273 mm
- **Hanger Thread Size :** For diameters from 14 mm to 65mm M8/M10 Combination Boss. For diameters from 73 mm to 116 mm M10/M12 Combination Boss. For diameters from 138 mm to 171 mm M12/M16 Combination Boss. For diameters from 219 mm to 273 mm M16/M20 Combination Boss
- **Closure Cylinder Head Screw Sizes :** M6x20 to M8x25
- **Temperature Range :** -50°C - +110°C
- **Materials :** Profile: Carbon steel; Rubber: EPDM
- **Finish :** Electro Zinc Plated
- **Fire rating :** DIN EN 135501-1:E



#### Pipe Clamp with Insulation - HDPCI

#### Physical Data

Reference	Nominla Pipe Size	M	d (mm)		Box Qty.
	inch				
577033	3/8"	M8/M10	14-18	2000	50
577034	1/2"	M8/M10	19-23	2000	50
577035	3/4"	M8/M10	24-28	2000	50
577036	1"	M8/M10	29-33	2000	50
577038	1 1/4"	M8/M10	40-45	2000	50
577039	1 1/2"	M8/M10	47-52	2000	50
577041	2"	M8/M10	60-65	2000	50
577043	2 1/2"	M10/M12	73-78	3500	25
577045	3"	M10/M12	88-93	3500	25
577048	4"	M10/M12	108-116	3500	25
577052	5"	M12/M16	138-145	5000	10
577055	6"	M12/M16	165-171	5000	10
577061	8"	M12/M16	219-225	8500	1
577066	10"	M12/M20	265-273	10000	1