



**CAUTION: CONCEALED COVER ASSEMBLY 12207 IS FRAGILE!
TO ASSURE SATISFACTORY PERFORMANCE OF THE PRODUCT, HANDLE WITH CARE.**



**Concealed Sprinkler and Adapter
Assembly with Protective Cap**

**Concealed Sprinkler and Adapter
Assembly (Protective Cap Removed)**



**Cover Plate Assembly
Base Part Number 12207**



GENERAL HANDLING AND STORAGE INSTRUCTIONS:

- Do not store in temperatures exceeding 100 °F (38 °C). Avoid direct sunlight and confined areas subject to heat.
- Protect sprinklers and cover assemblies during storage, transport, handling, and after installation.
 - Use original shipping containers.
 - Do not place sprinklers or cover assemblies loose in boxes, bins, or buckets.
- Keep the sprinkler bodies covered with the protective sprinkler cap (Viking Part Number 12199) any time the sprinklers are shipped or handled, during testing of the system, and while ceiling finish work is being completed.
- Use only the designated Viking recessed sprinkler wrench (refer to the appropriate sprinkler data page) to install these sprinklers. NOTE: The protective cap is temporarily removed during installation and then placed back on the sprinkler for protection until ceiling work is finished.
- Do not over-tighten the sprinklers into fittings during installation.
- Do not use the sprinkler deflector to start or thread the sprinklers into fittings during installation.
- Do not attempt to remove drywall, paint, etc., from the sprinklers.
- Remove the plastic protective cap from the sprinkler before attaching the cover plate assembly. **PROTECTIVE CAPS MUST BE REMOVED FROM SPRINKLERS BEFORE PLACING THE SYSTEM IN SERVICE!**

FOR COMPLETE CARE, HANDLING, & INSTALLATION INSTRUCTIONS, REFER TO THE SPRINKLER DATA PAGE AND THE APPROPRIATE SPRINKLER GENERAL CARE, INSTALLATION, AND MAINTENANCE GUIDE.