



THE VIKING CORPORATION  
 210 N. Industrial Park Drive  
 Hastings, MI 49058 U.S.A.  
 Telephone: (269) 945-9501  
 (877) 384-5464  
 Fax: (269) 818-1680  
 e-mail: techsvcs@vikingcorp.com

**SPRINKLER IDENTIFICATION NUMBER (SIN) DIRECTORY**

SIN*	Technical Data Page(s)	Sprinkler Base Part Number	Nominal K-Factor		Sprinkler Model and Type	Maximum Pressure Rating
			U.S.	metric		
VK001	<a href="#">11q-v</a>	10192 and 13007	2.8	40.3	Standard Response Model M Upright, Small Orifice, 15 mm BSP	175 psi
VK001	<a href="#">11q-v</a>	10218 and 13006	2.8	40.3	Standard Response Model M Upright, Small Orifice, ½" NPT	175 psi
VK002	N/A	10176	4.2	57	Standard Response Model M Upright, Small Orifice, 10 mm BSP (discontinued product)	175 psi
VK002	<a href="#">11q-v</a>	10191	4.2	57	Standard Response Model M Upright, Small Orifice, 15 mm BSP	175 psi
VK002	<a href="#">11q-v</a>	10219	4.2	57	Standard Response Model M Upright, Small Orifice, ½" NPT	175 psi
VK003	<a href="#">11a-h</a>	10189 and 12992	2.8	40.3	Standard Response Model M Pendent, Small Orifice, 15 mm BSP	175 psi
VK003	<a href="#">11a-h</a>	10221 and 12994	2.8	40.3	Standard Response Model M Pendent, Small Orifice, ½" NPT	175 psi
VK004	N/A	10175	4.2	57	Standard Response Model M Pendent, Small Orifice, 10 mm BSP (discontinued product)	175 psi
VK004	N/A	10188	4.2	57	SR Model M Pendent, Small Orifice, 15 mm BSP (discontinued product)	175 psi
VK004	<a href="#">11a-h</a>	10222	4.2	57	Standard Response Model M Pendent, Small Orifice, ½" NPT	175 psi
VK005	N/A	05569	2.8	40.3	SR Model M Fusible Link Upright, Small Orifice, ½" NPT (discontinued product)	175 psi
VK005	N/A	12975	2.8	40.3	SR Model M Fusible Link Upright, Small Orifice, ½" NPT (discontinued product)	175 psi
VK006	N/A	05510	4.2	57	Standard Response Model M Fusible Link Upright, Small Orifice, 10 mm BSP (discontinued product)	175 psi
VK006	<a href="#">18a-f</a>	05574	4.2	57	Standard Response Model M Fusible Link Upright, Small Orifice, ½" NPT	175 psi
VK007	N/A	05570	2.8	40.3	SR Model M Fusible Link Pendent, Small Orifice, ½" NPT (discontinued product)	175 psi
VK007	N/A	12976	2.8	40.3	SR Model M Fusible Link Pdt, Small Orifice, ½" NPT (discontinued product)	175 psi
VK008	N/A	05512	4.2	57	Standard Response Model M Fusible Link Pendent, Small Orifice, 10 mm BSP (discontinued product)	175 psi
VK008	<a href="#">18a-f</a>	05575	4.2	57	Standard Response Model M Fusible Link Pendent, Small Orifice, ½" NPT	175 psi
VK015	<a href="#">14e-j</a>	09997	2.8	40.3	HP Standard Response Model M Horizontal Sidewall, Small Orifice, ½" NPT	250 psi
VK016	<a href="#">14e-j</a>	09126	4.2	57	Standard Response Model M Horizontal Sidewall, Small Orifice, 10 mm BSP	175 psi
VK018	<a href="#">14a-b</a>	09127	4.2	57	Standard Response Model M Vertical Sidewall, Small Orifice, 10 mm BSP	175 psi
VK021	<a href="#">11a-h</a>	09995	2.8	40.3	HP Standard Response Model M HP Upright, Small Orifice, ½" NPT	250 psi
VK023	<a href="#">11a-h</a>	09994	2.8	40.3	HP Standard Response Model M HP Pendent, Small Orifice, ½" NPT	250 psi
VK030	N/A	09284	4.2	57	Special Response Upright, Small Orifice, 10 mm BSP (discontinued product)	175 psi
VK032	N/A	09285	4.2	57	Special Response Pendent, Small Orifice, 10 mm BSP (discontinued product)	175 psi
VK100	<a href="#">11q-v</a>	10138 and 12986	5.6	80.6	Standard Response Model M Upright, Standard Orifice, ½" NPT	175 psi
VK100	<a href="#">11q-v</a>	10193 and 12993	5.6	80.6	Standard Response Model M Upright, Standard Orifice, 15 mm BSP	175 psi
VK102	<a href="#">11a-h</a>	10139 and 12987	5.6	80.6	Standard Response Model M Pendent, Standard Orifice, ½" NPT	175 psi
VK102-D	<a href="#">11-q</a>	10139A-X	5.6	80.6	Standard Response Domed Concealed Pendent, Standard Orifice, ½" NPT	175 psi
VK102	<a href="#">11a-h</a>	10173 and 12989	5.6	80.6	Standard Response Model M Pendent, Standard Orifice, 15 mm BSP	175 psi
VK104	<a href="#">14e-j</a>	10171 and 12988	5.6	80.6	Standard Response Model M HSW, Standard Orifice, 15 mm BSP	175 psi
VK104	<a href="#">14e-j</a>	10224 and 12995	5.6	80.6	Standard Response Model M Horizontal Sidewall, Standard Orifice, ½" NPT	175 psi
VK106	<a href="#">14a-b</a>	10186 and 12991	5.6	80.6	Standard Response Model M Vertical Sidewall, Standard Orifice, 15 mm BSP	175 psi
VK106	<a href="#">14a-b</a>	10226 and 12996	5.6	80.6	Standard Response Model M Vertical Sidewall, Standard Orifice, ½" NPT	175 psi
VK108	<a href="#">18a-f</a>	05506 and 12971	5.6	80.6	Standard Response Model M Fusible Element Upright, Standard Orifice, 15 mm BSP	175 psi
VK108	<a href="#">18a-f</a>	05557 and 12973	5.6	80.6	Standard Response Model M Fusible Element Upright, Standard Orifice, ½" NPT	175 psi
VK110	<a href="#">18a-f</a>	05508 and 12972	5.6	80.6	Standard Response Model M Fusible Element Pendent, Standard Orifice, ½" NPT	175 psi
VK112	<a href="#">19a-e</a>	05559 and 12974	5.6	80.6	Standard Response Model M Fusible Element Horizontal Sidewall, Standard Orifice, ½" NPT	175 psi
VK114	N/A	06347 and 12977	5.6	80.6	Standard Response Model M Fusible Element Vertical Sidewall, Standard Orifice, ½" NPT (discontinued product)	175 psi
VK116	<a href="#">14e-j</a>	09849	5.6	80.6	HP Standard Response Model M-5 HSW, Standard Orifice, ½" NPT	250 psi
VK118	<a href="#">11q-v</a>	10172	5.6	80.6	Standard Response Model M Conventional, Standard Orifice, 15 mm BSP	175 psi
VK118	<a href="#">11q-v</a>	10227	5.6	80.6	Standard Response Model M Conventional, Standard Orifice, ½" NPT	175 psi
VK120	<a href="#">11q-v</a>	10168	8.0	115.2	Standard Response Model M Conventional, Large Orifice, 20 mm BSP	175 psi
VK120	<a href="#">11q-v</a>	10228	8.0	115.2	Standard Response Model M Conventional, Large Orifice, 3/4" NPT	175 psi
VK120	N/A	12106	8.0	115.2	Standard Response Model M Conv., Large Orifice, 3/4" NPT (discontinued product)	175 psi
VK122	<a href="#">11a-h</a>	09992	5.6	80.6	HP Standard Response Model M HP Pendent, Standard Orifice, ½" NPT	250 psi
VK124	<a href="#">11q-v</a>	09993	5.6	80.6	HP Standard Response Model M HP Upright, Standard Orifice, ½" NPT	250 psi
VK130	<a href="#">15a-e</a>	05012B	5.6	80.6	Standard Response Model N-2 Stainless Steel Upright, Standard Orifice, ½" NPT	175 psi
VK130	<a href="#">15a-e</a>	06501BZ	5.6	80.6	Standard Response Open Model N-2 Stainless Steel Upright, Standard Orifice, ½" NPT	175 psi
VK132	<a href="#">15a-e</a>	06483B	5.6	80.6	Standard Response Model N-2 Stainless Steel Pendent, Standard Orifice, ½" NPT	175 psi
VK132	<a href="#">15a-e</a>	06502BZ	5.6	80.6	Standard Response Open Model N-2 Stainless Steel Pendent, Standard Orifice, ½" NPT	175 psi
VK134	<a href="#">125a-g</a>	09224	5.6	80.6	Special Response Pendent, Standard Orifice, ½" NPT (discontinued product)	175 psi
VK134	<a href="#">125a-g</a>	09956	5.6	80.6	Special Response Pendent, Standard Orifice, 15 mm BSP (discontinued product)	175 psi

Continued from page 7.

SIN*	Technical Data Page(s)	Sprinkler Base Part Number	Nominal K-Factor		Sprinkler Model and Type	Maximum Pressure Rating
			U.S.	metric		
VK136	<a href="#">125a-g</a>	09225	5.6	80.6	Special Response Conventional, Standard Orifice, ½" NPT (discontinued product)	175 psi
VK136	<a href="#">125a-g</a>	09958	5.6	80.6	Special Response Conventional, Standard Orifice, 15 mm BSP (discontinued product)	175 psi
VK138	<a href="#">125a-g</a>	09226	5.6	80.6	Special Response Upright, Standard Orifice, ½" NPT (discontinued product)	175 psi
VK138	<a href="#">125a-g</a>	09959	5.6	80.6	Special Response Upright, Standard Orifice, 15 mm BSP (discontinued product)	175 psi
VK145	<a href="#">11q-v</a>   <a href="#">12a-f</a>	10174 and 12990	5.6	80.6	Standard Response Model M Upright, Standard Orifice, 15 mm BSP	175 psi
VK145	<a href="#">11q-v</a>   <a href="#">12a-f</a>	10233 and 13001	5.6	80.6	Standard Response Model M Upright, Standard Orifice, ½" NPT	175 psi
VK150	<a href="#">101a-g</a>	07852U	5.6	80.6	Standard Response Model M Plain Barrel Dry Pendent, Standard Orifice, 1" NPT	175 psi
VK150	<a href="#">101a-g</a>	07855U	5.6	80.6	Standard Response Model M Plain Barrel Dry Pendent, Standard Orifice, 25 mm BSP	175 psi
VK151	<a href="#">101a-g</a>	09343	5.6	80.6	Model M Plain Barrel Dry Pendent, Standard Orifice, 1" NPT	175 psi
VK1510	<a href="#">110a-g</a>	17389	5.6	80.6	Model M Plain Barrel Dry Pendent, Standard Orifice, 25 mm BSP	175 psi
VK1510	<a href="#">110a-g</a>	17388	5.6	80.6	Model M Plain Barrel Dry Pendent, Standard Orifice, 1" NPT	175 psi
VK152	<a href="#">102a-i</a>	07858U	5.6	80.6	Standard Response Model M Plain Barrel Dry Horizontal Sidewall, Standard Orifice, 1" NPT	175 psi
VK152	<a href="#">102a-i</a>	07861U	5.6	80.6	Standard Response Model M Plain Barrel Dry Horizontal Sidewall, Standard Orifice, 25 mm BSP	175 psi
VK153	<a href="#">103a-f</a>	09125U	5.6	80.6	Standard Response Model M Plain Barrel Dry Vertical Sidewall, Standard Orifice, 1" NPT	175 psi
VK153	<a href="#">103a-f</a>	08963U	5.6	80.6	Standard Response Model M Plain Barrel Dry Vertical Sidewall, Standard Orifice, 25 mm BSP	175 psi
VK154	<a href="#">101a-g</a>	07740U	5.6	80.6	Standard Response Model M Adjustable Standard Dry Pendent, Standard Orifice, 1" NPT	175 psi
VK154	<a href="#">101a-g</a>	07854U	5.6	80.6	Standard Response Model M Adjustable Standard Dry Pendent, Standard Orifice, 25 mm BSP	175 psi
VK155	<a href="#">101a-g</a>	09341	5.6	80.6	Model M Adjustable Standard Dry Pendent, Standard Orifice, 1" NPT	175 psi
VK1550	<a href="#">110a-g</a>	17391	5.6	80.6	Model M Adjustable Standard Dry Pendent, Standard Orifice, 25 mm BSP	175 psi
VK1550	<a href="#">110a-g</a>	17390	5.6	80.6	Model M Adjustable Standard Dry Pendent, Standard Orifice, 1" NPT	175 psi
VK156	<a href="#">102a-i</a>	07857U	5.6	80.6	Standard Response Model M Adjustable Standard Dry Horizontal Sidewall, Standard Orifice, 1" NPT	175 psi
VK156	<a href="#">102a-i</a>	07860U	5.6	80.6	Standard Response Model M Adjustable Standard Dry Horizontal Sidewall, Standard Orifice, 1" NPT	175 psi
VK157	<a href="#">103a-f</a>	09123U	5.6	80.6	Standard Response Model M Adjustable Standard Dry Vertical Sidewall, Standard Orifice, 1" NPT	175 psi
VK157	<a href="#">103a-f</a>	08961U	5.6	80.6	Standard Response Model M Adjustable Standard Dry Vertical Sidewall, Standard Orifice, 25 mm BSP	175 psi
VK158	<a href="#">101a-g</a>	06530U	5.6	80.6	Standard Response Model M Adjustable Recessed Dry Pendent, Standard Orifice, 1" NPT	175 psi
VK158	<a href="#">101a-g</a>	07853U	5.6	80.6	Standard Response Model M Adjustable Recessed Dry Pendent, Standard Orifice, 25 mm BSP	175 psi
VK159	<a href="#">101a-g</a>	09342	5.6	80.6	Model M Adjustable Recessed Dry Pendent, Standard Orifice, 1" NPT	175 psi
VK1590	<a href="#">110a-g</a>	17387	5.6	80.6	Model M Adjustable Recessed Dry Pendent, Standard Orifice, 25 mm BSP	175 psi
VK1590	<a href="#">110a-g</a>	17386	5.6	80.6	Model M Adjustable Recessed Dry Pendent, Standard Orifice, 1" NPT	175 psi
VK160	<a href="#">101i-m</a>	08050	5.6	80.6	Standard Response Model M Plain Barrel Dry Upright, Standard Orifice, 1" NPT	175 psi
VK160	<a href="#">101i-m</a>	08079	5.6	80.6	Standard Response Model M Plain Barrel Dry Upright, Std. Orifice, 25 mm BSP	175 psi
VK161	<a href="#">103a-f</a>	09124U	5.6	80.6	Standard Response Model M Adjustable Recessed Dry Vertical Sidewall, Standard Orifice, 1" NPT	175 psi
VK161	<a href="#">103a-f</a>	08962U	5.6	80.6	Standard Response Model M Adjustable Recessed Dry Vertical Sidewall, Standard Orifice, 25 mm BSP	175 psi
VK162	<a href="#">102a-i</a>	07856U	5.6	80.6	Standard Response Model M Adjustable Recessed Dry Horizontal Sidewall, Standard Orifice, 1" NPT	175 psi
VK162	<a href="#">102a-i</a>	07859U	5.6	80.6	Standard Response Model M Adjustable Recessed Dry HSW, Standard Orifice, 25 mm BSP Dry Horizontal Sidewall, Standard Orifice, 25 mm BSP	175 psi
VK163	<a href="#">101o-t</a>	12810U	8.0	115.2	Standard Response Model M Adjustable Standard Dry Pendent, Large Orifice, 1" NPT	175 psi
VK163	<a href="#">101o-t</a>	12813U	8.0	115.2	Standard Response Model M Adjustable Standard Dry Pendent, Large Orifice, 25 mm BSP	175 psi
VK164	<a href="#">101o-t</a>	12811U	8.0	115.2	Standard Response Model M Adjustable Recessed Dry Pendent, Large Orifice, 1" NPT	175 psi
VK164	<a href="#">101o-t</a>	12814U	8.0	115.2	Standard Response Model M Adjustable Recessed Dry Pendent, Large Orifice, 25 mm BSP	175 psi
VK166	<a href="#">101o-t</a>	12741U	8.0	115.2	Standard Response Model M Plain Barrel Dry Pendent, Large Orifice, 1" NPT	175 psi
VK166	<a href="#">101o-t</a>	12812U	8.0	115.2	Standard Response Model M Plain Barrel Dry Pendent, Large Orifice, 25 mm BSP	175 psi
VK168	<a href="#">101u-x</a>	09798U	5.6	80.6	Standard Response Model M Stainless Steel Plain Barrel Dry Pendent, Standard Orifice, 1" NPT	175 psi
VK168	<a href="#">101u-x</a>	09799U	5.6	80.6	Standard Response Model M Stainless Steel Plain Barrel Dry Pendent, Standard Orifice, 25 mm BSP	175 psi
VK169	<a href="#">101u-x</a>	10360U	5.6	80.6	Standard Response Model M Stainless Steel Adjustable Recessed Dry Pendent, Standard Orifice, 1" NPT	175 psi
VK169	<a href="#">101u-x</a>	10377U	5.6	80.6	Standard Response Model M Stainless Steel Adjustable Recessed Dry Pendent, Large Orifice, 25 mm BSP	175 psi
VK172	<a href="#">105a-f</a>	08387U	5.6	80.6	Quick Response Model M Plain Barrel Dry Pendent, Standard Orifice, 1" NPT	175 psi
VK172	<a href="#">105a-f</a>	16455U	5.6	80.6	Quick Response Model M Plain Barrel Dry Pendent, Standard Orifice, 25 mm BSP	175 psi

Continued from page 8.

SIN*	Technical Data Page(s)	Sprinkler Base Part Number	Nominal K-Factor		Sprinkler Model and Type	Maximum Pressure Rating
			U.S.	metric		
VK173	<a href="#">105h-n</a>	13248U	8.0	115.2	Quick Response Ordinary Hazard Plain Barrel Dry Pendent, Large Orifice, 1" NPT	175 psi
VK173	<a href="#">105h-n</a>	13251U	8.0	115.2	Quick Response Ordinary Hazard Plain Barrel Dry Pdt, Large Orifice, 25 mm BSP	175 psi
VK174	<a href="#">106a-h</a>	08388U	5.6	80.6	Quick Response Model M Plain Barrel Dry HSW, Standard Orifice, 1" NPT	175 psi
VK174	<a href="#">106a-h</a>	16456U	5.6	80.6	Quick Response Model M Plain Barrel Dry HSW, Standard Orifice, 25 mm BSP	175 psi
VK176	<a href="#">105a-f</a>	08383U	5.6	80.6	Quick Response Model M Adjustable Standard Dry Pendent, Standard Orifice, 1" NPT	175 psi
VK176	<a href="#">105a-f</a>	16457U	5.6	80.6	Quick Response Model M Adjustable Standard Dry Pendent, Standard Orifice, 25 mm BSP	175 psi
VK177	<a href="#">105h-n</a>	13249U	8.0	115.2	Quick Response Ordinary Hazard Adjustable Standard Dry Pendent, Large Orifice, 1" NPT	175 psi
VK177	<a href="#">105h-n</a>	13252U	8.0	115.2	Quick Response Ordinary Hazard Adjustable Standard Dry Pendent, Large Orifice, 25 mm BSP	175 psi
VK178	<a href="#">106a-h</a>	08384U	5.6	80.6	Quick Response Model M Adjustable Standard Dry Horizontal Sidewall, Standard Orifice, 1" NPT	175 psi
VK178	<a href="#">106a-h</a>	16458U	5.6	80.6	Quick Response Model M Adjustable Standard Dry Horizontal Sidewall, Standard Orifice, 25 mm BSP	175 psi
VK180	<a href="#">105a-d</a>	08385U	5.6	80.6	Quick Response Model M Adjustable Recessed Dry Pendent, Standard Orifice, 1" NPT	175 psi
VK180	<a href="#">105a-d</a>	16453U	5.6	80.6	Quick Response Model M Adjustable Recessed Dry Pendent, Standard Orifice, 25 mm BSP	175 psi
VK181	<a href="#">105h-n</a>	13250U	8.0	115.2	Quick Response Ordinary Hazard Adjustable Recessed Dry Pendent, Large Orifice, 1" NPT	175 psi
VK181	<a href="#">105h-n</a>	13253U	8.0	115.2	Quick Response Ordinary Hazard Adjustable Recessed Dry Pendent, Large Orifice, 25 mm BSP	175 psi
VK182	<a href="#">106a-h</a>	08386U	5.6	80.6	Quick Response Model M Adjustable Recessed Dry Horizontal Sidewall, Standard Orifice, 1" NPT	175 psi
VK182	<a href="#">106a-h</a>	16454U	5.6	80.6	Quick Response Model M Adjustable Recessed Dry Horizontal Sidewall, Standard Orifice, 25 mm BSP	175 psi
VK184	<a href="#">107a-d</a>	08417UA	5.6	80.6	Quick Response Model M Dry Upright, Standard Orifice, 1" NPT	175 psi
VK186	<a href="#">108a-f</a>	10541U	5.6	80.6	Standard Response/Quick Response Extended Coverage Model M Adjustable Recessed Dry Pendent, Standard Orifice, 1" NPT or 25 mm BSP	175 psi
VK188	<a href="#">109a-f</a>	10542U	5.6	80.6	Standard Response/Quick Response Extended Coverage Model M Adjustable Recessed Dry Horizontal Sidewall, Standard Orifice, 1" NPT	175 psi
VK190-D	<a href="#">104a-e</a>	12421UA	5.6	80.6	Standard Response Dry Domed Concealed Pendent, Standard Orifice, 1" NPT	175 psi
VK190-D	<a href="#">104a-e</a>	12429UA	5.6	80.6	Standard Response Dry Domed Concealed Pendent, Standard Orifice, 25 mm BSP	175 psi
VK192-D	<a href="#">103g-u</a>	12424UA	8.0	115.2	Standard Response Dry Domed Concealed Pendent, Large Orifice, 1" NPT	175 psi
VK192-D	<a href="#">103g-u</a>	12432UA	8.0	115.2	Standard Response Dry Domed Concealed Pendent, Large Orifice, 25 mm BSP	175 psi
VK194-D	<a href="#">104j-n</a>	12422UA	5.6	80.6	Quick Response Dry Domed Concealed Pendent, Standard Orifice, 1" NPT	175 psi
VK194-D	<a href="#">104j-n</a>	12430UA	5.6	80.6	Quick Response Dry Domed Concealed Pendent, Standard Orifice, 25 mm BSP	175 psi
VK196-D	<a href="#">108i-o</a>	12423UA	5.6	80.6	Standard/QR EC Dry Domed Concealed Pendent, Standard Orifice, 1" NPT	175 psi
VK196-D	<a href="#">108i-o</a>	12431UA	5.6	80.6	Standard/QR EC Dry Domed Concealed Pendent, Standard Orifice, 25 mm BSP	175 psi
VK200	<a href="#">11q-v</a>	10141	8.0	115.2	Standard Response Model M Upright, Large Orifice, 3/4" NPT	175 psi
VK200	<a href="#">11q-v</a>	10169	8.0	115.2	Standard Response Model M Upright, Large Orifice, 20 mm BSP	175 psi
VK200	N/A	10190	8.0	115.2	Standard Response Model M Upright, Large Orifice, 15 mm BSP (discontinued product)	175 psi
VK200	<a href="#">11q-v</a>	10220	8.0	115.2	Standard Response Model M Upright, Large Orifice, 1/2" NPT	175 psi
VK202	<a href="#">11a-h</a>	10142	8.0	115.2	Standard Response Model M Pendent, Large Orifice, 3/4" NPT	175 psi
VK202-D	<a href="#">11i-o</a>	10142A-X	8.0	115.2	Standard Response Domed Concealed Pendent, Large Orifice, 3/4" NPT	175 psi
VK202	<a href="#">11a-h</a>	10170	8.0	115.2	Standard Response Model M Pendent, Large Orifice, 20 mm BSP	175 psi
VK202	N/A	10187	8.0	115.2	Standard Response Model M Pendent, Large Orifice, 15 mm BSP (discontinued product)	175 psi
VK202	<a href="#">11a-h</a>	10223	8.0	115.2	Standard Response Model M Pendent, Large Orifice, 1/2" NPT	175 psi
VK202	N/A	12105	8.0	115.2	Standard Response Model M Pendent, Large Orifice, 3/4" NPT (discontinued product)	175 psi
VK204	<a href="#">18a-f</a>	05514	8.0	115.2	Standard Response Model M Fusible Link Upright, Large Orifice, 3/4" NPT	175 psi
VK204	<a href="#">18a-f</a>	05576	8.0	115.2	Standard Response Model M Fusible Link Upright, Large Orifice, 1/2" NPT	175 psi
VK206	<a href="#">18a-f</a>	05578	8.0	115.2	Standard Response Model M Fusible Link Pendent, Large Orifice, 1/2" NPT	175 psi
VK206	<a href="#">18a-f</a>	05516	8.0	115.2	Standard Response Model M Fusible Link Pendent, Large Orifice, 3/4" NPT	175 psi
VK210	<a href="#">125a-g</a>	09227	8.0	115.2	Special Response Upright, Large Orifice, 3/4" NPT (discontinued product)	175 psi
VK212	<a href="#">125a-g</a>	09228	8.0	115.2	Special Response Pendent, Large Orifice, 3/4" NPT (discontinued product)	175 psi
VK214	<a href="#">125a-g</a>	09229	8.0	115.2	Special Response Conventional, Large Orifice, 3/4" NPT (discontinued product)	175 psi
VK250	<a href="#">102s-z</a>	13173U	8.0	115.2	Standard Response Ordinary Hazard Plain Barrel Dry HSW, Large Orifice, 1" NPT	175 psi
VK250	<a href="#">102s-z</a>	13179U	8.0	115.2	Standard Response Ordinary Hazard Plain Barrel Dry HSW, Large Orifice, 25 mm BSP	175 psi
VK252	<a href="#">102s-z</a>	13172U	8.0	115.2	Standard Response Ordinary Hazard Adjustable Standard Dry HSW, Large Orifice, 1" NPT	175 psi

Continued from page 9.

SIN*	Technical Data Page(s)	Sprinkler Base Part Number	Nominal K-Factor		Sprinkler Model and Type	Maximum Pressure Rating
			U.S.	metric		
VK252	<a href="#">102s-z</a>	13178U	8.0	115.2	Standard Response Ordinary Hazard Adjustable Standard Dry HSW, Large Orifice, 25 mm BSP	175 psi
VK254	<a href="#">102s-z</a>	13174U	8.0	115.2	Standard Response Ordinary Hazard Adjustable Recessed Dry HSW, Large Orifice, 1" NPT	175 psi
VK254	<a href="#">102s-z</a>	13180U	8.0	115.2	Standard Response Ordinary Hazard Adjustable Recessed Dry HSW, Large Orifice, 25 mm BSP	175 psi
VK275	<a href="#">106s-z</a>	13170U	8.0	115.2	Quick Response Ordinary Hazard Plain Barrel Dry HSW, 1" NPT	175 psi
VK275	<a href="#">106s-z</a>	13176U	8.0	115.2	Quick Response Ordinary Hazard Plain Barrel Dry HSW, 25 mm BSP	175 psi
VK277	<a href="#">106s-z</a>	13169u	8.0	115.2	Quick Response Ordinary Hazard Adjustable Standard Dry HSW, 1" NPT	175 psi
VK277	<a href="#">106s-z</a>	13175U	8.0	115.2	Quick Response Ordinary Hazard Adjustable Standard Dry HSW, 25 mm BSP	175 psi
VK279	<a href="#">106s-z</a>	13171U	8.0	115.2	Quick Response Ordinary Hazard Adjustable Recessed Dry HSW, 1" NPT	175 psi
VK279	<a href="#">106s-z</a>	13177U	8.0	115.2	Quick Response Ordinary Hazard Adjustable Recessed Dry HSW, 25 mm BSP	175 psi
VK282	<a href="#">105p-u</a>	13254U	8.0	115.2	Quick Response Plain Barrel Dry Pendent Fusible Link, Large Orifice, 1" NPT	175 psi
VK282	<a href="#">105p-u</a>	13257U	8.0	115.2	Quick Response Plain Barrel Dry Pendent Fusible Link, Large Orifice, 25 mm BSP	175 psi
VK284	<a href="#">107o-t</a>	13239U	8.0	115.2	Quick Response Ordinary Hazard Plain Barrel Dry HSW Fusible Link, Large Orifice, 1" NPT	175 psi
VK284	<a href="#">107o-t</a>	13242U	8.0	115.2	Quick Response Ordinary Hazard Plain Barrel Dry HSW Fusible Link, Large Orifice, 25 mm BSP	175 psi
VK286	<a href="#">105p-u</a>	13255U	8.0	115.2	Quick Response Adjustable Standard Dry Pendent Fusible Link, Large Orifice, 1" NPT	175 psi
VK286	<a href="#">105p-u</a>	13258U	8.0	115.2	Quick Response Adjustable Standard Dry Pendent Fusible Link, Large Orifice, 25 mm BSP	175 psi
VK288	<a href="#">107o-t</a>	13240U	8.0	115.2	Quick Response Ordinary Hazard Adjustable Standard Dry HSW Fusible Link, Large Orifice, 1" NPT	175 psi
VK288	<a href="#">107o-t</a>	13243U	8.0	115.2	Quick Response Adjustable Standard Dry Pendent Fusible Link, Large Orifice, 25 mm BSP	175 psi
VK290	<a href="#">105p-u</a>	13256U	8.0	115.2	Quick Response Adjustable Recessed Dry Pendent Fusible Link, Large Orifice, 1" NPT	175 psi
VK290	<a href="#">105p-u</a>	13259U	8.0	115.2	Quick Response Adjustable Recessed Dry Pendent Fusible Link, Large Orifice, 25 mm BSP	175 psi
VK292	<a href="#">107o-t</a>	13241U	8.0	115.2	Quick Response Ordinary Hazard Adjustable Recessed Dry HSW Fusible Link, Large Orifice, 1" NPT	175 psi
VK292	<a href="#">107o-t</a>	13244U	8.0	115.2	Quick Response Ordinary Hazard Adjustable Recessed Dry HSW Fusible Link, Large Orifice, 25 mm BSP	175 psi
VK300	<a href="#">51a-e</a>   <a href="#">41u-z</a>	06661B and 12978	5.6	80.6	Quick Response Model M Upright, Standard Orifice, ½" NPT	175 psi
VK301	<a href="#">47a-f</a>	12279 and 17535	5.6	80.6	Quick Response Fusible Element Upright, Standard Orifice, ½" NPT	175 psi
VK302	<a href="#">41a-f</a>   <a href="#">41u-z</a>	06662B and 12979	5.6	80.6	Quick Response Model M Pendent, Standard Orifice, ½" NPT	175 psi
VK302-D	<a href="#">41g-l</a>	06662BA-X	5.6	80.6	Standard/Quick Response Domed Concealed Pendent, Standard Orifice, ½" NPT	175 psi
VK303	<a href="#">47a-f</a>	12275 and 17536	5.6	80.6	Quick Response Fusible Element Pendent, Standard Orifice, ½" NPT	175 psi
VK304	<a href="#">43u-z</a>	12982	5.6	80.6	Quick Response Model M Horizontal Sidewall, Standard Orifice, ½" NPT	175 psi
VK305	<a href="#">43a-f</a>   <a href="#">43u-z</a>	12121 and 12997	5.6	80.6	Model M-5 Quick Response Horizontal Sidewall, ½" NPT	175 psi
VK306	<a href="#">52e-h</a>	06727B	5.6	80.6	Quick Response Model M Vertical Sidewall, Standard Orifice, ½" NPT	175 psi
VK307	<a href="#">52o-t</a>   <a href="#">52u-z</a>	13947 and 13948	5.6	80.6	Quick Response Fusible Element Horizontal Sidewall, ½" NPT	175 psi
VK308	<a href="#">52o-t</a>   <a href="#">43h-m</a>	13949 and 13950	5.6	80.6	Quick Response Fusible Element HSW, Standard Orifice, ½" NPT	175 psi
VK309	<a href="#">50a-d</a>	13951	5.6	80.6	Quick Response Fusible Element VSW, Standard Orifice, ½" NPT	175 psi
VK310	<a href="#">51a-e</a>	06766B	5.6	80.6	Quick Response Model M Conventional, Standard Orifice, ½" NPT	175 psi
VK311	<a href="#">51h-k</a>	13952	5.6	80.6	Quick Response Fusible Element Conventional, Standard Orifice, ½" NPT	175 psi
VK315	<a href="#">51a-e</a>	12281	5.6	80.6	HP Quick Response Model M Upright, Standard Orifice, ½" NPT	250 psi
VK316	<a href="#">51h-k</a>	13953	5.6	80.6	Quick Response Fusible Element Upright, Standard Orifice, 1/2" NPT	250 psi
VK317	<a href="#">41a-f</a>	12282	5.6	80.6	HP Quick Response Model M Pendent, Standard Orifice, ½" NPT	250 psi
VK318	<a href="#">40a-f</a>	13954	5.6	80.6	HP Quick Response Fusible Element Pendent, Standard Orifice, ½" NPT	250 psi
VK319	<a href="#">43a-f</a>	12285	5.6	80.6	HP Model M-5 Quick Response Horizontal Sidewall, ½" NPT	250 psi
VK320	<a href="#">43h-m</a>	13955	5.6	80.6	Quick Response Fusible Element HSW, Standard Orifice, ½" NPT	175 psi
VK325	<a href="#">51a-e</a>	06717B	2.8	40.3	Quick Response Model M Upright, Small Orifice, ½" NPT	175 psi
VK326	<a href="#">42h-m</a>   <a href="#">51h-k</a>	13956 and 13957	2.8	40.3	Quick Response Fusible Element Upright, Small Orifice, ½" NPT	175 psi
VK327	<a href="#">51a-e</a>	06931B	4.2	57	Quick Response Model M Upright, Small Orifice, 10 mm BSP	175 psi
VK327	<a href="#">51a-e</a>	06719B	4.2	57	Quick Response Model M Upright, Small Orifice, ½" NPT	175 psi
VK328	<a href="#">51h-k</a>	13958	4.2	57	Quick Response Upright, Small Orifice, 1/2" NPT	175 psi
VK329	<a href="#">41a-f</a>   <a href="#">41u-z</a>	06718B and 12981	2.8	40.3	Quick Response Model M Pendent, Small Orifice, ½" NPT	175 psi

Continued from page 10.

SIN*	Technical Data Page(s)		Sprinkler Base Part Number	Nominal K-Factor		Sprinkler Model and Type	Maximum Pressure Rating
				U.S.	metric		
VK330	42h-m	40a-f	13959 and 13960	2.8	40.3	Quick Response Fusible Element Pendent, Small Orifice, ½" NPT	175 psi
VK331	41a-f		06932B	4.2	57	Quick Response Model M Pendent, Small Orifice, 10 mm BSP	175 psi
VK331	41a-f		06720B	4.2	57	Quick Response Model M Pendent, Small Orifice, ½" NPT	175 psi
VK332	40a-f		13961	4.2	57	Quick Response Fusible Element Pendent, Small Orifice, ½" NPT	175 psi
VK333	52a-f		10035	2.8	40.3	Quick Response Model M Horizontal Sidewall, Small Orifice, ½" NPT	175 psi
VK334	52u-z		13962	2.8	40.3	Quick Response Fusible Element Horizontal Sidewall, Small Orifice, 1/2" NPT	175 psi
VK335	72a-d		08983	4.2	57	Quick Response Model M Horizontal Sidewall, Small Orifice, 10 mm BSP	175 psi
VK337	52e-h		08985	4.2	57	Quick Response Model M Vertical Sidewall, Small Orifice, 10 mm BSP	175 psi
VK338	46a-d		14692	5.6	80.6	Quick Response Stainless Steel Upright, Standard Orifice, ½" NPT	175 psi
VK339	46a-d		14693	5.6	80.6	Quick Response Stainless Steel Pendent, Standard Orifice, ½" NPT	175 psi
VK340	51a-e		12286	2.8	40.3	HP Quick Response Model M Upright, Small Orifice, ½" NPT	250 psi
VK341	51h-k		13963	2.8	40.3	Quick Response Upright, Small Orifice, 1/2" NPT	250 psi
VK342	41a-f		12290	2.8	40.3	HP Quick Response Model M Pendent, Small Orifice, ½" NPT	250 psi
VK343	40a-f		13964	2.8	40.3	HP Quick Response Fusible Element Pendent, Small Orifice, ½" NPT	250 psi
VK344	52a-f		12287	2.8	40.3	HP Quick Response Model M Horizontal Sidewall, Small Orifice, ½" NPT	250 psi
VK345	51a-e	41u-z	07060 and 12984	5.6	80.6	Quick Response Model M Upright, Standard Orifice, 15 mm BSP	175 psi
VK346	52u-z		13965	2.8	40.3	HP Quick Response Fusible Element Horizontal Sidewall, Small Orifice, 1/2" NPT	250 psi
VK350	51a-e		06665B	8.0	115.2	Quick Response Model M Upright, Large Orifice, 3/4" NPT	175 psi
VK350	51a-e		14817	8.0	115.2	Quick Response Model M Upright, Large Orifice, 20 mm BSP	175 psi
VK350	51a-e		06764B	8.0	115.2	Quick Response Model M Upright, Large Orifice, ½" NPT	175 psi
VK351	51h-k		13976	8.0	115.2	Quick Response Fusible Element Upright, Large Orifice, 3/4" NPT	175 psi
VK352	41a-f		06666B	8.0	115.2	Quick Response Model M Pendent, Large Orifice, 3/4" NPT	175 psi
VK352-D	41q-l		06666BA-X	8.0	115.2	Standard/Quick Response Domed Concealed Pendent, Large Orifice, 3/4" NPT	175 psi
VK352	41a-f		06765B	8.0	115.2	Quick Response Model M Pendent, Large Orifice, ½" NPT	175 psi
VK352	N/A		12104	8.0	115.2	Quick Response Model M Pendent, Large Orifice, 3/4" NPT	175 psi
VK353	40a-f		13975	8.0	115.2	Quick Response Fusible Element Pendent, Large Orifice, 3/4" NPT	175 psi
VK353	42o-s		13975A-X	8.0	115.2	Quick Response Concealed Fusible Element Pendent, Large Orifice, 3/4" NPT	175 psi
VK354	51a-e		06768B	8.0	115.2	Quick Response Model M Conventional, Large Orifice, 3/4" NPT	175 psi
VK355	51h-k		13979	8.0	115.2	Quick Response Fusible Element Conventional, Large Orifice, 3/4" NPT	175 psi
VK360	43o-t		15591	8.0	115.2	Quick Response Horizontal Sidewall, Large Orifice, 3/4" NPT	175 psi
VK375	N/A		08338	11.2	161.3	Quick Response Model M ELO Upright, Extra-Large Orifice, 3/4 NPT (discontinued product)	175 psi
VK377	70a-e		08337	11.2	161.3	Quick Response Model M ELO Pendent, (Special Application), 3/4" NPT	175 psi
VK400	16a-d		06697B	5.6	80.6	Standard Response Model H Fusible Link Flush Pendent, Std. Orifice, ½" NPT	175 psi
VK401	N/A		07937	5.6	80.6	Standard Response Model H Fusible Link Flush Pendent, Std. Orifice, ½" NPT (discontinued product)	175 psi
VK402	53a-d		06702B	5.6	80.6	Quick Response Model H-1 Fusible Link Flush Pendent, Standard Orifice, ½" NPT	175 psi
VK403	N/A		10741	5.6	80.6	Quick Response Model H-4 Fusible Link Flush Horizontal Sidewall, Standard Orifice, ½" NPT (discontinued product)	175 psi
VK404	20a-e	57a-f	09783A	5.6	80.6	Standard Response/Quick Response Model B-2 Fusible Link Concealed Pendent, Standard Orifice, ½" NPT	175 psi
VK405	20a-e	57a-f	09782A	5.6	80.6	HP Standard Response/Quick Response Model B-2 Fusible Link Concealed Pendent, Standard Orifice, ½" NPT (discontinued product)	250 psi
VK406	N/A		10491A	8.0	115.2	Quick Response Model B-2 Fusible Link Concealed Pendent, Lrg. Orifice, ½" NPT (discontinued product)	175 psi
VK406	N/A		10681A	8.0	115.2	Quick Response Model B-2 Fusible Link Concealed Pendent, Large Orifice, 3/4" NPT (discontinued product)	175 psi
VK407	N/A		08617A	5.5	80.6	LPCB Approved Model B-1 Concealed Sprinkler (discontinued product)	175 psi
VK408	63a-e		11262A	5.6	80.6	Quick Response Concealed Horizontal Sidewall Sprinkler, Std. Orifice, ½" NPT (discontinued product)	175 psi
VK410	126a-h		10554	5.6	80.6	Quick Response Model HQR-2 Fusible Link Flush Pendent,	175 psi
VK412	126k-q		10579	5.6	80.6	Quick Response Model HQR-2 Fusible Link Flush Horizontal Sidewall, Standard Orifice, ½" NPT	175 psi
VK413	53a-d		11487	5.6	80.6	Quick Response Model H Fusible Link Flush Pendent, Standard Orifice, ½" NPT	175 psi
VK416	N/A		11600A	4.2	60	Quick Response Concealed Pendent, ½" NPT (discontinued product)	175 psi
VK420	145a-b		09458	3.8	54.8	Residential Model H-3 Fusible Link Flush Pendent, ½" NPT	175 psi
VK421	N/A		06858B	5.5	80.6	Residential Model H Fusible Link Flush Pendent, ½" NPT (discontinued product)	175 psi
VK425	N/A		10784A	4.1	59.1	Residential Model B-3 Fusible Link Flush Concealed, ½" NPT (discontinued product)	175 psi
VK430	140a-c		09530	4.3	62.0	Residential Model M-4 Pendent, ½" NPT	175 psi
VK432	N/A		10050	5.5	79.3	Residential Model M-5 Pendent, ½" NPT (discontinued product)	175 psi
VK434	N/A		10149	3.1	44.7	Residential Model M-6 Pendent, ½" NPT (discontinued product)	175 psi
VK436	N/A		12166	5.2	75.0	Residential Pendent, ½" NPT (discontinued product)	175 psi
VK436	N/A		12166A-X	5.2	75.0	Residential Domed Concealed Pendent, ½" NPT (discontinued product)	175 psi
VK438	N/A		12224	4.9	70.6	Residential Pendent, ½" NPT (discontinued product)	175 psi
VK438	N/A		12224A-X	4.9	70.6	Residential Domed Concealed Pendent, ½" NPT (discontinued product)	175 psi
VK440	N/A		09787	4.3	62.0	Residential Model M-4 Horizontal Sidewall, ½" NPT (discontinued product)	175 psi
VK442	N/A		12119	5.5	79.3	Residential Model M-5 Horizontal Sidewall, ½" NPT (discontinued product)	175 psi

Continued from page 11.

SIN*	Technical Data Page(s)	Sprinkler Base Part Number	Nominal K-Factor		Sprinkler Model and Type	Maximum Pressure Rating
			U.S.	metric		
VK444	N/A	10210	3.7	53.3	Residential Model M-7 Horizontal Sidewall, ½" NPT (discontinued product)	175 psi
VK446	N/A	06769B	5.5	79.3	Quick Response Light Hazard Horizontal Sidewall Sprinkler, 13 mm BSP (discontinued product)	175 psi
VK446	<a href="#">41o-s</a>	10037	5.6	80.6	Quick Response Light Hazard Horizontal Sidewall Sprinkler, 13 mm BSP (discontinued product)	175 psi
VK448	N/A	11810	4.3	62.0	Residential Horizontal Sidewall, ½" NPT (discontinued product)	175 psi
VK450	<a href="#">143m-t</a>	12357	4.2	57	Residential Horizontal Sidewall Sprinkler VK450 (K4.2) (discontinued product)	175 psi
VK454	<a href="#">20a-e</a>   <a href="#">57a-f</a>	12292	5.6	80.6	HP Quick Response Model B-2 Fusible Link Concealed Pendant, ½" NPT	250 psi
VK456	N/A	13620A	4.9	70.6	Residential Fusible Link Concealed Pendant, ½" NPT (discontinued product)	175 psi
VK4560	N/A	106871AJ	4.9	70.6	Residential Fusible Link Concealed Lead Free Pendant, ½" NPT (discontinued product)	175 psi
VK457	<a href="#">147u-z</a>	14694A	4.9	70.6	Residential Fusible Element Concealed Pendant, ½" NPT	175 psi
VK4570	<a href="#">151h-m</a>	16872AC	4.9	70.6	Residential Fusible Element Concealed Lead Free Pendant, ½" NPT	175 psi
VK458	<a href="#">140u-z</a>	13230	7.4	106.7	Residential Pendant, 3/4" NPT	175 psi
VK458	<a href="#">142u-z</a>	13230ABX	7.4	106.7	Residential Domed Concealed Pendant, 3/4" NPT	175 psi
VK460	<a href="#">152a-h</a>	13933	5.8	83.6	Residential Horizontal Sidewall, ½" NPT	175 psi
VK461	<a href="#">54h-l</a>	13831A	2.8	40.3	Standard/Quick Response Concealed Pendant, Small Orifice, ½" NPT	175 psi
VK461	<a href="#">140a-c</a>	14927	2.8	40.3	Adjustable Concealed Sprinkler Assembly, 1" NPT Male Connection	175 psi
VK461	<a href="#">140a-c</a>	14928	2.8	40.3	Adjustable Concealed Sprinkler Assembly, 1" NPT Female Connection	175 psi
VK462	<a href="#">54a-e</a>	13503A	5.6	80.6	Quick Response Concealed Pendant, Standard Orifice, ½" NPT	175 psi
VK462	<a href="#">54p-t</a>	15480A	5.6	80.6	Quick Response Concealed Pendant MRI, Standard Orifice, ½" NPT	175 psi
VK462	<a href="#">140a-c</a>	14918	5.6	80.6	Adjustable Concealed Sprinkler Assembly, 1" NPT Male Connection	175 psi
VK462	<a href="#">140a-c</a>	14919	5.6	80.6	Adjustable Concealed Sprinkler Assembly, 1" NPT Female Connection	175 psi
VK462	<a href="#">136g-i</a>	13642/CR	5.6	80.6	Cleanroom Sprinkler (Cover Assembly)	175 psi
VK463	<a href="#">54a-e</a>	13667A	5.6	80.6	HP Quick Response Concealed Pendant, Standard Orifice, ½" NPT	250 psi
VK464	<a href="#">55a-d</a>	13614A	8.0	115.2	Quick Response Concealed Pendant, Large Orifice, 3/4" NPT	175 psi
VK464	<a href="#">54p-t</a>	15481A	8.0	115.2	Quick Response Concealed Pendant MRI, Large Orifice, 3/4" NPT	175 psi
VK465	<a href="#">64a-e</a>	14262A	4.2	57	Quick Response Concealed Pendant, Small Orifice, 1/2" NPT	175 psi
VK465	<a href="#">140a-c</a>	14929	4.2	57	Adjustable Concealed Sprinkler Assembly, 1" NPT Male Connection	175 psi
VK465	<a href="#">140a-c</a>	14930	4.2	57	Adjustable Concealed Sprinkler Assembly, 1" NPT Female Connection	175 psi
VK466	<a href="#">141j-p</a>	13781	5.2	74.9	Residential Pendant, 1/2" NPT	175 psi
VK466	<a href="#">141r-w</a>	13781A-X	5.2	74.9	Residential Concealed Pendant, 1/2" NPT	175 psi
VK468	<a href="#">149m-t</a>	13637	4.9	70.6	Residential Pendant, ½" NPT	175 psi
VK467	<a href="#">158a-e</a>	19154	4.9	70.6	Residential Upright, ½" NPT	175 psi
VK4680	<a href="#">152h-o</a>	16876	4.9	70.6	Residential Lead Free Pendant, ½" NPT	175 psi
VK468	<a href="#">150u-z</a>	13637A-X	4.9	70.6	Residential Concealed Pendant, ½" NPT	175 psi
VK469	<a href="#">55o-s</a>	15764A	11.2	161.3	Quick Response ELO Concealed Pendant, Extra Large Orifice, 3/4" NPT	175 psi
VK470	<a href="#">153g-i</a>	17147	3.0	43.2	Residential Pendant, ½" NPT	175 psi
VK4700	<a href="#">154u-x</a>	17147	3.0	43.2	Residential Lead Free Pendant, ½" NPT	175 psi
VK472	<a href="#">148o-r</a>	16130	5.8	83.6	Residential Pendant, ½" NPT	175 psi
VK474	<a href="#">148h-l</a>	15790AC	5.8	83.6	Residential Concealed Pendant, ½" NPT	175 psi
VK476	<a href="#">145h-m</a>	15630MC/-	4.9	70.6	Residential Flush Pendant, ½" NPT	175 psi
VK480	<a href="#">153a-f</a>	16116AC	4.0	57.7	Residential Concealed Horizontal Sidewall, ½" NPT	175 psi
VK4800	<a href="#">151g-v</a>	16880AC	4.0	57.7	Residential Lead Free Concealed Horizontal Sidewall, ½" NPT	175 psi
VK481	<a href="#">63h-l</a>	17555A	5.6	80.6	Quick Response Concealed Horizontal Sidewall, ½" NPT	175psi
VK482	<a href="#">111a-g</a>	18385	5.6	80.6	Quick Response Flush Concealed Dry Pendant, 1" NPT	175psi
VK484	<a href="#">144h-m</a>	16240	4.2	57	Residential Horizontal Sidewall, ½" NPT	175 psi
VK4840	<a href="#">144o-t</a>	16881	4.2	57	Residential Lead Free Horizontal Sidewall, ½" NPT	175 psi
VK486	<a href="#">156u-z</a>	17315	4.0	57.7	Residential Horizontal Sidewall, ½" NPT	175 psi
VK488	<a href="#">157a-e</a>	18325	3.0	43.2	Freedom Residential Concealed Pendant, ½" NPT	175 psi
VK500	<a href="#">120a-f</a>	10284	14.0	-	Model S-1 ESFR Pendant, 3/4" NPT	175 psi
VK500	<a href="#">120a-f</a>	11350	-	202	Model S-1 ESFR Pendant, 20 mm NPT	175 psi
VK500	N/A	14779	14.0	-	Model S-1 ESFR Pendant, 3/4" NPT (discontinued product)	175 psi
VK501	<a href="#">122a-g</a>	14909	14.0	202	ESFR Dry Pendant, 2" Grooved Connection (discontinued product)	175 psi
VK501	<a href="#">122a-g</a>	14910	14.0	202	ESFR Dry Pendant, 1-1/2" NPT Threaded Connection (discontinued product)	175 psi
VK501	<a href="#">122a-g</a>	14911	14.0	202	ESFR Dry Pendant, 1-1/2" BSP Threaded Connection (discontinued product)	175 psi
VK502	<a href="#">122j-g</a>	042012	14.0	202	ESFR Dry Pendant, 2" Grooved Connection	175psi
VK502	<a href="#">122j-g</a>	042012	14.0	202	ESFR Dry Pendant, 1-1/2" NPT Threaded Connection	175psi
VK502	<a href="#">122j-g</a>	042012	14.0	202	ESFR Dry Pendant, 1-1/2" BSP Threaded Connection	175psi
VK503	<a href="#">123a-f</a>	14073	16.8	242	ESFR Pendant, 3/4" NPT	175 psi
VK503	<a href="#">123a-f</a>	14818	16.8	242	ESFR Pendant, 20 mm BSP	175 psi
VK504	<a href="#">129a-h</a>	19015	16.8	242	ESFR Dry Pendant, 1-1/2" Grooved Connection	175 psi
VK504	<a href="#">129a-h</a>	19016	16.8	242	ESFR Dry Pendant, 1-1/2" NPT Threaded Connection	175 psi
VK504	<a href="#">129a-h</a>	19017	16.8	242	ESFR Dry Pendant, 1-1/2" BSP Threaded Connection	175 psi
VK506	<a href="#">128a-f</a>	18493, 18494	22.4	320	ESFR Pendant, 1" NPT, 25mm BSP	175 psi
VK510	<a href="#">124a-f</a>	12080 and 15221	25.2	363.3	ESFR Pendant, 1" NPT (Part No. 15221 discontinued)	175 psi
VK510	<a href="#">124a-f</a>	12200 and 14958	25.2	363.3	ESFR Pendant, 25 mm BSP (Part No. 14958 discontinued)	175 psi
VK520	<a href="#">121a-e</a>	10625	14.0	202	Model A-4 ESFR Upright, 3/4" NPT	175 psi
VK530	<a href="#">13e-j</a>	09679	11.2	161.3	Standard Response Model M ELO Upright (Special Application), 3/4" NPT	175 psi
VK530	<a href="#">13e-j</a>	14819	11.2	161.3	Standard Response Model M ELO Upright (Special Application), 20 mm BSP	175 psi
VK531	<a href="#">70h-k</a>	10633	11.2	161.3	Model M Quick Response ELO Upright (Special Application), 3/4" NPT	175 psi
VK532	<a href="#">83a-f</a>	08687	11.2	161.3	Standard/Quick Response EC LH/OH Model M ELO Upright, 3/4" NPT	175 psi
VK533	<a href="#">70w-z</a>	13978	11.2	161.3	Quick Response ELO Fusible Element Upright (Special Application), 3/4" NPT	175 psi
VK534	<a href="#">83a-f</a>	08340	11.2	161.3	Standard and QR ECOH Model M ELO Pendant, 3/4" NPT	175 psi
VK535	<a href="#">83o-t</a>	14139	11.2	161.3	Standard and QR ECOH ELO Fusible Element Upright, 3/4" NPT	175 psi
VK536	<a href="#">13e-j</a>	07961	11.2	161.3	Standard Response Model M ELO Upr (Special Application) and Pdt, 3/4" NPT	175 psi
VK536	<a href="#">13e-j</a>	14820	11.2	161.3	Standard Response Model M ELO Upr (Special Application) and Pdt, 20 mm BSP	175 psi

Continued from page 12.

SIN*	Technical Data Page(s)	Sprinkler Base Part Number	Nominal K-Factor		Sprinkler Model and Type	Maximum Pressure Rating
			U.S.	metric		
VK537	<a href="#">83o-t</a>	14611	11.2	161.3	Standard and QR ECOH ELO Fusible Element Pendent, 3/4" NPT	175 psi
VK538	<a href="#">89h-l</a>	17115A	11.2	161.3	EC/QREC OH Concealed Pendent, Extra-Large Orifice, 3/4" NPT	175 psi
VK540	<a href="#">113a-e</a>	13167	11.2	161.3	Model A-2 Standard Response High Challenge® Upright Large Drop, ELO, 3/4" NPT	175 psi
VK540	<a href="#">113a-e</a>	13166	11.2	161.3	Model A-2 Standard Response High Challenge® Upright Large Drop, ELO, 1/2" NPT	175 psi
VK550	<a href="#">131a-e</a>	10138--U and 12986--U	5.6	80.6	Standard Response Model M Upright Intermediate Level, Standard Orifice, 1/2" NPT	175 psi
VK551	<a href="#">131a-e</a>	12279--U	5.6	80.6	Quick Response Fusible Element Upright Intermediate Level, Standard Orifice, 1/2" NPT	175 psi
VK552	<a href="#">131a-e</a>	05557--U and 12973--U	5.6	80.6	Standard Response Model M Fusible Link Upright Intermediate Level, Standard Orifice, 1/2" NPT	175 psi
VK556	<a href="#">131a-e</a>	06661B--U and 12978--U	5.6	80.6	Quick Response Model M Upright Intermediate Level, Standard Orifice, 1/2" NPT	175 psi
VK558	<a href="#">131a-e</a>	12281--U	5.6	80.6	HP Quick Response Model M Upright Intermediate Level, Standard Orifice, 1/2" NPT	250 psi
VK560	<a href="#">131a-e</a>	10141--U	8.0	115.2	Standard Response Model M Upright Intermediate Level, Large Orifice, 3/4" NPT	175 psi
VK560	<a href="#">131a-e</a>	10220--U	8.0	115.2	Standard Response Model M Upright Intermediate Level, Large Orifice, 1/2" NPT	175 psi
VK562	<a href="#">131a-e</a>	05514--U	8.0	115.2	Standard Response Model M Fusible Link Upright Intermediate Level, Large Orifice, 3/4" NPT	175 psi
VK566	<a href="#">131a-e</a>	06665B--U	8.0	115.2	Quick Response Model M Upright Intermediate Level, Large Orifice, 3/4" NPT	175 psi
VK567	<a href="#">131a-e</a>	13976--U	8.0	115.2	Quick Response Model M Upright Intermediate Level, Large Orifice, 3/4" NPT	175 psi
VK570	<a href="#">83h-m</a>	13840	14.0	202	Extended Coverage Ordinary Hazard Upright, 3/4" NPT	175 psi
VK572	<a href="#">83h-m</a>	13722	14.0	202	Extended Coverage Ordinary Hazard Pendent, 3/4" NPT	175 psi
VK580	<a href="#">13a-d</a>	12739	16.8	242.2	Standard Response Upright, 3/4" NPT	175 psi
VK592	<a href="#">114l-s</a>	14243	19.6	282.6	Standard Response Pendent, 1" NPT	175 psi
VK592	N/A	15483	19.6	282.6	Standard Response Pendent, 1" NPT (discontinued product)	175 psi
VK592	<a href="#">114l-s</a>	15468	19.6	282.6	Standard Response Pendent, 25 mm BSP	175 psi
VK592	N/A	15484	19.6	282.6	Standard Response Pendent, 25 mm BSP (discontinued product)	175 psi
VK595	<a href="#">124l-m</a>	16859	25.2	363.3	EC Upright (Storage-Density/Area), 1" NPT	175 psi
VK595	<a href="#">124l-m</a>	16885	25.2	363.3	EC Upright (Storage-Density/Area), 25 mm BSP	175 psi
VK600	<a href="#">81a-f</a>	06778B	5.6	80.6	Standard Response/Quick Response Model M Extended Coverage Pendent, Standard Orifice, 1/2" NPT	175 psi
VK601	<a href="#">81h-l</a>	13969	5.6	80.6	Quick Response EC Fusible Element Pendent, Standard Orifice, 1/2" NPT	175 psi
VK602	<a href="#">81a-f</a>	07077B	8.0	115.2	Standard Response/Quick Response Model M Extended Coverage Pendent, Large Orifice, 3/4" NPT	175 psi
VK603	<a href="#">81h-l</a>	14140	8.0	115.2	Quick Response Extended Coverage Pendent, Large Orifice, 3/4" NPT	175 psi
VK604	<a href="#">90e-i</a>	10335	5.6	80.6	Standard Response/Quick Response Model M-5 Extended Coverage Pendent, Standard Orifice, 1/2" NPT	175 psi
VK605	<a href="#">91a-f</a>	12120	5.6	80.6	Model M-5 HSW (with EC, QREC, and Specific Application Listings), 1/2" NPT	175 psi
VK606	<a href="#">82a-f</a>	13005	8.0	115.2	Standard Response/Quick Response Model M Extended Coverage Horizontal Sidewall, Large Orifice, 3/4" NPT	175 psi
VK607	<a href="#">90v-z</a>	13970	5.6	80.6	Standard Response/Quick Response Extended Coverage Fusible Element Pendent, Standard Orifice, 1/2" NPT	175 psi
VK608	<a href="#">85a-f</a>	08339	11.2	161.3	Standard Response/Quick Response Model M Extended Coverage Light Hazard Extra-Large Orifice Pendent, 3/4" NPT	175 psi
VK609	<a href="#">91h-m</a>	13971	5.6	80.6	Standard Response/Quick Response Extended Coverage Fusible Element Horizontal Sidewall, Standard Orifice, 1/2" NPT	175 psi
VK610	<a href="#">90e-i</a>	12294	5.6	80.6	HP Standard Response/Quick Response Model M-5 Extended Coverage Pendent, Standard Orifice, 1/2" NPT	250 psi
VK611	<a href="#">90v-z</a>	13972	5.6	80.6	HP Standard Response/Quick Response Extended Coverage Fusible Element Pendent, Standard Orifice, 1/2" NPT	250 psi
VK612	<a href="#">91a-f</a>	12295	5.6	80.6	HP Standard Response/Quick Response Model M-5 EC HSW, 1/2" NPT	250 psi
VK613	<a href="#">91h-m</a>	13973	5.6	80.6	HP Standard Response/Quick Response Extended Coverage Fusible Element Horizontal Sidewall, Standard Orifice, 1/2" NPT	250 psi
VK614-D	<a href="#">88a-f</a>	06778BA-X	5.6	80.6	Standard Response/Quick Response Extended Coverage Domed Concealed Pendent, Standard Orifice, 1/2" NPT	175 psi
VK616-D	<a href="#">88a-f</a>	07077BA-X	8.0	115.2	Standard Response/Quick Response Extended Coverage	175 psi
VK617	<a href="#">85h-m</a>	14141	11.2	161.3	Standard Response/Quick Response Extended Coverage Light Hazard Extra-Large Orifice Fusible Element Pendent, 3/4" NPT	175 psi
VK618-D	<a href="#">86a-f</a>	08339A-X	11.2	161.3	Standard Response/Quick Response Extended Coverage Domed Concealed Light Hazard Extra-Large Orifice Pendent, 3/4" NPT	175 psi
VK625	N/A	08498A	5.6	80.6	Standard Response/Quick Response Model B-1 Fusible Link Extended Coverage Concealed Pendent, Standard Orifice, 1/2" NPT (discontinued product)	175 psi
VK627	N/A	10485A	8.0	115.2	Standard Response/Quick Response Model B-2 Fusible Link Extended Coverage Concealed Pendent, Large Orifice, 1/2" NPT (discontinued product)	175 psi
VK627	N/A	10680A	8.0	115.2	Standard Response/Quick Response Model B-2 Fusible Link Extended Coverage Concealed Pendent, Large Orifice, 3/4" NPT (discontinued product)	175 psi
VK630	<a href="#">80a-e</a>	13500	8.0	115.2	Quick Response Extended Coverage Horizontal Sidewall, Large Orifice, 3/4" NPT	175 psi
VK630-D	<a href="#">87h-m</a>	13500A-X	8.0	115.2	Quick Response EC Domed Concealed HSW, Large Orifice, 3/4" NPT	175 psi
VK631	N/A	16112	8.0	115.2	HP Quick Response Extended Coverage HSW, Large Orifice, 3/4" NPT (discontinued product)	300 psi
VK631-D	N/A	16112A-X	8.0	115.2	HP Quick Response EC Domed Concealed HSW, Large Orifice, 3/4" NPT (discontinued product)	300 psi
VK632	<a href="#">92a-f</a>	14613A	5.6	80.6	Quick Response EC Concealed Pendent, Standard Orifice, 1/2" NPT	175 psi
VK634	<a href="#">92a-f</a>	14535A	8.0	115.2	Quick Response EC Concealed Pendent, Large Orifice, 3/4" NPT	175 psi
VK636	<a href="#">89a-e</a>	16102A	11.2	161.3	Quick Response EC LH Concealed Pendent, Extra-Large Orifice, 3/4" NPT	175 psi
VK638	<a href="#">84n-r</a>	17375	8.0	115.2	Quick Response EC Horizontal Sidewall, Large Orifice, 3/4" NPT	175psi
VK638	<a href="#">84u-z</a>	17375	8.0	115.2	Quick Response EC Concealed Horizontal Sidewall, Large Orifice, 3/4" NPT	175psi

Continued from page 13.

SIN*	Technical Data Page(s)	Sprinkler Base Part Number	Nominal K-Factor		Sprinkler Model and Type	Maximum Pressure Rating
			U.S.	metric		
VK680	<a href="#">87n-q</a>	17114AC	8.0	115.2	Quick Response EC Concealed HSW, Large Orifice, 3/4" NPT	175 psi
VK740	<a href="#">20-32</a>	05133AAJ or AJJ	1.2	17.3	30° Model A-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK741	<a href="#">20-32</a>	05133AAK or AJK	1.2	17.3	60° Model A-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK742	<a href="#">20-32</a>	05133AAL or AJL	1.2	17.3	90° Model A-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK743	<a href="#">20-32</a>	05133AAM or AJM	1.4	20.2	120° Model A-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK744	<a href="#">20-32</a>	05133AAN or AJN	1.4	20.2	140° Model A-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK750	<a href="#">20-32</a>	05134AAJ or AJJ	2.0	28.8	30° Model A-2X Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK751	<a href="#">20-32</a>	05134AAK or AJK	2.0	28.8	60° Model A-2X Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK752	<a href="#">20-32</a>	05134AAL or AJL	2.0	28.8	90° Model A-2X Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK753	<a href="#">20-32</a>	05134AAM or AJM	2.2	31.7	120° Model A-2X Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK754	<a href="#">20-32</a>	05134AAN or AJN	2.2	31.7	140° Model A-2X Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK760	<a href="#">20-32</a>	05135AAJ or AJJ	2.8	40.3	30° Model B-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK761	<a href="#">20-32</a>	05135AAK or AJK	2.8	40.3	60° Model B-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK762	<a href="#">20-32</a>	05135AAL or AJL	2.8	40.3	90° Model B-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK763	<a href="#">20-32</a>	05135AAM or AJM	3.3	47.6	120° Model B-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK764	<a href="#">20-32</a>	05135AAN or AJN	3.3	47.6	140° Model B-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK770	<a href="#">20-32</a>	05136AAJ or AJJ	3.4	49	30° Model C-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK771	<a href="#">20-32</a>	05136AAK or AJK	3.4	49	60° Model C-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK772	<a href="#">20-32</a>	05136AAL or AJL	3.8	54.8	90° Model C-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK773	<a href="#">20-32</a>	05136AAM or AJM	3.9	56.2	120° Model C-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK774	<a href="#">20-32</a>	05136AAN or AJN	3.9	56.2	140° Model C-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK780	<a href="#">20-32</a>	05137AAJ or AJJ	4.7	67.8	30° Model D-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK781	<a href="#">20-32</a>	05137AAK or AJK	4.7	67.8	60° Model D-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK782	<a href="#">20-32</a>	05137AAL or AJL	5.0	72.1	90° Model D-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK783	<a href="#">20-32</a>	05137AAM or AJM	5.2	75.0	120° Model D-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK784	<a href="#">20-32</a>	05137AAN or AJN	5.2	75.0	140° Model D-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK790	<a href="#">11-14</a>	01320B	1.5	21.6	Model C-1 Window Sprinkler, 1/4" Orifice, 1/2" NPT	N/A
VK791	<a href="#">11-14</a>	01321B	2.1	30.3	Model C-1 Window Sprinkler, 5/16" Orifice, 1/2" NPT	N/A
VK792	<a href="#">11-14</a>	01322B	3.0	43.2	Model C-1 Window Sprinkler, 3/8" Orifice, 1/2" NPT	N/A
VK793	<a href="#">11-14</a>	01323B	4.3	62	Model C-1 Window Sprinkler, 7/16" Orifice, 1/2" NPT	N/A
VK794	<a href="#">11-14</a>	01324B	5.8	83.6	Model C-1 Window Sprinkler, 1/2" Orifice, 1/2" NPT	N/A
VK795	<a href="#">11-14</a>	01325B	7.3	105.2	Model C-1 Window Sprinkler, 5/8" Orifice, 3/4" NPT	N/A
VK796	<a href="#">11-14</a>	01326B	8.1	117.3	Model C-1 Window Sprinkler, 3/4" Orifice, 3/4" NPT	N/A
VK800	<a href="#">286a-c</a>	07848	-	-	Model M HP Fixed Temperature Release, Standard Orifice, 1/2" NPT	250 psi
VK810	<a href="#">32a-i</a>	12867	7.2	103.8	65° Model E Spray Nozzle, 1/2" NPT	175 psi
VK810	<a href="#">32a-i</a>	12868	5.6	80.6	65° Model E Spray Nozzle, 1/2" NPT	175 psi
VK810	<a href="#">32a-i</a>	12869	4.1	59.1	65° Model E Spray Nozzle, 1/2" NPT	175 psi
VK810	<a href="#">32a-i</a>	12870	3.2	46.3	65° Model E Spray Nozzle, 1/2" NPT	175 psi
VK810	<a href="#">32a-i</a>	12871	2.3	33.2	65° Model E Spray Nozzle, 1/2" NPT	175 psi
VK810	<a href="#">32a-i</a>	12872	1.8	25.9	65° Model E Spray Nozzle, 1/2" NPT	175 psi
VK810	<a href="#">32a-i</a>	12873	1.2	17.3	65° Model E Spray Nozzle, 1/2" NPT	175 psi
VK811	<a href="#">32a-i</a>	12874	7.2	103.8	80° Model E Spray Nozzle, 1/2" NPT	175 psi
VK811	<a href="#">32a-i</a>	12875	5.6	80.6	80° Model E Spray Nozzle, 1/2" NPT	175 psi
VK811	<a href="#">32a-i</a>	12876	4.1	59.1	80° Model E Spray Nozzle, 1/2" NPT	175 psi
VK811	<a href="#">32a-i</a>	12877	3.2	46.3	80° Model E Spray Nozzle, 1/2" NPT	175 psi
VK811	<a href="#">32a-i</a>	12878	2.3	33.2	80° Model E Spray Nozzle, 1/2" NPT	175 psi
VK811	<a href="#">32a-i</a>	12879	1.8	25.9	80° Model E Spray Nozzle, 1/2" NPT	175 psi
VK811	<a href="#">32a-i</a>	12880	1.2	17.3	80° Model E Spray Nozzle, 1/2" NPT	175 psi
VK812	<a href="#">32a-i</a>	12881	7.2	103.8	95° Model E Spray Nozzle, 1/2" NPT	175 psi
VK812	<a href="#">32a-i</a>	12882	5.6	80.6	95° Model E Spray Nozzle, 1/2" NPT	175 psi
VK812	<a href="#">32a-i</a>	12883	4.1	59.1	95° Model E Spray Nozzle, 1/2" NPT	175 psi
VK812	<a href="#">32a-i</a>	12884	3.2	46.3	95° Model E Spray Nozzle, 1/2" NPT	175 psi
VK812	<a href="#">32a-i</a>	12885	2.3	33.2	95° Model E Spray Nozzle, 1/2" NPT	175 psi
VK812	<a href="#">32a-i</a>	12886	1.8	25.9	95° Model E Spray Nozzle, 1/2" NPT	175 psi
VK812	<a href="#">32a-i</a>	12887	1.2	17.3	95° Model E Spray Nozzle, 1/2" NPT	175 psi
VK813	<a href="#">32a-i</a>	12888	7.2	103.8	110° Model E Spray Nozzle, 1/2" NPT	175 psi
VK813	<a href="#">32a-i</a>	12889	5.6	80.6	110° Model E Spray Nozzle, 1/2" NPT	175 psi
VK813	<a href="#">32a-i</a>	12890	4.1	59.1	110° Model E Spray Nozzle, 1/2" NPT	175 psi
VK813	<a href="#">32a-i</a>	12891	3.2	46.3	110° Model E Spray Nozzle, 1/2" NPT	175 psi
VK813	<a href="#">32a-i</a>	12892	2.3	33.2	110° Model E Spray Nozzle, 1/2" NPT	175 psi
VK813	<a href="#">32a-i</a>	12893	1.8	25.9	110° Model E Spray Nozzle, 1/2" NPT	175 psi
VK813	<a href="#">32a-i</a>	12894	1.2	17.3	110° Model E Spray Nozzle, 1/2" NPT	175 psi
VK814	<a href="#">32a-i</a>	12895	7.2	103.8	125° Model E Spray Nozzle, 1/2" NPT	175 psi
VK814	<a href="#">32a-i</a>	12896	5.6	80.6	125° Model E Spray Nozzle, 1/2" NPT	175 psi
VK814	<a href="#">32a-i</a>	12897	4.1	59.1	125° Model E Spray Nozzle, 1/2" NPT	175 psi
VK814	<a href="#">32a-i</a>	12898	3.2	46.3	125° Model E Spray Nozzle, 1/2" NPT	175 psi
VK814	<a href="#">32a-i</a>	12899	2.3	33.2	125° Model E Spray Nozzle, 1/2" NPT	175 psi
VK814	<a href="#">32a-i</a>	12900	1.8	25.9	125° Model E Spray Nozzle, 1/2" NPT	175 psi
VK814	<a href="#">32a-i</a>	12901	1.2	17.3	125° Model E Spray Nozzle, 1/2" NPT	175 psi
VK815	<a href="#">32a-i</a>	12902	7.2	103.8	140° Model E Spray Nozzle, 1/2" NPT	175 psi



Continued from page 14.

SIN*	Technical Data Page(s)	Sprinkler Base Part Number	Nominal K-Factor		Sprinkler Model and Type	Maximum Pressure Rating
			U.S.	metric		
VK815	<a href="#">32a-i</a>	12903	5.6	80.6	140° Model E Spray Nozzle, ½" NPT	175 psi
VK815	<a href="#">32a-i</a>	12904	4.1	59.1	140° Model E Spray Nozzle, ½" NPT	175 psi
VK815	<a href="#">32a-i</a>	12905	3.2	46.3	140° Model E Spray Nozzle, ½" NPT	175 psi
VK815	<a href="#">32a-i</a>	12906	2.3	33.2	140° Model E Spray Nozzle, ½" NPT	175 psi
VK815	<a href="#">32a-i</a>	12907	1.8	25.9	140° Model E Spray Nozzle, ½" NPT	175 psi
VK815	<a href="#">32a-i</a>	12908	1.2	17.3	140° Model E Spray Nozzle, ½" NPT	175 psi
VK816	<a href="#">32a-i</a>	12909	7.2	103.8	160° Model E Spray Nozzle, ½" NPT	175 psi
VK816	<a href="#">32a-i</a>	12910	5.6	80.6	160° Model E Spray Nozzle, ½" NPT	175 psi
VK816	<a href="#">32a-i</a>	12911	4.1	59.1	160° Model E Spray Nozzle, ½" NPT	175 psi
VK816	<a href="#">32a-i</a>	12912	3.2	46.3	160° Model E Spray Nozzle, ½" NPT	175 psi
VK816	<a href="#">32a-i</a>	12913	2.3	33.2	160° Model E Spray Nozzle, ½" NPT	175 psi
VK816	<a href="#">32a-i</a>	12914	1.8	25.9	160° Model E Spray Nozzle, ½" NPT	175 psi
VK816	<a href="#">32a-i</a>	12915	1.2	17.3	160° Model E Spray Nozzle, ½" NPT	175 psi
VK817	<a href="#">32a-i</a>	12916	7.2	103.8	180° Model E Spray Nozzle, ½" NPT	175 psi
VK817	<a href="#">32a-i</a>	12917	5.6	80.6	180° Model E Spray Nozzle, ½" NPT	175 psi
VK817	<a href="#">32a-i</a>	12918	4.1	59.1	180° Model E Spray Nozzle, ½" NPT	175 psi
VK817	<a href="#">32a-i</a>	12919	3.2	46.3	180° Model E Spray Nozzle, ½" NPT	175 psi
VK817	<a href="#">32a-i</a>	12920	2.3	33.2	180° Model E Spray Nozzle, ½" NPT	175 psi
VK817	<a href="#">32a-i</a>	12921	1.8	25.9	180° Model E Spray Nozzle, ½" NPT	175 psi
VK817	<a href="#">32a-i</a>	12922	1.2	17.3	180° Model E Spray Nozzle, ½" NPT	175 psi
VK824	<a href="#">33a-f Euro</a>	13633	.82	12.0	Model EM Spray Nozzle	175 psi
VK825	<a href="#">33a-f Euro</a>	13872	.48	7.0	Model EM Spray Nozzle	175 psi
VK900	<a href="#">112a-i</a>	12493	4.2	57	Coin™ QR Upright (Specific Application), Standard Orifice, ½" NPT	175 psi
VK901	<a href="#">112c-z</a>	12676AE	4.2	57	Coin™ QR Fusible Element Upright (Specific Application), Standard Orifice, ½" NPT	175 psi
VK920	<a href="#">127a-e</a>	15111	5.6	80.6	Flat Spray QR Pendent Sprinkler, Standard Orifice, 1/2" NPT (discontinued product)	175 psi
VK922	<a href="#">127a-e</a>	15112	8.0	115.2	Flat Spray QR Pendent Sprinkler, Large Orifice, 3/4" NPT (discontinued product)	175 psi

\* The Sprinkler Identification Number (SIN) is stamped on the sprinklers.