



Section I **Spray Nozzles**

TABLE OF CONTENTS

Model E Spray Nozzles, Blow Off Plugs, Model EM, Model EM Dust Cover, Open Window Sprinklers	I-1
Frame Style Spray Nozzles, Model A/B/C/D Spray Nozzles, Plastic Dust Covers	I-2

Notes

1. Refer to Viking technical data pages for complete product specifications. You may print or download technical data by visiting www.vikinggroupinc.com.
2. List prices effective June 2026. Supersedes previous list price book.
3. All sales by Viking are subject to the Terms & Conditions found on the last page of this book.

DESCRIPTION	SPRAY ANGLE	PART NUMBER	LIST PRICE (each)	
			Brass	Nickel
Finish Suffix ¹			A	J
MODEL E SPRAY NOZZLE				
	1/2" / 15mm NPT			
<u>VK810</u>				
K=7.2 (10,4)	65°	12867	\$225.80	\$322.62
K=5.6 (8,1)	65°	12868	\$225.80	\$322.62
K=4.1 (5,9)	65°	12869	\$225.80	\$322.62
K=3.2 (4,6)	65°	12870	\$225.80	\$322.62
K=2.3 (3,3)	65°	12871	\$225.80	\$322.62
K=1.8 (2,6)	65°	12872	\$225.80	\$322.62
K=1.2 (1,7)	65°	12873	\$225.80	\$322.62
<u>VK811</u>				
K=7.2 (10,4)	80°	12874	\$225.80	\$322.62
K=5.6 (8,1)	80°	12875	\$225.80	\$322.62
K=4.1 (5,9)	80°	12876	\$225.80	\$322.62
K=3.2 (4,6)	80°	12877	\$225.80	\$322.62
K=2.3 (3,3)	80°	12878	\$225.80	\$322.62
K=1.8 (2,6)	80°	12879	\$225.80	\$322.62
K=1.2 (1,7)	80°	12880	\$225.80	\$322.62
<u>VK812</u>				
K=7.2 (10,4)	95°	12881	\$225.80	\$322.62
K=5.6 (8,1)	95°	12882	\$225.80	\$322.62
K=4.1 (5,9)	95°	12883	\$225.80	\$322.62
K=3.2 (4,6)	95°	12884	\$225.80	\$322.62
K=2.3 (3,3)	95°	12885	\$225.80	\$322.62
K=1.8 (2,6)	95°	12886	\$225.80	\$322.62
K=1.2 (1,7)	95°	12887	\$225.80	\$322.62
<u>VK813</u>				
K=7.2 (10,4)	110°	12888	\$225.80	\$322.62
K=5.6 (8,1)	110°	12889	\$225.80	\$322.62
K=4.1 (5,9)	110°	12890	\$225.80	\$322.62
K=3.2 (4,6)	110°	12891	\$225.80	\$322.62
K=2.3 (3,3)	110°	12892	\$225.80	\$322.62
K=1.8 (2,6)	110°	12893	\$225.80	\$322.62
K=1.2 (1,7)	110°	12894	\$225.80	\$322.62
<u>VK814</u>				
K=7.2 (10,4)	125°	12895	\$225.80	\$322.62
K=5.6 (8,1)	125°	12896	\$225.80	\$322.62
K=4.1 (5,9)	125°	12897	\$225.80	\$322.62
K=3.2 (4,6)	125°	12898	\$225.80	\$322.62
K=2.3 (3,3)	125°	12899	\$225.80	\$322.62
K=1.8 (2,6)	125°	12900	\$225.80	\$322.62
K=1.2 (1,7)	125°	12901	\$225.80	\$322.62
<u>VK815</u>				
K=7.2 (10,4)	140°	12902	\$225.80	\$322.62
K=5.6 (8,1)	140°	12903	\$225.80	\$322.62
K=4.1 (5,9)	140°	12904	\$225.80	\$322.62
K=3.2 (4,6)	140°	12905	\$225.80	\$322.62
K=2.3 (3,3)	140°	12906	\$225.80	\$322.62
K=1.8 (2,6)	140°	12907	\$225.80	\$322.62
K=1.2 (1,7)	140°	12908	\$225.80	\$322.62
<u>VK816</u>				
K=7.2 (10,4)	160°	12909	\$225.80	\$322.62
K=5.6 (8,1)	160°	12910	\$225.80	\$322.62
K=4.1 (5,9)	160°	12911	\$225.80	\$322.62
K=3.2 (4,6)	160°	12912	\$225.80	\$322.62
K=2.3 (3,3)	160°	12913	\$225.80	\$322.62
K=1.8 (2,6)	160°	12914	\$225.80	\$322.62
K=1.2 (1,7)	160°	12915	\$225.80	\$322.62
<u>VK817</u>				
K=7.2 (10,4)	180°	12916	\$225.80	\$322.62
K=5.6 (8,1)	180°	12917	\$225.80	\$322.62
K=4.1 (5,9)	180°	12918	\$225.80	\$322.62
K=3.2 (4,6)	180°	12919	\$225.80	\$322.62
K=2.3 (3,3)	180°	12920	\$225.80	\$322.62
K=1.8 (2,6)	180°	12921	\$225.80	\$322.62
K=1.2 (1,7)	180°	12922	\$225.80	\$322.62
OPEN=Z				
IPG V216				

IPG V216

DESCRIPTION	SIZE	PART NUMBER	LIST PRICE (each)		
Blow Off Plug Use with Model E Spray Nozzles Packaged 10 plugs per bag	<u>Kfactor</u>		Price Per Bag		
	1.2K	13161	\$47.90		
	1.8K	13161	\$47.90		
	2.3K	13161	\$47.90		
	3.2K	13159	\$47.90		
	4.1K	13160	\$47.90		
	5.6K	13161	\$47.90		
	7.2K	13162	\$47.90		
IPG V216					
LOW PRESSURE MODEL EM SPRAY NOZZLE¹ VdS Approved K=0.8 (12 LPM/Bar ^{1/2}) K=0.5 (7 LPM/Bar ^{1/2})	<u>Spray Angle</u>		LIST PRICE (each)		
			Brass A	Nickel J	
	125°	13633	\$256.58	\$366.25	
	95°	13872	\$256.58	\$366.25	
OPEN=Z					
IPG V216					
DUST COVER MODEL EM SPRAY NOZZLE	Stainless Steel	13632	LIST PRICE (each)		
			\$280.54		
DESCRIPTION	MODEL NUMBER (SIN)		PART NUMBER	LIST PRICE (each)	
Open Window Sprinkler Model C-1 180° Flat Spray Pattern Brass K=1.5 (2, 1) K=2.1 (3, 0) K=3.0 (4, 3) K=4.3 (6, 2) K=5.8 (8, 4) K=7.3 (10, 5) K=8.1 (11, 7) Chrome K=1.5 (2, 1) K=2.1 (3, 0) K=3.0 (4, 3) K=4.3 (6, 2) K=5.8 (8, 4) K=7.3 (10, 5) K=8.1 (11, 7)	<u>Model No. (SIN)</u>				
	Thread 1/2" NPT				
	VK790		01320BA	\$142.06	
	VK791		01321BA	\$142.06	
	VK792		01322BA	\$142.06	
	VK793		01323BA	\$142.06	
	VK794		01324BA	\$150.80	
	Thread 3/4" NPT				
	VK795		01325BA	\$157.22	
	VK796		01326BA	\$157.22	
	Thread 1/2" NPT				
	VK790		01320BF	\$163.03	
	VK791		01321BF	\$163.03	
	VK792		01322BF	\$163.03	
	VK793		01323BF	\$163.03	
	VK794		01324BF	\$169.90	
	Thread 3/4" NPT				
	VK795		01325BF	\$178.14	
	VK796		01326BF	\$178.14	
	IPG V217				

¹ Add the desired finish suffix to the base part number.

DESCRIPTION	SPRAY ANGLE	MODEL NUMBER	PART NUMBER	LIST PRICE	DESCRIPTION	SPRAY ANGLE	PART NUMBER	LIST PRICE (ea)	
		(SIN)		(each)				Brass	Black PTFE
					Finish Suffix ³				
					A				
					N				

² For installation of Model A2, A2X, B2, C2 and D2 spray nozzles, use standard crescent wrench.

³ Add the desired finished suffix to the base part number.