

Northbrook, Illinois • (847) 272-8800
Melville, New York • (631) 271-6200
Santa Clara, California • (408) 985-2400
Research Triangle Park,
North Carolina • (919) 549-1400
Camas, Washington • (360) 817-5500



VIKING CORP
MR E JACKSON
210 N INDUSTRIAL PARK RD
HASTINGS MI 49058

Your most recent Certification is shown below. You may also view this information on UL's Online Certifications Directory at www.ul.com. Please review the text and contact the Conformity Assessment Services staff member who handled your project if revisions are required.

Effective June 30, 2004, UL plans to discontinue the distribution of Listing Information Pages in a printed format since this information is readily available via UL's Online Certifications Directory at www.ul.com. To view your company's current Listing Information or for ordering your company's Listing Information in the 3 x 5-inch card format (effective June 30, 2004), please refer to www.ul.com. Prior to June 30, 2004, the 3 x 5 inch Listing Cards can be ordered using the enclosed form. If you have any questions or comments about the discontinuance of the printed Listing Information Pages, please email Susan Druktenis at Susan.M.Druktenis@us.ul.com.

VLFT May 18, 2004
Special System Water Control Valves, Deluge Type

VIKING CORP
210 N INDUSTRIAL PARK RD, HASTINGS MI 49058

EX2006

Water control valves for horizontal or vertical installation. Models E-3, E-4, H-3, H-4 in the 1-1/2 in. size rated 250 psig. Models E-1, E-2, H-1, H-2 in the 2, 3, 4 and 6 in. sizes rated 250 psig. Models F-1, F-2 in the 3, 4, 6 and 8 in. size rated 250 psig, and Models J-1, J-2 in the 4, 6 and 8 in. size rated 250 psig. For operation by wet pilot sprinklers, the height of pilot line above valve is limited as shown in the Manufacturer's Installations Instructions. For accessories used with these valves, see listing under "Accessories For Special Systems".

Models E-1 and E-2 water control valves in the 2, 3, 4 and 6 in. sizes, and Models E-3, E-4 in the 1-1/2 in. size and Models F-1, F-2 in the 3, 4, 6 and 8 in sizes are rated to 250 psig when provided with optional Viking EZ Trim, installed in accordance with the manufacturer's installation instructions. For accessories used with these valves, see Listing under "Accessories For Special Systems".

Models H-1, H-2 water control valves in the 2, 4 and 6 in. sizes are rated 175 psig when provided with optional Viking pressure regulating trim assembly Part Nos. 09066, 09067, 09068, installed in accordance with the manufacturer's installation instructions.

Authorities having jurisdiction to be consulted before installation.

LOOK FOR LISTING MARK ON PRODUCT

Northbrook, Illinois • (847) 272-8800
Melville, New York • (631) 271-6200
Santa Clara, California • (408) 985-2400
Research Triangle Park,
North Carolina • (919) 549-1400
Camas, Washington • (360) 817-5500



VIKING CORP
MR E JACKSON
210 N INDUSTRIAL PARK RD
HASTINGS MI 49058

Your most recent Certification is shown below. You may also view this information on UL's Online Certifications Directory at www.ul.com. Please review the text and contact the Conformity Assessment Services staff member who handled your project if revisions are required.

Effective June 30, 2004, UL plans to discontinue the distribution of Listing Information Pages in a printed format since this information is readily available via UL's Online Certifications Directory at www.ul.com. To view your company's current Listing Information or for ordering your company's Listing Information in the 3 x 5-inch card format (effective June 30, 2004), please refer to www.ul.com. Prior to June 30, 2004, the 3 x 5-inch Listing Cards can be ordered using the enclosed form. If you have any questions or comments about the discontinuance of the printed Listing Information Pages, please email Susan Druktenis at Susan.M.Druktenis@us.ul.com.

VLFT7 May 18, 2004
Special System Water Control Valves-Deluge Type Certified for Canada

VIKING CORP
210 N INDUSTRIAL PARK RD, HASTINGS MI 49058

EX2006

Water control valves for horizontal or vertical installation, Models E-3, E-4, H-3 and H-4 in the 1-1/2 in. size, rated 1724 kPa; Models E-1, E-2, H-1 and H-2 in the 2, 3, 4 and 6 in. sizes, rated 1724 kPa; Models F-1, F-2 in the 3, 4, 6 and 8 in. size, rated 1724 kPa, and Models J-1 and J-2 in the 4, 6 and 8 in. size, rated 1724 kPa. For operation by wet pilot sprinklers, the height of pilot line above valve is limited as shown in the Manufacturer's Installations Instructions. For accessories used with these valves, see listing under "Accessories For Special Systems".

Models E-1 and E-2 water control 1724 kPa in the 2, 3, 4, 6 in. sizes; Models E-3 and E-4 in the 1-1/2 in. size and Models F1, F-2 in the 3, 4, 6 and 8 in. sizes are rated to when provided with optional Viking EZ Irim, installed in accordance with the manufacturer's installation instructions. For accessories used with these valves, see Listing under "Accessories For Special Systems".

Authorities having jurisdiction to be consulted before installation.

LOOK FOR LISTING MARK ON PRODUCT