




REPLACEMENT PARTS


ALARM CHECK VALVE
MODEL H-3

Manufactured 1991 - 2000




Valve Take Out

"A" Dimension	
3" (DN75)	- 10-1/8" (257mm)
4" (DN100)	- 10-5/8" (270mm)
6" (DN150)	- 13-3/8" (340mm)
8" (DN200)	- 17" (432mm)



Original Clapper Assembly



Replacement Clapper Assembly

NOTE: The clapper assembly is different than on original valve. New clapper assembly has a single bolt style with Ryton bushings for hinge pin.

ITEM NO.	PART NUMBER				DESCRIPTION	MATERIAL	NO. REQ'D			
	3" (80 mm)	4" (100 mm)	6" (150 mm)	8" (200 mm)			3"	4"	6"	8"
1	--	--	--	--	Body	Cast Ductile Iron	1	1	1	1
2	--	--	--	--	Cover Assembly w/Data Plate	HSLA Stainless Steel	1	1	1	1
3	05355A	04900A	04991A	053334A	Hinge Pin	Stainless Steel	1	1	1	1
4	05445A	05445A	05445A	05369A	Retaining Ring	Stainless Steel	2	2	2	2
5	--	--	--	--	Hinge Pin Washer	Stainless Steel	0	2	2	0
6	01517A	01517A			3/8-16 x 3/4 Lg. Hex Head Cap Screw	Zinc Plated Steel	4	6	0	0
			04993A		1/2-13 x 7/8 Lg. Hex Head Cap Screw	Zinc Plated Steel	0	0	6	0
				01922A	5/8-11 x 1-1/4 Lg. Hex Head Cap Screw	Zinc Plated Steel	0	0	0	6
7	05354B	04649B	04992B	05339C	Cover Gasket	SBR Rubber	1	1	1	1
8	06021B	05939B	05940B	05952B	Torsion Spring	Stainless Steel	1	1	1	1
9	*	*			Sealing Washer 3/8" x 1" O.D.	EPDM & Stainless Steel	2	2		
			*	*	Sealing Washer 1/2" x 1-1/8" O.D.	EPDM & Stainless Steel			2	2
	*	*			Screw, Button Head, Socket, 3/8"-24 UNF x 1/2" (12,7 mm) lg.	Stainless Steel, UNS-S30400	2	2		
			*		Screw, Button Head, Socket, 1/4"-20 UNF x 3/4" (19,0 mm) lg.	Stainless Steel, UNS-S30400			2	
10	*	*	*		Screw, Button Head, Socket, 1/4"-20 UNF x 7/8" (22,2 mm) lg.	Stainless Steel, UNS-S30400				2
				*	Clapper	H.R. Steel	1	1	1	0
				*	Clapper	Stainless Steel	0	0	0	1
11	*	*	*		Clapper Rubber	EPDM	1	1	1	1
12	--	--	--	--	Seat	Brass	1	1	1	1
13	*	*	*	*	Rubber Retainer	Stainless Steel	1	1	1	1
14	*	*			Clapper Hex Nut 3/8"-16 UNC	Stainless Steel	1	1		
			*	*	Clapper Hex Nut 1/2"-13 UNC	Stainless Steel			1	1

--Indicates replacement part not available

* Indicates replacement part only available in a Sub-Assembly, as indicated below.

SUB-ASSEMBLY

ITEM NO.	3" (80 mm)	4" (100 mm)	6" (150 mm)	8" (200 mm)	DESCRIPTION
9-11, 13, 14	09916	09398	09421	09917	Clapper Assembly

Note: Clapper assembly is single bolt design with Ryton bushings for hinge pin.