

DETAIL AND SUBMITTAL SHEET

| 3700 Series - Nozzies | | | |
|-------------------------|-------|--|--|
| Project/Location: | Date: | | |
| Architect/Engineer: | Qty: | | |
| Contractor: | | | |
| ® Appropriate Selection | | | |

<u>Rack/Reel Nozzles</u> - Used to shape and direct water stream for fire protection. "On/off" flow and pattern adjustment through body rotation. **Fully adjustable** type (fog/straight stream) for **Class A, B and C (electrical)** fires.

| Model No. | Base | Type/Description |
|-----------|-------|--------------------------------------|
| ® 3704* | 11/2" | Fully adjustable, machined brass, UL |
| ® 3704B* | 11/2" | Fully adjustable, machined brass, UL |
| ® 3712 | 3/4" | Fully adjustable, red polycarbonate |
| ® 3713 | 1" | Fully adjustable, red polycarbonate |
| ® 3714 | 11/2" | Fully adjustable, red polycarbonate |
| ® 3714E | 11/2" | All-fog, red polycarbonate |
| ® 3715 | 2" | Fully adjustable, red polycarbonate |
| ® 3716 | 21/2" | Fully adjustable, red polycarbonate |

^{*}Optional Finishes: ® -B Polished ® -C Rough Chrome Plated ® -D Polished Chrome Plated Threads: ® -NST ® Other _____

Industrial Nozzles - Used to shape and direct water stream for fire protection and washdown applications. "On/off" flow and pattern adjustment through body rotation. Fully adjustable type (fog/straight stream) for Class A and B fires and All-fog type for Class A, B and C (electrical) fires.

| Model No. | Base | Type/Description |
|-----------|-------|--------------------------------------|
| ® 3722* | 3/4" | Fully adjustable, machined brass, UL |
| ® 3723* | 1" | Fully adjustable, machined brass, UL |
| ® 3724* | 11/2" | Fully adjustable, machined brass, UL |
| ® 3724E* | 11/2" | All-fog, machine brass, UL |
| ® 3725* | 2" | Fully adjustable, machined brass, UL |
| ® 3726* | 21/2" | Fully adjustable, machined brass, UL |

^{*}Optional Finishes: ® -B Polished ® -C Rough Chrome Plated ® -D Polished Chrome Plated Threads: ® -NST ® Other

<u>Plain Nozzles</u> - Used to shape and direct water stream for washdown applications. Straight stream only.

| Model No. | Base | Type/Description |
|-----------|-------|---------------------------------|
| ® 3732* | 3/4" | Fixed, 6" long, machined brass |
| ® 3733* | 1" | Fixed, 8" long, machined brass |
| ® 3734* | 11/2" | Fixed, 10" long, machined brass |
| ® 3736* | 21/2" | Fixed, 12" long, machined brass |

^{*}Optional Finishes: ® -B Polished ® -C Rough Chrome Plated ® -D Polished Chrome Plated Threads: ® -NST ® Other _____

<u>Ball Shutoffs with Pistol Grip</u> - Used with nozzles for shut-off function and improve control (NST threads only)

| Model No. | Base | Type/Description |
|-----------|-------|--------------------------------------|
| ® 3744 | 11/2" | 11/2" Outlet, machined brass |
| ® 3746 | 21/2" | 11/2" Outlet, machined brass |
| ® 3744A | 11/2" | 11/2" Outlet, hard-anodized aluminum |
| ® 3746A | 21/2" | 11/2" Outlet, hard-anodized aluminum |















