


455 Malleable Split Ring Hanger



- Recommended for the suspension of stationary non-insulated pipe lines
- Allows for piping runs close to ceiling or walls
- Conforms with Federal Specification WW-H-171 (Type 25), Manufacturers Standardization Society (MSS) SP-58 (Type 12)



Material: Cast Iron

Part Number	Pipe Size	Outer Diameter OD	Rod Size RS	A	B	Static Load F
Finish: Plain						
4550037PL	3/8"	0.675"	3/8"	1 5/16"	3/8"	180 lb
4550050PL	1/2"	0.840"	3/8"	1 1/2"	3/8"	180 lb
4550075PL	3/4"	1.050"	3/8"	1 3/4"	7/16"	180 lb
4550100PL	1"	1.315"	3/8"	2"	7/16"	180 lb
4550125PL	1 1/4"	1.660"	3/8"	2 3/8"	1/2"	180 lb
4550150PL	1 1/2"	1.900"	3/8"	2 5/8"	1/2"	180 lb
4550200PL	2"	2.375"	3/8"	3 1/8"	1/2"	180 lb
4550250PL	2 1/2"	2.875"	1/2"	3 1/4"	5/8"	300 lb
4550300PL	3"	3.500"	1/2"	4 3/8"	5/8"	300 lb
4550400PL	4"	4.500"	1/2"	5 3/8"	11/16"	300 lb
Finish: Electrogalvanized						
4550037EG	3/8"	0.675"	3/8"	1 5/16"	3/8"	180 lb
4550050EG	1/2"	0.840"	3/8"	1 1/2"	3/8"	180 lb
4550075EG	3/4"	1.050"	3/8"	1 3/4"	7/16"	180 lb
4550100EG	1"	1.315"	3/8"	2"	7/16"	180 lb
4550125EG	1 1/4"	1.660"	3/8"	2 3/8"	1/2"	180 lb
4550150EG	1 1/2"	1.900"	3/8"	2 5/8"	1/2"	180 lb
4550200EG	2"	2.375"	3/8"	3 1/8"	1/2"	180 lb



Part Number	Pipe Size	Outer Diameter OD	Rod Size RS	A	B	Static Load F
4550250EG	2 1/2"	2.875"	1/2"	3 1/4"	5/8"	300 lb
4550300EG	3"	3.500"	1/2"	4 3/8"	5/8"	300 lb
4550400EG	4"	4.500"	1/2"	5 3/8"	11/16"	300 lb

Bolt and rivet are carbon steel.

WARNING

Pentair products shall be installed and used only as indicated in Pentair's product instruction sheets and training materials. Instruction sheets are available at erico.pentair.com and from your Pentair customer service representative. Improper installation, misuse, misapplication or other failure to completely follow Pentair's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

© 2016 Pentair. All rights reserved.

Pentair, CADDY, CADWELD, CRITEC, ERICO, ERIFLEX, ERITECH and LENTON are owned by Pentair or its global affiliates.

All other trademarks are the property of their respective owners. Pentair reserves the right to change specifications without prior notice.

