



## VLFT.EX2006 Special System Water Control Valves, Deluge Type

[Page Bottom](#)

### Special System Water Control Valves, Deluge Type

[See General Information for Special System Water Control Valves, Deluge Type](#)

#### VIKING CORP

EX2006

210 N INDUSTRIAL PARK RD  
HASTINGS, MI 49058 USA

Models E-3, E-4, H-3, H-4 in the 1-1/2 in. size rated 250 psig; Models E-1, E-2, H-1, H-2 in the 2, 3, 4 and 6 in. sizes rated 250 psig; Models F-1, F-2 in the 1-1/2, 2, 3, 4, 6 and 8 in. size rated 250 psig; Models J-1, J-2 in the 1-1/2, 2, 2-1/2, 3, 4, 6 and 8 in. size rated 250 psig. For operation by wet pilot sprinklers, the height of pilot line above valve is limited as shown in the Manufacturer's Installations Instructions. For accessories used with these valves, see listing under "Accessories For Special Systems." For horizontal or vertical installation.

Models E-1 and E-2 water control valves in the 2, 3, 4 and 6 in. sizes, and Models E-3, E-4 in the 1-1/2 in. size and Models F-1, F-2 in the 3, 4, 6 and 8 in sizes are rated to 250 psig when provided with optional Viking EZ Trim, installed in accordance with the manufacturer's installation instructions. For accessories used with these valves, see Listing under "Accessories For Special Systems.". For horizontal or vertical installation.

Model E-3 in the 1-1/2 in. size, Model E-1 in the 2, 3, 4 and 6 in. sizes; and the Model F-1 in the 3, 4, 6 and 8 in. sizes are rated 250 psig when provided with the optional Viking HP Dry System, installed in accordance with the manufacturer's installation instructions. For accessories used with these valves, see Listing under "Accessories For Special Systems." For horizontal or vertical installation.

Model F-1 and F-2 in the 1-1/2, 2, 2-1/2, 3, 4, 6, and 8 in. sizes are rated 250 psig when provided with the SUREFIRE, single interlocked and pre-primed single interlock pre-action systems, installed in accordance with the manufacturer's installation instructions. For accessories used with these valves, see Listing under "Accessories For Special Systems." For horizontal or vertical installation.

Models H-1, H-2 water control valves in the 2, 4 and 6 in. sizes are rated 175 psig when provided with optional Viking pressure regulating trim assembly, installed in accordance with the manufacturer's installation instructions. For horizontal or vertical installation.

Models H-1, H-2 water control valves in the 2, 4 and 6 in. sizes are rated 250 psig when provided with optional Viking pilot pressure regulating trim assembly, installed in accordance with the manufacturer's installation instructions. For horizontal or vertical installation.

Models J-1, J-2 water control valves in the 1-1/2, 2, 4, 6, and 8 in. sizes are rated 250 psig when provided with optional Viking pilot pressure regulating trim, installed in accordance with the manufacturer's installation instructions. For horizontal or vertical installation.

Authorities having jurisdiction to be consulted before installation.

[Last Updated](#) on 2008-06-23

[Questions?](#)

[Notice of Disclaimer](#)

[Page Top](#)

[Copyright © 2008 Underwriters Laboratories Inc.®](#)

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Listed and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Designs and/or Listings (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from Underwriters Laboratories Inc." must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "Copyright © 2008 Underwriters Laboratories Inc.®"

An independent organization working for a safer world with integrity, precision and knowledge.

