



VLFT7.EX2006

Special System Water Control Valves, Deluge Type Certified for Canada

[Page Bottom](#)

Special System Water Control Valves, Deluge Type Certified for Canada

[See General Information for Special System Water Control Valves, Deluge Type Certified for Canada](#)

VIKING CORP

EX2006

210 N INDUSTRIAL PARK RD
HASTINGS, MI 49058 USA

Models E-3, E-4, H-3 and H-4 in the 1-1/2 in. size, rated 1724 kPa ; Models E-1, E-2, H-1 and H-2 in the 2, 3, 4 and 6 in. sizes, rated 1724 kPa; Models F-1, F-2 in the 1-1/2, 2, 3, 4, 6 and 8 in. size, rated 1724 kPa; and Models J-1 and J-2 in the 1-1/2, 2, 2-1/2, 3, 4, 6 and 8 in. size, rated 1724 kPa. For operation by wet pilot sprinklers, the height of pilot line above valve is limited as shown in the manufacturer's installations instructions. For accessories used with these valves, see listing under "Accessories For Special Systems". For horizontal or vertical installation.

Models E-1 and E-2 water control 1724 kPa in the 2, 3, 4, 6 in. sizes; Models E-3 and E-4 in the 1-1/2 in. size and Models F1, F-2 in the 3, 4, 6 and 8 in. sizes are rated to when provided with optional Viking EZ Trim, installed in accordance with the manufacturer's installation instructions. For accessories used with these valves, see Listing under "Accessories For Special Systems." For horizontal or vertical installation.

Model E-3 in the 1-1/2 in. size, Model E-1 in the 2, 3, 4 and 6 in. sizes; and the Model F-1 in the 3, 4, 6 and 8 in. sizes are rated 1724 kPa when provided with the optional Viking HP Dry System, installed in accordance with the manufacturer's installation instructions. For accessories used with these valves, see Listing under "Accessories For Special Systems." For horizontal or vertical installation.

Model F-1 and F-2 in the 1-1/2, 2, 2-1/2, 3, 4, 6, and 8 in. sizes are rated 1724 kPa when provided with the SUREFIRE, single interlocked and pre-primed single interlock pre-action systems, installed in accordance with the manufacturer's installation instructions. For accessories used with these valves, see Listing under "Accessories For Special Systems." For horizontal or vertical installation.

Models H-1, H-2 water control valves in the 2, 4 and 6 in. sizes are rated 1206 kPa when provided with optional Viking pressure regulating trim assembly, installed in accordance with the manufacturer's installation instructions. For horizontal or vertical installation.

Models H-1, H-2 water control valves in the 2, 4 and 6 in. sizes are rated 1724 kPa when provided with optional Viking pilot pressure regulating trim assembly, installed in accordance with the manufacturer's installation instructions. For horizontal or vertical installation.

Models J-1, J-2 water control valves in the 1-1/2, 2, 4, 6, and 8 in. sizes are rated 1724 kPa when provided with optional Viking pilot pressure regulating trim, installed in accordance with the manufacturer's installation instructions. For horizontal or vertical installation.

Authorities having jurisdiction to be consulted before installation.

[Last Updated](#) on 2008-06-23

[Questions?](#)

[Notice of Disclaimer](#)

[Page Top](#)

[Copyright © 2008 Underwriters Laboratories Inc.®](#)

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Listed and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Designs and/or Listings (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from Underwriters Laboratories Inc." must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "Copyright © 2008 Underwriters Laboratories Inc.®"

An independent organization working for a safer world with integrity, precision and knowledge.

