



TECHNICAL DATA

AUTOMATIC DRIP CHECK

1. PRODUCT NAME

Automatic Drip Check, 3/4"

Model D-1 (Deluge & Flow Control Valves) Part Number 10730

Model D-2 (Dry Valve Replacement with Model B-1 Accelerator) Part Number 10731

Model D-3 (Dry Valve) Part Number 10732

Model D-4 (Deluge, Electroless Nickel Plated) Part Number 10733

Manufactured since 1980

2. MANUFACTURER

The Viking Corporation
210 N Industrial Park Drive
Hastings MI 49058 U.S.A.

Telephone: (269) 945-9501

(877) 384-5464

Fax: (269) 945-4495

Email: techsvcs@vikingcorp.com

3. PRODUCT DESCRIPTION

The Automatic Drip Checks are designed to drain water automatically, which may leak past a normally closed dry valve or deluge valve. They close, however, against an increase in flow pressure and will open automatically at a predetermined decrease in pressure. The devices are used with dry and deluge valves to drain any water that may seep by the valve clapper.

Model D-1 and D-4 Drip Check is used with a valve that does not have an automatic alarm line drain. It has a notched seat so that a slight amount of water will discharge through the Drip Check when the valve trips. When the control valve is closed, the alarm line will automatically drain through the Drip Check. This unit is normally used with the Viking Deluge Valves.

Model D-2 Drip Check is normally used with Viking Model C dry valves with iron trim. The Drip Check has a 3/8" pipe plug installed for use with the Model B-1 Accelerator. When the valve trips, no water will discharge through the Drip Check. When the control valve is closed and the system is drained, the Drip Check will open and drain off any excess water in the valve.

Model D-3 Drip Check is used with a Model D or E dry valve that has an automatic drain for the alarm line. When the valve trips, no water will discharge through the Drip Check. When the control valve is closed and the system is drained, the Drip Check will open and drain off any excess water in the valve.

4. TECHNICAL DATA

Designed to Underwriter's Laboratory and Factory Mutual requirements.

Working water pressure: 250 PSI (17.2 bar)

Materials:

Body: Brass casting UNS-C84400

Ball: Stainless Steel

Spring: Phosphor Bronze

Retaining Ring: Stainless Steel

Model D-4: Electroless Nickel Plated

5. AVAILABILITY

The Viking Automatic Drip Check is available through a network of domestic and international distributors. See the Viking Corp. Web site for closest distributor or contact The Viking Corporation.

6. GUARANTEES

For details of warranty, refer to Viking's current list price schedule or contact Viking directly.


7. MAINTENANCE

During each inspection of valve, push plunger to make sure no water is trapped.

8. INSTALLATION

A. Install in outlet provided in valve trim.

B. Unit should be level.



Viking Technical Data may be found on
The Viking Corporation's Web site at
<http://www.vikingcorp.com>.
The Web site may include a more recent
edition of this Technical Data Page.



TECHNICAL DATA

AUTOMATIC BALL DRIP VALVE MODEL B-1

1. PRODUCT NAME

Automatic Ball Drip Valve, 1/2" Model B-1
Manufactured since 1978
Part Number 04292B

2. MANUFACTURER

The Viking Corporation
210 N Industrial Park Drive
Hastings MI 49058 U.S.A.
Telephone: (269) 945-9501
(877) 384-5464
Fax: (269) 945-4495
Email: techsvcs@vikingcorp.com

3. PRODUCT DESCRIPTION

The Automatic Ball Drip Valve is designed to drain water automatically which may leak past a normally closed check valve or gate valve. It closes, however, against an increase in flow pressure and will open automatically at a predetermined decrease in pressure. Automatic ball drip valves are used, for example, on the inlet side of fire department check valve or pumper connections to prevent water from collecting and freezing.

4. TECHNICAL DATA

Designed to Underwriter's Laboratory and Factory Mutual requirements.

Working water pressure: 250 PSI (17.2 bar)

Materials:

Bar: Brass UNS-C36000

Spring: Stainless Steel UNS-S30200

Retaining Ring: Stainless Steel UNS-S15700

Closing pressure: 13.5 PSI (93 kPa) with increasing pressure

Opening pressure: 12.5 PSI (86 kPa) with decreasing pressure

6. AVAILABILITY

The Viking Automatic Ball Drip Valve is available through a network of domestic and international distributors. See the Viking Corp. Web site for closest distributor or contact The Viking Corporation.

7. GUARANTEES

For details of warranty, refer to Viking's current list price schedule or contact Viking directly.


7. MAINTENANCE

The Automatic Ball Drip Valve should be inspected annually.

8. INSTALLATION

Install the automatic ball drip in a horizontal position. If desirable, pipe discharge to an open drain. 1/4" NPT is provided in the drain outlet.

NOTE: THIS VALVE IS NOT DESIGNED TO SHUT COMPLETELY AND WILL CONTINUE TO DRIP WHEN PRESSURIZED.



Viking Technical Data may be found on
The Viking Corporation's Web site at
<http://www.vikingcorp.com>.
The Web site may include a more recent
edition of this Technical Data Page.