



TECHNICAL DATA

THERMOSTATIC RELEASE ACCESSORIES

The Viking Corporation, 210 N Industrial Park Drive, Hastings MI 49058

Telephone: 269-945-9501 Technical Services 877-384-5464 Fax: 269-945-4495 Email: techsvcs@vikingcorp.com

<p>Customer receives as shown above. Hanger must be formed as shown</p>	<p>Formed finished product</p>	<p>* Dimension provides clearance for 2" (40 mm) through 6" (150 mm) flanges.</p>
---	--------------------------------	---

Release Line Hangers

Release line hangers are for supporting 1/2" (15 mm) release line piping from system piping. The hanger is made of 1/16" (1,59 mm) by 1" (25,4 mm) galvanized hot rolled steel or stainless steel. It is fastened by two 1/4"-20 x 3/4" (6,35 mm -20 x 19,05 mm) slotted screws with nuts. Order for system pipe sizes 1", 1-1/4", 1-1/2", 2", 2-1/2", 3", 3-1/2", 4", 5", 6", and 8" (25 mm, 32 mm, 40 mm, 50 mm, 65 mm, 80 mm, 90 mm, 100 mm, 125 mm, 150 mm, and 200 mm).

Operation Indicator
Operation Indicator, Viking Part Number 02944A consists of a brass insert and orange plastic cap. The release operation indicator is installed in the 1/2" (15 mm) drain outlet of the release. When the release operates, the plastic cap of the operation indicator will blow open at 2 psi (14 kPa), thus indicating which release has operated. The brass insert is emralon coated to prevent the plastic cap from sticking.

Release Setting Tool Kit
Release Setting Tool Kit, Viking Part Number 01714A, consists of one 3/16" (4,76 mm) Allen wrench, with a special Schrader core removing end, one 0.025" (0,635 mm) feeler gauge, one 0.018" (0,457 mm) feeler gauge, and five replacement Schrader valve cores. C-1 Thermostatic Release uses 0.025" feeler gauge, and C-2 uses 0.018" feeler gauge.

**THIS PAGE
INTENTIONALLY
LEFT BLANK**