

	<h1 style="margin: 0;">TECHNICAL DATA</h1>	<h2 style="margin: 0;">CONTINUOUS FLOW HOSE REELS</h2>
---	--	--

The Viking Corporation, 210 N Industrial Park Drive, Hastings MI 49058

Telephone: 269-945-9501 Technical Services 877-384-5464 Fax: 269-818-1680 Email: techsvcs@vikingcorp.com

1. DESCRIPTION

Features

- Galvanized carbon steel
- Manual rewind
- Equipped with booster hose and hand line nozzle
- Instant, single-person operation
- Only unreel the amount of hose required



Viking Technical Data may be found on The Viking Corporation's Web site at <http://www.vikinggroupinc.com>. The Web site may include a more recent edition of this Technical Data Page.

2. TECHNICAL DATA

Specifications:

Pressure Rating: 250 psi

Material Standards:

Reel: Galvanized Carbon Steel

Ordering Information:

See Table 1

3. INSPECTIONS, TESTS AND MAINTENANCE

NOTICE: The owner is responsible for maintaining the fire protection system and devices in proper operating condition. For minimum maintenance and inspection requirements, refer to recognized standards such as those produced by NFPA, LPC, and VdS which describe care and maintenance of sprinkler systems. In addition, the "Authority Having Jurisdiction" may have additional maintenance, testing and inspection requirements which must be followed.

WARNING: Any system maintenance or testing which involves placing a control valve or detection system out of service may eliminate the Fire Protection of that system. Prior to proceeding, notify all Authorities Having Jurisdiction. Consideration should be given to employment of a Fire Patrol in the affected area.

4. AVAILABILITY

Viking Foam Products are available through a network of domestic and international distributors. See the Viking web site for closest distributor or contact The Viking Corporation.

5. GUARANTEE

For details of warranty, refer to Viking's current list price schedule or contact Viking directly.

Table 1: Part Numbers				
Viking Part #	Chemguard Model #	Hose Length	Hose Diameter	Nozzle
F15353	CHRS50	50'	1-1/2"	SB95P
F15354	CHRS75	75'		
F15355	CHRS100	100'		
F15356	CHRS125	125'		
F15357	CHRS150	150'		
F15358	CHRS175	175'		
F15359	CHRS200	200'		

THIS PAGE INTENTIONALLY
LEFT BLANK