




## Pipe Clamp with Rubber Insulation

240

### Technical Features

- **Sizes (Pipe Accomodation Diameter):** 12mm through 63mm
- **Hanger Thread Size :** M8/M10 Combination Boss.
- **Closure Cylinder Head Screw Sizes :** M6x20 to M8x30
- **Temperature Rating :** from -50°C up to +110°C
- **Fire Rating :** B2 acc. to DIN 4102
- **Materials :**  
Profile: Carbon steel  
Rubber: EPDM
- **Finish :** Electro Zinc Plated
- **Specification :** To be used with Threaded Rod (not supplied). EPDM rubber insulated for sound reduction, compliant with DIN 4109



Pipe Support

### Pipe Clamp with Rubber Insulation - 240

Physical Data

Reference	Nominal Pipe Size		Thread	B x S (mm)	Sc x L	d (mm)	Box Qty.	Weight (x1) (kg / lbs)
	metric (DN)	inch						
400078	DN8	1/4"	M8/M10	20x1,5	M6x20	12-14	150	0,06 / 0.13
400079	DN10	3/8"	M8/M10	20x1,5	M6x20	15-19	150	0,06 / 0.13
400080	DN15	1/2"	M8/M10	20x1,5	M6x20	21-23	100	0,07 / 0.15
400081	DN20	3/4"	M8/M10	20x1,5	M6x20	26-28	100	0,08 / 0.18
400082	DN25	1"	M8/M10	20x1,5	M6x20	32-35	75	0,09 / 0.20
400083	DN32	1 1/4"	M8/M10	20x1,5	M6x20	40-43	50	0,10 / 0.22
400084	44-49mm	-	M8/M10	20x2,0	M6x20	44-49	50	0,12 / 0.26
400085	DN40	1 1/2"	M8/M10	20x2,0	M6x25	50-56	50	0,13 / 0.29
400086	DN50	2"	M8/M10	20x2,0	M6x25	57-61	50	0,14 / 0.31
400087	63-67mm	-	M8/M10	20x2,0	M6x25	63-67	50	0,15 / 0.33
400088	70-73mm	-	M8/M10	20x2,0	M6x25	70-73	50	0,16 / 0.35
400089	DN65	2 1/2"	M8/M10	20x2,0	M6x25	74-80	50	0,18 / 0.40
400090	DN80	3"	M8/M10	20x2,0	M6x25	83-91	50	0,21 / 0.46
400091	101-106mm	-	M8/M10	23x2,5	M6x25	101-106	25	0,31 / 0.68
400092	DN100	4"	M8/M10	23x2,5	M6x25	108-114	25	0,34 / 0.75
400093	115-116mm	-	M8/M10	23x2,5	M6x25	115-116	25	0,36 / 0.79
400094	125mm	-	M8/M10	23x2,5	M6x25	125	25	0,37 / 0.82
400095	131-135mm	-	M8/M10	23x2,5	M6x25	131-135	25	0,39 / 0.86
400096	136-139mm	-	M8/M10	23x2,5	M6x25	136-139	25	0,39 / 0.86
400097	140-144mm	-	M8/M10	23x2,5	M6x25	140-144	25	0,36 / 0.79
400098	DN125	5"	M8/M10	23x2,5	M8x30	159-163	20	0,43 / 0.95
400099	DN150	6"	M8/M10	23x2,5	M8x30	165-169	20	0,44 / 0.97
400100	193-200mm	-	M8/M10	25x3,0	M8x30	193-200	10	0,64 / 1.41
400101	210-212mm	-	M8/M10	25x3,0	M8x30	210-212	10	0,65 / 1.43