




Nuts with and w/o Spring (for use with Strut Chan. and Cantilever Strut)

Pipe Support

Technical Features

- **Sizes:**
T-Head Nut: M8, M10 and M12
To fit Strut Channel: 21x41, 41x41, 62x41, 83x41
and Cantilever Strut: 21x41, 41x41.
- **Material :** Carbon steel
- **Finish :**
T-Head Nut: Electro Zinc Plated and Hot Dipped Galvanized.
- **Specifications :** Serrated nut to fit with Strut Channels
Available with and without spring
To use with Screws and Washers
(see separate datasheets)



Nuts (for use with Curved Interior Rails) - UM

Physical Data

Thread Size (M)	Width (H) (mm)	Torque Max. (Nm)	Box Qty.	Weight (x1) (kg / lbs)	Reference
M8	6	28	100	0,03 / 0.07	315015
M10	8	55	100	0,04 / 0.09	315025
M12	8	95	100	0,04 / 0.09	315035
M8	6	28	100	0,03 / 0.07	315095*
M10	8	55	100	0,04 / 0.09	315105*
M12	8	95	100	0,04 / 0.09	315115*

* Nut with spring