




Hanger / Restrainer "Stand-Off" for CPVC Pipe

28

Technical Features

- Available for pipe sizes (Nominal) : DN20/3/4", DN25/1", DN32/1 1/4", DN40/1 1/2", DN50/2".
- Material : Carbon steel
- Finish : Pre-galvanized
- Features : Flared edge design protects CPVC pipe from rough surfaces. Twist and lock design holds pipe firmly in place and allows retrofit installation. "Stand-Off" design eliminates need for any extension. Can be installed on vertical or horizontal piping. Attaches easily to wood using two hex-head self-threading screws (supplied).



Hanger / Restrainer "Stanf-Off" for CPVC Pipe - 28

Physical Data

Nominal Pipe Size		Dimensions (mm / inch)		Box Quantity	Box Weight (kg / lbs)	Fastener Hex Head Size (in)	Reference
Metric	inch	A	B				
DN20	3/4"	62,2 / 2.45	33,5 / 1.32	100	3,4 / 9.0	5/16"	28-75
DN25	1"	59,4 / 2.34	36,8 / 1.45	100	3,4 / 9.0	5/16"	28-0100
DN32	1 1/4"	78,0 / 3.07	41,9 / 1.65	100	4,1 / 11.0	5/16"	28-0125
DN40	1 1/2"	84,3 / 3.32	44,5 / 1.75	100	4,5 / 12.0	5/16"	28-0150
DN50	2"	95,3 / 3.75	54,6 / 2.15	100	5,6 / 15.0	5/16"	28-0200

Notes

This product is intended to perform as hanger/restrainer to support CPVC piping used in sprinkler systems. Use two hex-head self-threading screws (supplied) and two Speed Nuts (See Figure 1) when used as a hanger and restrainer to prevent upward movement of sprinkler head when activated. The restrainer shall be located not more that 30,5cm (12") from the sprinkler being restrained. Use two hex-head self-threading screws (supplied) and one Speed

Nut (See Figure 2) on the upper installed screw when used as a hanger only. If other fasteners are used the must equal or exceed the diameter of a #10 x 1" self-threading screw. The use of a cordless drill fitted with a hex socket is recommended for installation. No impact tools (such as hammers) or impact fasteners (drive screws or nails) are permitted, as they could result in damage.

