


4-Way Inlet Breeching Valve

WR-115

Technical Features

- **Pressure Data** : Hydrostatically tested to 24 bar
Non-return valve tested to 22.5 bar
- **Inlet** : 65 mm male instantaneous coupling to BS 36 C/W, non-return valve, blanking caps and chain, brass alloy parts, with bronze springs and stainless steel lock-nut & washer.
- **Flange Size** : PN16 (BS EN 1092-2 : 1997)
- **Breeching Inlet Body** : HT200 Cast Iron
- **Total Weight** : 39.0 kg
- **Features** :
 - Compact design with excellent flow characteristics
 - High quality casting finishes
 - Adjustable Relief Valve
 - 25 mm drain valve with blanking cap and chain
 - Maintenance free
 - Vertical or horizontal mounting
- **Valve Standards** :
Manufactured in accordance with BS 5041 : Part 3 : 1975



WR-115

Parts List

No.	Part
1	Inlet Plastic Blank Cap c/w Bi S-Hook & Chain
2	Body
3	Inlet Connector Assembly
4	Drain Valve Blank Cap c/w Bi S-Hook & Chain
5	1" Drain Valve

