




Pump Initiation Board

VPB



2-Way Main Pump & Jockey

1-Way Main Pump

1-Way Jockey Only

Pump Initiation Board - VPB

Specifications

The Viking pump initiation boards have been designed with the user in mind and include the following features:

- Fully compliant with the EN12845/LPC Rules double switch arrangements
- Unions included allow for servicing of the check valves without the need to de-mount the board
- Globe valves allow slow and controlled release of pressure during testing
- Common drain with tundishes
- Lockable ball valves
- Market-leading Bailey & Mackey pressure switches (LPCB approved) installed on unions for easy wiring/servicing
- Modular approach allowing flexibility
- Mounted on Aluminium backboards with pre-drilled 10mm mounting holes
- 16 bar Glycerine filled gauges supplied as standard. Can be supplied without for users' own gauges
- Assembled by the same qualified team trimming alarm valves

Pump Initiation Board - VPB

Technical Data

Type	Dimensions (mm/inch)		Reference	Weight (kg)
	Height	Width		
1-Way Main Pump	600 / 23.6	450 / 17.7	VPB1	12.31
2-Way Main Pump & Jockey	600 / 23.6	750 / 29.5	VPB2	19.00
1-Way Jockey Only	600 / 23.6	300 / 11.8	VPB3	7.36