January 1, 2011 Sprinkler 64a



# **TECHNICAL DATA**

# MIRAGE® QUICK RESPONSE CONCEALED PENDENT SPRINKLER VK465 (K4.2)

The Viking Corporation, 210 N Industrial Park Drive, Hastings MI 49058

Telephone: 269-945-9501 Technical Services: 877-384-5464 Fax: 269-818-1680 Email: techsvcs@vikingcorp.com

#### 1. DESCRIPTION

Viking Mirage® Quick Response Concealed Pendent Sprinkler VK465 is a thermosensitive glass-bulb spray sprinkler designed for installation on concealed pipe systems where the appearance of a smooth ceiling is desired.

The sprinkler is pre-assembled with a threaded adapter for installation with a low-profile cover assembly that provides up to  $\frac{1}{2}$ " (12.7 mm) of vertical adjustment. The two-piece design allows installation and testing of the sprinkler prior to installation of the cover plate. The "push-on", "thread-off" design of the concealed cover plate assembly allows easy installation of the cover plate after the system has been tested and the ceiling finish has been applied. The cover assembly can be removed and reinstalled, allowing temporary removal of ceiling panels without taking the sprinkler system out of service or removing the sprinkler.



For Light Hazard Occupancies Only

Viking Technical Data may be found on

The Viking Corporation's Web site at

http://www.vikinggroupinc.com.

The Web site may include a more recent

edition of this Technical Data Page.

#### 2. LISTINGS AND APPROVALS

cULus Listed: Category VNIV

Refer to the Approval Chart on page 64c and Design Criteria on page 64d for cULus Listing requirements that must be followed.

#### 3. TECHNICAL DATA

#### Specifications:

Minimum Operating Pressure: 7 psi (0.5 bar).

Maximum Working Pressure: 175 psi (12 bar). Factory tested hydrostatically

to 500 psi (34.5 bar).

Testing: U.S.A. Patent No. 4,831,870 Thread size: 1/2" (15 mm) NPT Nominal K-Factor: 4.2 U.S. (57 metric\*)

\*Metric K-factor measurement is shown in bar. When pressure is measured in kPa, divide the metric K-factor shown by 10.0.

Glass-bulb fluid temperature rated to -65°F (-55°C)

Patents Pending

### **Material Standards:**

Sprinkler Body: Brass UNS-C84400 Deflector: Copper UNS-C19500

Deflector Pins: Stainless Steel UNS-S30300

Bushing: Brass UNS-C36000

Bulb: Glass, nominal 3 mm diameter

Pip Cap and Insert Assembly: Copper UNS-C11000 and Stainless Steel UNS-S30400

Button: Brass UNS-C36000 Screws: 18-8 Stainless Steel

Belleville Spring Sealing Assembly: Nickel Alloy, coated on both sides with Teflon Tape

Yoke: Phosphor Bronze UNS-C51000

Cover Adapter: Cold Rolled Steel UNS-G10080, Finish: Clear Chromate over Zinc Plating

Cover Assembly Materials: Cover: Copper UNS-C11000

Base: Brass UNS-C26000 or UNS-C26800

Springs: Nickel Alloy Solder: Eutectic

**Ordering Information:** (Also refer to the current Viking price list.)

Viking Mirage® Quick Response Concealed Pendent Sprinkler VK465 and Cover Plate Assembly must be ordered separately:

Sprinkler: Base Part No. 14262A

Specify sprinkler temperature rating by adding the appropriate suffix for the temperature rating to the base part number:

Temperature Suffix (°F/°C): 155°/68° = B, 175°/79° = D, 200°/93° = E

For example, sprinkler VK465 with a 155°F/68°C temperature rating = 14262AB.

Replaces page 64a-e, dated April 16, 2010. (Revised finish suffixes for white, black, and ivory painted cover finishes.)

Sprinkler 64b January 1, 2011



# **TECHNICAL DATA**

# MIRAGE® QUICK RESPONSE CONCEALED PENDENT SPRINKLER VK465 (K4.2)

The Viking Corporation, 210 N Industrial Park Drive, Hastings MI 49058

Telephone: 269-945-9501 Technical Services: 877-384-5464 Fax: 269-818-1680 Email: techsvcs@vikingcorp.com

**Cover Plate Assembly:** Base Part No. 13504 (2-3/4" diameter), Base Part No. 13642 (3-5/16" diameter), or Base Part No. 15394 (square cover plate, 3-5/16" diameter)

Specify finish and temperature rating of the cover plate assembly by adding the appropriate suffixes for the finish and the cover temperature rating to the base part number:

Finish Suffix: Polished Chrome = F, Brushed Chrome = F-/B, Bright Brass = B, Antique Brass = B-/A, Brushed Brass = B-/B, Brushed Copper = E-/B, Painted White = M-/W, Painted Ivory = M-/I, Painted Black = M-/B

Temperature Suffix (°F/°C):  $135^{\circ}/57^{\circ} = A$ ,  $165^{\circ}/74^{\circ} = C$ 

For example, cover 13504 with a Polished Chrome finish and a 165°F/74°C temperature rating = 13504FC.

Note: Square cover plate 15394 cULus Listing is for the 135°F (57°C) temperature rated cover plate only. Refer to the Approval Chart.

Available Finishes And Temperature Ratings: Refer to Table 1

Accessories: (Also refer to the "Sprinkler Accessories" section of the Viking data book.)

Sprinkler Wrenches\*\*:

- A. Heavy Duty Wrench Part No. 14047W/B (available since 2006), or
- B. Head Cabinet Wrench Part No. 14031\*\*\* (available since 2006)
- C. Optional Concealed Cover Plate Installer Tool Part No. 14412 for cover 13504, or Part No. 14867 for the large diameter cover (available since 2007)

\*\*Requires a ½" ratchet (not available from Viking). \*\*\*Optional for removal of the protective cap. Ideal for sprinkler cabinets.

**Sprinkler Cabinet:** Part No. 01731A (available since 1971)

#### 4. INSTALLATION

Refer to appropriate NFPA Installation Standards.

#### 5. OPERATION

During fire conditions, when the temperature around the sprinkler approaches its operating temperature, the cover plate detaches. Continued heating of the exposed sprinkler causes the heat-sensitive liquid in the glass bulb to expand and the bulb to shatter, releasing the yoke, pip-cap and sealing spring assembly. Water flowing through the sprinkler orifice strikes the sprinkler deflector, forming a uniform spray pattern to extinguish or control the fire.

#### 6. INSPECTIONS, TESTS AND MAINTENANCE

Refer to NFPA 25 for Inspection, Testing and Maintenance requirements.

#### 7. AVAILABILITY

Viking Mirage® Concealed Pendent Sprinkler VK465 is available through a network of domestic and international distributors. See The Viking Corporation web site for the closest distributor or contact The Viking Corporation.

#### 8. GUARANTEE

For details of warranty, refer to Viking's current list price schedule or contact Viking directly.

TABLE 1: AVAILABLE SPRINKLER TEMPERATURE RATINGS AND FINISHES				
Sprinkler Temperature Classification	Sprinkler Nominal Temperature Rating <sup>1</sup>	Maximum Ambient Ceiling Temperature <sup>2</sup>	Temperature Rating of Cover Assembly (Required)	Bulb Color
Ordinary	155°F (68°C)	100°F (38°C)	135°F (57°C)	Red
Intermediate	175°F (79°C)	150°F (65°C)	165°F (74°C)	Yellow
Intermediate	200°F (93°C)	150°F (65°C)	165°F (74°C)	Green

Cover Plate Finishes: Polished Chrome, Brushed Chrome, Bright Brass, Antique Brass, Brushed Brass, Brushed Copper, Painted White, Painted Ivory, or Painted Black

#### **Footnotes**

<sup>&</sup>lt;sup>1</sup> The sprinkler temperature rating is stamped on the sprinkler deflector.

<sup>&</sup>lt;sup>2</sup> Based on NFPA-13. Other limits may apply, depending on fire loading, sprinkler location, and other requirements of the Authority Having Jurisdiction. Refer to specific installation standards.

January 1, 2011 Sprinker 64c



# **TECHNICAL DATA**

# MIRAGE® QUICK RESPONSE CONCEALED PENDENT SPRINKLER VK465 (K4.2)

The Viking Corporation, 210 N Industrial Park Drive, Hastings MI 49058


Telephone: 269-945-9501 Technical Services: 877-384-5464 Fax: 269-818-1680 Email: techsvcs@vikingcorp.com

#### **Approval Chart** Sprinkler Temperature Rating Mirage® Quick Response Concealed Pendent Sprinkler VK465 Cover Plate Temperature Rating AW1← Cover Plate Finish KEY For Light Hazard Occupancies Only Maximum 175 PSI (12 bar) WWP **NPT Thread** Nominal **Overall Length** Listings and Approvals<sup>3</sup> Sprinkler Size K-Factor (Sprinkler Body) (Refer also to Design Criteria on page 64d.) **Base Part** SIN Number<sup>1</sup> Inch mm U.S. metric<sup>2</sup> Inches cULus⁴ FM NYC VdS **LPCB** mm $\epsilon$ 0 14262A VK465 1/2" 15 4.2 2-3/16" 56 AW1. BX1 See Footnote 5. --Finishes of the Cover Plate Assembly<sup>7</sup> Cover Plate Assembly Temp. Ratings<sup>6</sup> **Sprinkler Temperature Ratings** 1 - Polished Chrome, Brushed Chrome, Bright W - 135°F (57°C) cover 135041, 136421 (large diameter), or A - 155°F (68°C) Brass, Antique Brass, Brushed Brass, 153941 (square cover plate) B - 175°F (79°C) and 200°F (93°C) Brushed Copper, Painted White, Painted X - 165°F (74°C) cover 135041 or 136421 (large diameter) Ivory, or Painted Black

#### Footnotes

- <sup>1</sup> Part number shown is the base part number. For complete part number, refer to current Viking price list schedule.
- <sup>2</sup> Metric K-factor measurement is shown in Bar. When pressure is measured in kPa, divide the metric K-factor shown by 10.0.
- <sup>3</sup> This chart shows the listings and approvals available at the time of printing. Other approvals may be in process. Check with the manufacturer for any additional approvals.
- <sup>4</sup> Listed by Underwriter's Laboratories for use in the U.S. and Canada.
- <sup>5</sup> Meets New York City requirements, effective July 1, 2008.
- <sup>6</sup> The 135°F cover has an orange label. The 165°F cover has a white label.
- <sup>7</sup> Standard painted finishes consist of Polyester Baked Enamel. Other paint colors are available on request with the same listings as the standard paint colors. Listings and approvals apply for any paint manufacturer. Contact Viking for additional information.

NOTE: Custom colors are indicated on a label inside the cover assembly. Refer to Figure 2.



Sprinkler 64d January 1, 2011



# **TECHNICAL DATA**

MIRAGE® QUICK RESPONSE CONCEALED PENDENT SPRINKLER VK465 (K4.2)

The Viking Corporation, 210 N Industrial Park Drive, Hastings MI 49058
Telephone: 269-945-9501 Technical Services: 877-384-5464 Fax: 269-818-1680 Email: techsvcs@vikingcorp.com

#### **DESIGN CRITERIA**

(Also refer to the Approval Chart on page 64.)

#### **cULus Listing Requirements:**

Mirage® Quick Response Concealed Pendent Sprinkler VK465 is cULus Listed as a quick response sprinkler for installation in accordance with the latest edition of NFPA 13 for standard coverage pendent spray sprinklers as indicated below:

- Limited to Light Hazard Occupancies where allowed by the installation standards being applied, with hydraulically calculated wet systems, or hydraulically calculated dry pipe systems where piping is corrosion resistant or internally galvanized.
- · Maximum spacing allowed is 15 ft. (4.6 m).
- · Minimum spacing allowed is 6 ft. (1.8 m) unless baffles are installed in accordance with NFPA 13.
- Minimum distance from walls is 4 in. (102 mm).
- Maximum distance from walls shall be no more than one-half of the allowable distance between sprinklers. The distance shall be measured perpendicular to the wall.
- · The sprinkler obstruction rules contained in NFPA 13 for standard coverage pendent spray sprinklers must be followed.


NOTE: Concealed sprinklers must be installed in neutral or negative pressure plenums only.

IMPORTANT: Always refer to Bulletin Form No. F\_091699 - Care and Handling of Sprinklers. Also refer to page QR1-3 for general care, installation, and maintenance information. Viking sprinklers are to be installed in accordance with the latest edition of Viking technical data, the appropriate standards of NFPA, FM Global, LPCB, Assemblee Pleniere, VdS or other similar organizations, and also with the provisions of governmental codes, ordinances, and standards, whenever applicable.



Identification of Custom Paint Color:
All custom color painted cover plates will
have an identifying label affixed to the
inside of the cover that indicates custom
color and will have a representative sample
(a paint dot) of the paint on the label.

Figure 2: Identification of Custom Paint Color for Concealed Covers




January 1, 2011 Sprinker 64e



# **TECHNICAL DATA**

MIRAGE® QUICK RESPONSE CONCEALED PENDENT SPRINKLER VK465 (K4.2)

The Viking Corporation, 210 N Industrial Park Drive, Hastings MI 49058
Telephone: 269-945-9501 Technical Services: 877-384-5464 Fax: 269-818-1680 Email: techsvcs@vikingcorp.com



# THIS PAGE INTENTIONALLY LEFT BLANK